

# XUYFANEP60050

photo-electric sensor - XUY - fork - teach -  
50X59mm - 12..24VDC - M8

Product availability: Non-Stock - Not normally stocked in distribution facility



## Main

|                               |  |
|-------------------------------|--|
| Range of product              | OsiSense XU  |
| Series name                   | Application  |
| Electronic sensor type        | Photo-electric sensor  |
| Sensor name                   | XUY  |
| Sensor design                 | Fork   |
| Detection system              | Thru beam  |
| Emission                      | Infrared LED, modulated  |
| Passage width                 | 1.97 in (50 mm)  |
| Passage depth                 | 2.32 in (59 mm)  |
| Material                      | Metal/plastic  |
| Supply circuit type           | DC   |
| Wiring technique              | 4-wire   |
| Discrete output type          | PNP and NPN  |
| Discrete output function      | 1 NO or 1 NC programmable  |
| Electrical connection         | 1 male connector M8, 4 pins  |
| Product specific application  | Detection on small conveyor<br>Detection of double sheet<br>Detection of reference marks<br>Detection on vibrating rail<br>Detection of labels |
| [Sn] nominal sensing distance | 1.97 in (50 mm)  |

## Complementary

|                                       |   |
|---------------------------------------|---|
| Enclosure material                    | Painted aluminium and polyamide/glass   |
| Keypad type                           | Yellow  |
| Minimum object diameter for detection | 0.01 in (0.2 mm)  |
| Type of output signal                 | Discrete  |
| Output type                           | Solid state   |
| Status LED                            | 1 LED (red) adjustment mode and keypad locking<br>1 LED (yellow) output state |
| [Us] rated supply voltage             | 12...24 V DC with reverse polarity protection                                 |
| Supply voltage limits                 | 10...30 V DC  |
| Switching capacity in mA              | 100 mA (overload and short-circuit protection)                                |
| Switching frequency                   | 10 kHz  |
| Voltage drop                          | < 2 V (closed state)  |
| Current consumption                   | 40 mA (no-load)   |
| Load capacitance                      | 330 nF  |
| Time response                         | -20...20 µs   |
| Setting-up                            | Self teaching   |
| Product weight                        | 0.42 lb(US) (0.19 kg)   |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

|                                       |  |
|---------------------------------------|--|
| Product certifications                | CULus<br>CE  |
| Ambient air temperature for operation | -4...140 °F (-20...60 °C)  |
| Ambient air temperature for storage   | -22...176 °F (-30...80 °C)   |
| Immunity to ambient light             | 10000 lux with natural light<br>5000 lux with incandescent bulb            |
| Vibration resistance                  | 7 gn, amplitude = +/- 0.75 mm (f = 10...55 Hz) conforming to IEC 60068-2-6 |
| Shock resistance                      | 30 gn (duration = 11 ms) conforming to IEC 60068-2-27                      |
| IP degree of protection               | IP65 conforming to IEC 60529   |

## Ordering and shipping details

|                       |                                |
|-----------------------|--------------------------------|
| Category              | 22481 - SENSORS, PHOTOELECTRIC |
| Discount Schedule     | DS2                            |
| GTIN                  | 003389119006514                |
| Nbr. of units in pkg. | 1                              |
| Package weight(Lbs)   | 0.20000000000000001            |
| Returnability         | N                              |
| Country of origin     | FR                             |

## Offer Sustainability

|                           |  |
|---------------------------|--|
| RoHS (date code: YYWW)    | Compliant - since 0648 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a> |
| California proposition 65 | WARNING: This product can expose you to chemicals including:   |
| ----- Substance 1         | Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and  |
| ----- Substance 2         | Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.         |
| ----- More information    | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                      |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Dimensions



(1) Optical axis

Dimensions in mm

| A  | B  | b1 | C  |
|----|----|----|----|
| 50 | 59 | 74 | 40 |

Dimensions in in.

| A    | B    | b1   | C    |
|------|------|------|------|
| 1.97 | 2.32 | 2.91 | 1.57 |

## Wiring Schemes

### M8 Connector



- 1 : BN: Brown
- 2 : WH: White
- 3 : BU: Blue
- 4 : BK: Black

### 4-Wire, PNP/NPN Outputs



- BN : Brown
- WH : White
- BK : Black
- BU : Blue

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XUYFANEP60050](#)