



Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range	TeSys
Product name	TeSys GB2
Device short name	GB2
Product or component type	Circuit breaker
Device application	Control
Poles description	2P
Network type	AC/DC
Utilisation category	Category A conforming to IEC 60947-2 DC-12 conforming to IEC 60947-5-1 DC-13 conforming to IEC 60947-5-1
Network frequency	50/60 Hz conforming to IEC 60947-2
Breaking capacity	I _{cu} = 2 kA at 110 V AC 50/60 Hz conforming to IEC 60947-2 I _{cu} = 1.5 kA at 24 V DC conforming to IEC 60947-2 I _{cu} = 1.5 kA at 230/240 V AC 50/60 Hz conforming to IEC 60947-2 I _{cu} = 1.5 kA at 400/415 V AC 50/60 Hz conforming to IEC 60947-2
[I _{cs}] rated service short-circuit breaking capacity	75 % at 110 V AC 50/60 Hz conforming to IEC 60947-2 75 % at 230/240 V AC 50/60 Hz conforming to IEC 60947-2 75 % at 400/415 V AC 50/60 Hz conforming to IEC 60947-2
Trip unit technology	Thermal-magnetic
Magnetic tripping current	138 A

Complementary

Mounting mode	By clips
Mounting support	Plate Rail
Mounting position	Horizontal Vertical
Control type	Toggle
[I _n] rated current	10 A
System Voltage	277 V AC 50/60 Hz conforming to CSA C22.2 No 14 415 V AC 50/60 Hz conforming to IEC 60947-2 277 V AC 50/60 Hz conforming to UL 1077
[U _{imp}] rated impulse withstand voltage	4 kV conforming to IEC 60947-2
Power dissipation per pole	2 W
Mechanical durability	8000 cycles
Electrical durability	8000 cycles
Connections - terminals	Connector 1 cable(s) 0...0.01 in ² (0.75...6 mm ²) - cable stiffness : solid - without cable end cable end Connector 2 cable(s) 0...0.01 in ² (0.75...4 mm ²) - cable stiffness : solid - without cable end cable end Connector 1 cable(s) 0...0.01 in ² (0.75...4 mm ²) - cable stiffness : flexible - with cable end cable end Connector 2 cable(s) 0...0 in ² (0.75...2.5 mm ²) - cable stiffness : flexible - with cable end cable end
Tightening torque	10.62 lbf.in (1.2 N.m) - on connector

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mechanical robustness	Shocks 22 Gn for 20 ms conforming to IEC 60068-2-27 Vibrations 5 Gn, 5...110 Hz conforming to IEC 60068-2-6
Quantity per set	Set of 3
9 mm pitches	4
Height	2.91 in (74 mm)
Width	1.18 in (30 mm)
Depth	2.76 in (70 mm)
Product weight	0.25 lb(US) (0.115 kg)

Environment

Standards	EN 60947-1 EN 60947-2 IEC 60947-1 IEC 60947-2
Protective treatment	TC
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-4...140 °F (-20...60 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)
Fire resistance	1760 °F (960 °C) conforming to IEC 60695-2-1
Operating altitude	9842.52 ft (3000 m)

Ordering and shipping details

Category	22631 - TELE CIRCUIT BREAKER (GB2)
Discount Schedule	I
GTIN	00785901488118
Nbr. of units in pkg.	3
Package weight(Lbs)	0.22
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details- Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GB2DB16](#)