



Main

Range of Product	Twido
Product or Component Type	Compact base controller
Discrete I/O number	10
Discrete input number	6
Discrete input voltage	24 V
Discrete input voltage type	DC
Discrete output number	4 relay
[Us] rated supply voltage	100...240 V AC
Use of slot	Memory cartridge or realtime clock cartridge
Data backed up	Internal RAM lithium, 30 days 10 h 10 year(s)
Integrated connection type	Power supply Non isolated serial link mini DIN, Modbus/character mode master/slave RTU/ASCII RS485) half duplex, 38.4 kbit/s

Complementary

Discrete input logic	Sink or source
Input voltage limits	20.4...28.8 V
Discrete input current	11 mA I0.0 to I0.1 7 mA I0.2 to I0.5
Input impedance	2100 Ohm I0.0 to I0.1 3400 Ohm I0.2 to I0.5
Filter time	35 µs + programmed filter time for I0.0 to I0.5 at state 1 45 µs + programmed filter time for I0.0 to I0.5 at state 0
Insulation between channel and internal logic	1500 Vrms for 1 minute
Insulation resistance between channel	None
Minimum load	0.1 mA
Contact resistance	30000 µOhm
Load current	2 A 240 V AC inductive 30 cyc/mn relay output 2 A 240 V AC resistive 30 cyc/mn relay output 2 A 30 V DC inductive 30 cyc/mn relay output 2 A 30 V DC resistive 30 cyc/mn relay output
Mechanical durability	20000000 cycles relay output
Electrical durability	100000 cycles relay output
Current consumption	24 mA 5 V DC at state 1 26 mA 24 V DC at state 1 5 mA 5 V DC at state 0
I/O connection	Non-removable screw terminal block
Network Frequency	50/60 Hz
Supply voltage limits	85...264 V
Network frequency limits	47...63 Hz
Power supply output current	0.25 A 24 V DC sensors
Input Current	250 mA
Inrush current	35 A
Protection type	Power protection internal fuse
Power consumption in VA	20 VA 100 V 30 VA 264 V
Insulation resistance	> 10 MOhm at 500 V, between I/O and earth terminals > 10 MOhm at 500 V, between supply and earth terminals

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Program memory	700 instructions
Exact time for 1 Kinstruction	1 ms
System overhead	0.5 ms
Memory description	Internal RAM, 128 counters, no floating, no trigonometrical Internal RAM, 128 internal bits, no floating, no trigonometrical Internal RAM, 3000 internal words, no floating, no trigonometrical Internal RAM, 64 timers, no floating, no trigonometrical
Free slots	1
Realtime clock	Without
Counting input number	1 20000 Hz 32 bits 3 5000 Hz 16 bits
Analogue adjustment points	1 point adjustable from 0...1023
Status LED	PWR 1 LED Green) RUN 1 LED Green) I/O status 1 LED per channel Green) Module error (ERR) 1 LED Red) User pilot light (STAT) 1 LED
Depth	2.76 in (70 mm)
Height	3.15 in (80 mm)
Width	3.54 in (90 mm)
Terminals description PLC n°1	ALT COM_NEG#0-5 (2)IN_DIS#2 (+)PW_OUT_POS (-)PW_OUT_NEG (5)IN_DIS#5 (3)IN_DIS#3 (0)IN_DIS#0 (4)IN_DIS#4 TB_TOP (1)IN_DIS#1
Terminals description PLC n°2	COM_POS#0-5 (0)IN_DIS#0 (-)PW_OUT_NEG (3)IN_DIS#3 (1)IN_DIS#1 (4)IN_DIS#4 ALT_1 TB_TOP (5)IN_DIS#5 (+)PW_OUT_POS (2)IN_DIS#2
Terminals description PLC n°3	(GND)GROUND (0)OUT_DIS#0 (2)OUT_DIS#2 (3)OUT_DIS#3 (L)PW TB_BOTTOM (N)PW (1)OUT_DIS#1 (COM1)COM#3 (COM0)COM#0-2
Net Weight	0.51 lb(US) (0.23 kg)

Environment

Immunity to microbreaks	10 ms
Dielectric strength	1500 V for 1 minute, between I/O and earth terminals 1500 V for 1 minute, between supply and earth terminals
Product certifications	UL CSA
Marking	CE
Ambient Air Temperature for Operation	32...131 °F (0...55 °C)
Ambient Air Temperature for Storage	-13...158 °F (-25...70 °C)
Relative humidity	30...95 % without condensation
IP Degree of Protection	IP20
Operating altitude	0...6561.68 ft (0...2000 m)
Storage altitude	0.00...9842.52 ft (0...3000 m)

Vibration resistance	0.075 mm 10...57 Hz 35 mm symmetrical DIN rail 1 gn 57...150 Hz 35 mm symmetrical DIN rail 1.6 mm 2...25 Hz plate or panel with fixing kit 4 gn 25...100 Hz plate or panel with fixing kit
Shock resistance	15 gn 11 ms

Ordering and shipping details

Category	22531 - PLCS, TWIDO, TWD
Discount Schedule	PC12
GTIN	3595862044202
Nbr. of units in pkg.	1
Package weight(Lbs)	12.66 oz (359.0 g)
Returnability	No
Country of origin	JP


Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.13 in (10.5 cm)
Package 1 width	4.33 in (11 cm)
Package 1 Length	4.92 in (12.5 cm)

Contractual warranty


Warranty	18 months
----------	-----------

Dimensions




(1) 8.5 mm (0.33 in) when the clamp is pulled out.


Minimum Clearances for a Compact Base and Expansion I/O Modules



Mounting Hole Layout




AC Power Supply Wiring Diagram




DC Source Inputs Wiring Diagrams

External Power




Internal Power




Max current: 250mA.

DC Sink Inputs Wiring Diagrams

External Power





Internal Power



Max current: 250mA.


Relay and Transistor Outputs Wiring Diagram





Performance Curves

I/O Usage Limits



- (1) Limit for TWDLCA•AA16DRF, TWDLCA•A24DRF, TWDLCA•40DRF and TWDLCA•40DRF
- (2) All compact bases

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[TWDLCAA10DRF](#)