



Main

Range of Product	Zelio Control
Product or Component Type	Industrial measurement and control relays
Relay Type	Current measurement relay
Relay name	RM4J
Relay monitored parameters	Overcurrent or undercurrent detection
Time delay	Adjustable 0.05...30 s
Maximum power consumption in VA	3.3 VA AC
Measurement range	1...5 A current AC 1...5 A current DC 3...15 A current AC 3...15 A current DC 300...1500 mA current AC 300...1500 mA current DC
Contacts type and composition	2 C/O

Complementary

Maximum switching voltage	440 V AC
[Us] Rated Supply Voltage	24...240 V AC 50/60 Hz +/- 5 % 24...240 V DC
Operating voltage tolerance	0.85...1.1 Uc
Maximum power consumption in W	1.2 W DC
Output contacts	2 C/O
Maximum measuring cycle	80 ms
Internal input resistance	0.06 Ohm 0.006 Ohm 0.02 Ohm
Permissible continuous overload	7 A 20 A 2 A
Permissible non repetitive overload	10 A <= 3 s 100 A 15 A
Setting accuracy of the switching threshold	+/- 5 %
Switching threshold drift	<= 0.06 % per degree centigrade depending permissible ambient air temperature <= 0.5 % within the supply voltage range (0.85...1.1 Un)
Setting accuracy of time delay	10 P
Time delay drift	<= 0.07 % per degree centigrade depending on temperature <= 0.5 % within the supply voltage range (0.85...1.1 Un)
Hysteresis	5...30 % adjustable current threshold setting
Marking	CE : EMC 89/336/EEC CE : LVD 73/23/EEC
Overvoltage category	III IEC 60664-1
[Ui] rated insulation voltage	500 V IEC
Supply disconnection value	> 0.1 Uc
Operating position	Any position without derating
Connections - terminals	Screw terminals, 2 x 1.5 mm ² flexible with cable end Screw terminals, 2 x 2.5 mm ² flexible without cable end
Tightening torque	5.31...9.74 lbf.in (0.6...1.1 N.m)
Mechanical durability	30000000 cycles

[Ith] conventional free air thermal current	8 A
[Ie] rated operational current	2 A 24 V DC-13 158 °F (70 °C) IEC 60947-5-1/1991 2 A 24 V DC-13 158 °F (70 °C) VDE 0660 3 A 115 V AC-15 158 °F (70 °C) IEC 60947-5-1/1991 3 A 115 V AC-15 158 °F (70 °C) VDE 0660 3 A 24 V AC-15 158 °F (70 °C) IEC 60947-5-1/1991 3 A 24 V AC-15 158 °F (70 °C) VDE 0660 3 A 250 V AC-15 158 °F (70 °C) IEC 60947-5-1/1991 3 A 250 V AC-15 158 °F (70 °C) VDE 0660 0.1 A 250 V DC-13 158 °F (70 °C) IEC 60947-5-1/1991 0.1 A 250 V DC-13 158 °F (70 °C) VDE 0660 0.3 A 115 V DC-13 158 °F (70 °C) IEC 60947-5-1/1991 0.3 A 115 V DC-13 158 °F (70 °C) VDE 0660
Switching capacity in mA	10 mA 12 V
Switching voltage	250 V AC
Contacts material	90/10 silver nickel contacts
Number of cables	2
Width	1.77 in (45 mm)
Depth	3.15 in (80 mm)
Terminals description ISO n°1	(C-B1-B2-B3)CO (25-26-28)OC (A1-A2)CO (15-16-18)OC
Output relay state	Tripped if V measured > V set Tripped if A measured > A set
9 mm pitches	5
Net Weight	0.45 lb(US) (0.204 kg)

Environment

Electromagnetic compatibility	Electrostatic discharge 6 kV contact discharge)level 3 IEC 61000-4-2 Electrostatic discharge 8 kV air discharge)level 3 IEC 61000-4-2
Standards	EN/IEC 60255-6
Product certifications	GL UL CSA
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Ambient air temperature for operation	-4...149 °F (-20...65 °C)
Environmental characteristic	3K3
Relative humidity	15...85 % IEC 60721-3-3
Shock resistance	15 gn 11 ms IEC 60255-21-1
IP degree of protection	IP20 IEC 60529 terminals) IP50 IEC 60529 casing)
Pollution degree	3 IEC 60664-1
Dielectric test voltage	2.5 kV
Non-dissipating shock wave	4.8 kV
Resistance to electrostatic discharge	6 kV contact IEC 61000-4-2 level 3 8 kV air IEC 61000-4-2 level 3
Resistance to electromagnetic fields	9.14 V/m (10 V/m) IEC 61000-4-3 level 3
Resistance to fast transients	2 kV IEC 61000-4-4 level 3
Protection against electric shocks	2 kV level 3 IEC 61000-4-5
Disturbance radiated/conducted	CISPR 22 - class A CISPR 11 group 1 - class A

Ordering and shipping details

Category	22376-RELAYS-MEASUREMENT(RM4)
Discount Schedule	CP2
GTIN	00785901481577
Package weight(Lbs)	0.45 lb(US) (0.203 kg)
Returnability	No
Country of origin	ID

Packing Units


Package 1 Height	0.510 dm
Package 1 width	0.850 dm
Package 1 Length	1.600 dm

Contractual warranty

Warranty	18 months
----------	-----------


Current Measurement Relays

Dimensions




Current Measurement Relays

Rail mounting




Screw fixing



Current Measurement Relays


RM4JA01 Wiring Diagram



A1-A2 Supply voltage
B1, B2, B3, C Currents to be measured (see table below)

Connection and current values to be measured	
B1-C	3...30 mA
B2-C	10...100 mA
B3-C	0.1...1 A


RM4JA31 Wiring Diagram



A1-A2 Supply voltage
B1, B2, B3, C Currents to be measured (see table below)

Connection and current values to be measured	
B1-C	3...30 mA
B2-C	10...100 mA
B3-C	0.1...1 A

RM4JA32 Wiring Diagram




A1-A2 Supply voltage
B1, B2, B3, C Currents to be measured (see table below)

Connection and current values to be measured	
B1-C	0.3...1.5 A
B2-C	1...5 A
B3-C	3...15 A


Application Schemes

Example: Detection of Blockage on a Crusher (Overcurrent Function)

Current measured ≤ 15 A




Current measured > 15 A



Electrical Durability and Load Limit Curves

AC Load


Curve 1: Electrical durability of contacts on resistive load in millions of operating cycles



X Current broken in A

Y Millions of operating cycles

Curve 2: Reduction factor k for inductive loads (applies to values taken from durability Curve 1)




X Power factor on breaking ($\cos \phi$)

Y Reduction factor K

DC Load

Load limit curve




X Current in A

Y Voltage in V

1 L/R = 20 ms

2 L/R with load protection diode


3 Resistive load



Function Diagram

Overcurrent Detection

Function ">"



Legend

t Time delay

U A1-A2 Supply voltage

IS1 Setting current threshold

IS2 Current measured


15-18, 15-16; 25-28, 25-26 Output relays connections

Relay status: black color = energized.

Function Diagram

Undercurrent Detection

Function "<"



Legend

t Time delay

U A1-A2 Supply voltage

IS1 Setting current threshold

IS2 Current measured

15-18, 15-16; 25-28, 25-26 Output relays connections

Relay status: black color = energized.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RM4JA32MW](#)