



Product availability: Stock - Normally stocked in distribution facility



Main

Range of product	Zelio Relay
Product or component type	Socket
Contact terminal arrangement	Separate

Complementary

Product compatibility	RXG plug-in relay 1 C/O
[Ui] rated insulation voltage	250 V
[Uimp] rated impulse withstand voltage	6 kV
Line Rated Current	10 A
System Voltage	250 V conforming to IEC 300 V conforming to UL
Connections - terminals	Screw terminals, clamping capacity: 1 x 0.25...1 x 2.5 mm ² (AWG 22...AWG 14) flexible with cable end Screw terminals, clamping capacity: 2 x 0.25...2 x 1 mm ² (AWG 22...AWG 17) flexible with cable end Screw terminals, clamping capacity: 2 x 0.5...2 x 1.5 mm ² (AWG 20...AWG 16) solid without cable end Screw terminals, clamping capacity: 1 x 0.5...1 x 2.5 mm ² (AWG 20...AWG 14) solid without cable end
Screw type	M3

Environment

Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Ambient air temperature for operation	-40...158 °F (-40...70 °C)
Relative humidity	10...85 %
Standards	UL 508 CSA C22.2 No 14 IEC 61984
Product certifications	China RoHS EAC UL RoHS REACH CSA CE
IP degree of protection	IP20
Overvoltage category	III
Pollution degree	3

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.


Ordering and shipping details

Category	21128 - ZELIO ICE CUBE RELAY ACCESSORIES
Discount Schedule	CP2
GTIN	00785901412151
Nbr. of units in pkg.	10
Package weight(Lbs)	8.999999999999997E-2
Returnability	Y
Country of origin	CN

Offer Sustainability


Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1426 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Dimensions



(1) Maintaining clamp

Wiring Diagram



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RGZE1S35M](#)