


# SSP3A250F7T

solid state relay -panel-input 90-140VAC,  
output 48-530VAC,50A-Thermal Interface



Product availability: Stock - Normally stocked in distribution facility



## Main

Range of product	Zelio Relay
Product or component type	Solid state relay
Provided accessory	Thermal interface
Device short name	SSP
Mounting support	Panel
Phase	3 phases
Contacts type and configuration	3 NO
Solid state output type	Zero voltage switching

## Complementary

Control type	Without test button
[Uc] control circuit voltage	90...140 V AC
Minimum switching voltage	90 V AC turn-on
Maximum switching voltage	10 V AC turn-off
Response time	30 ms turn-off 20 ms turn-on
Input current	7...16 mA
Output voltage	48...530 V AC
Load current	0.1...50 A
Transient overvoltage	1200 V
Surge current	715 A for 20 ms 750 A for 16.6 ms 150 A for 1 s
Maximum I <sup>2</sup> t for fusing	2520 A <sup>2</sup> .s 10 ms at 50 Hz half cycle 2320 A <sup>2</sup> .s 8.3 ms at 60 Hz half cycle
Leakage current	<= 3 mA off-state
Voltage drop	<= 1.35 V on-state
DV/dt	500 V/μs off-state at maximum voltage
Power factor	0.5 with maximum load
Motor controller rating	1.5 hp at <= 40 °C 120 V AC 3 hp at <= 40 °C 240 V AC 7.5 hp at <= 40 °C 480 V AC 8.8 hp at <= 40 °C 530 V AC
Motor power kW	1.11 kW at 104 °F (40 °C) 120 V AC 2.22 kW at 104 °F (40 °C) 240 V AC 5.55 kW at 104 °F (40 °C) 480 V AC 6.47 kW at 104 °F (40 °C) 530 V AC
Insulation resistance	>= 1000 MOhm at 500 V DC
Maximum capacitance	8 pF input/output
Dielectric strength	4 kV AC input/output 4 kV AC input or output to case
Tightening torque	0.9...1.1 N.m input 1.7...2.2 N.m output
Connections - terminals	Screw terminals : 1 x 0.2...1 x 2.5 mm <sup>2</sup> , (AWG 24...AWG 14) input Screw terminals : 1 x 1.5...1 x 10 mm <sup>2</sup> , (AWG 16...AWG 8) output
Thermal resistance	0.12 °C/W
LED indicator	LED, green input

IP degree of protection	IP20
Product weight	0.53 lb(US) (0.24 kg)
Width	101.3 mm
Height	79.7 mm
Depth	35.4 mm


### Environment

Flame retardance	V0 conforming to UL 94
Ambient air temperature for operation	-40...176 °F (-40...80 °C)
Ambient air temperature for storage	-40...257 °F (-40...125 °C)
Pollution degree	2
Overvoltage category	III
Product certifications	UL RoHS CSA REACH
Marking	CE
Standards	IEC 61000 IEC 60950-1 IEC 62314

### Ordering and shipping details

Category	22375 - INTERFACE MODULE(ABA,R,S)
Discount Schedule	CP2
GTIN	00785901971085
Nbr. of units in pkg.	1
Package weight(Lbs)	0.9100000000000003
Returnability	Y
Country of origin	MX

### Offer Sustainability


Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1328 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

Dimensions



(1) 4 Mounting slots

Derating Curves



A : Load Current (Amperes)  
B : Ambient Temperature (°C)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SSP3A250F7T](#)