



Schneider Electric Relays


200 N. Martingale Rd., Suite 1000

Schaumburg, IL 60173

Phone: 847-441-2540 • Fax: 847-881-0741

E-Mail: relays@schneider-electric.com • Web site: www.serelays.com

ITEM # 788XCXRC1-24D, 788 POWER RELAYS - SIDE FLANGE / 3PDT, 10 AMP RATING



[SPECIFICATIONS](#) | [COIL CHARACTERISTICS](#) | [PERFORMANCE CHARACTERISTICS](#) | [ENVIRONMENT](#) | [PRODUCT CERTIFICATIONS](#)

Specifications	
Check Inventory	Check Distributor Inventory
Status	NCNR
Legacy Part No.	788XCXC1-24D
Terminal Style	Plug-in
Contact Configuration	3PDT
Thermal (Carrying) Current	10 A
Coil Resistance (Ohms)	470 Ohm
Load Type	Standard
Contact Materials	Silver Alloy with Gold Flash
Maximum Switching Voltages	IEC: 250 VAC/28 VDC UL: 300 VAC/30 VDC
Switching Current at Voltage (AC, Resistive)	IEC: 10 A at 250 VAC 50/60 Hz UL: 10 A at 277 VAC 50/60 Hz

Switching Current at Voltage (DC, Resistive)	IEC: 10 A at 28 VDC UL: 10 A at 30 VDC
---	---

Switching Current at Voltage (HP)	1 at 277 VAC hp 1/3 at 120 VAC hp
--	--------------------------------------

Pilot Duty	B300
-------------------	------

Minimum Switching Requirement	10 mA at 17 VDC
--------------------------------------	-----------------

Cover Options	Flange Cover
----------------------	--------------

Features	Mechanical flag indicator
-----------------	---------------------------

California Proposition 65 Warning



WARNING: This product can expose you to chemicals including:

Substance 1: Nickel compounds, which is known to the State of California to cause cancer.

Substance 2: DIDP, which is known to the State of California to cause birth defects or other reproductive harm.

For more information go to www.p65warnings.ca.gov

Coil Characteristics

Coil Voltage	24 VDC
---------------------	--------

Operating Range - % of Nominal (AC)	85 to 110 %
--	-------------

Operating Range - % of Nominal (DC)	80 to 110 %
--	-------------

Average Consumption (DC / W)	1.40 W
-------------------------------------	--------

Drop-out Voltage Threshold (DC)	10 %
--	------

Performance Characteristics

Electrical Life (UL508), Operations at Rated Current (Resistive)	100000
---	--------

Mechanical Life, Unpowered	5000000
-----------------------------------	---------

Operating Time (Response Time)	20 ms
---------------------------------------	-------

Dielectric Strength - Between Coil and Contact (AC)	2500 V(rms)
--	-------------

Dielectric Strength - Between Poles (AC)	2000 V(rms)
---	-------------

Environment

Vibration Resistance - Operational	3 g-n at 35-150 Hz
---	--------------------

Shock Resistance	10 g-n
-------------------------	--------

Degree of Protection

IP 40

Weight83 g
2.93 oz**Product Certifications****Agency Approvals**UL (E164862)
CSA (225619 Class 3211-07)
CE
RoHs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[788XCXRC1-24D](#)