

### Features:

- Tolerance to  $\pm 0.05\%$
- Low TCR to  $\pm 10$  ppm/ $^{\circ}\text{C}$
- AEC-Q200 compliant
- RoHS compliant, lead free and halogen free
- REACH compliant

### Applications:


- Industrial electronics
- Communication devices
- Measuring instrument
- Converters

## Electrical Specifications

Type / Code	Power Rating (W) @ 70°C	Maximum Working Voltage (V) <sup>(1)</sup>	Maximum Overload Voltage (V)	TCR (ppm/ $^{\circ}\text{C}$ )	Ohmic Range ( $\Omega$ ) and Tolerance				
					$\pm 0.05\%$	$\pm 0.1\%$	$\pm 0.25\%$	$\pm 0.5\%$	$\pm 1\%$
RNCA0402	0.063	50	100	$\pm 10$	49.9 - 12 K	10 - 68.1 K			
				$\pm 15$		4.7 - 221 K			
RNCA0603	0.1	75	150	$\pm 10$	49.9 - 30.1 K	10 - 332 K			
				$\pm 15$		4.7 - 681 K			
RNCA0805	0.125	150	300	$\pm 10$	49.9 - 49.9 K	10 - 681 K			
				$\pm 15$		4.7 - 1 M			
RNCA1206	0.25	200	400	$\pm 10$	49.9 - 100 K	10 - 1 M			
				$\pm 15$		4.7 - 1.5 M			


(1) Lesser of  $\sqrt{\text{PR}}$  or maximum working voltage.

## Mechanical Specifications



Type / Code	L Body Length	W Body Width	H Body Height	$l_1$ Top Termination	$l_2$ Bottom Termination	Unit
RNCA0402	0.039 $\pm$ 0.004	0.020 $\pm$ 0.002	0.012 $\pm$ 0.002	0.008 $\pm$ 0.004	0.008 $\pm$ 0.004	inches
	1.00 $\pm$ 0.10	0.50 $\pm$ 0.05	0.30 $\pm$ 0.05	0.20 $\pm$ 0.10	0.20 $\pm$ 0.10	mm
RNCA0603	0.063 $\pm$ 0.006	0.031 $\pm$ 0.004	0.018 $\pm$ 0.004	0.012 $\pm$ 0.008	0.012 $\pm$ 0.008	inches
	1.60 $\pm$ 0.15	0.80 $\pm$ 0.10	0.45 $\pm$ 0.10	0.30 $\pm$ 0.20	0.30 $\pm$ 0.20	mm
RNCA0805	0.079 $\pm$ 0.006	0.049 $\pm$ 0.006	0.022 $\pm$ 0.004	0.014 $\pm$ 0.008	0.016 $\pm$ 0.008	inches
	2.00 $\pm$ 0.15	1.25 $\pm$ 0.15	0.55 $\pm$ 0.10	0.35 $\pm$ 0.20	0.40 $\pm$ 0.20	mm
RNCA1206	0.120 $\pm$ 0.006	0.063 $\pm$ 0.006	0.022 $\pm$ 0.004	0.018 $\pm$ 0.008	0.020 $\pm$ 0.008	inches
	3.05 $\pm$ 0.15	1.60 $\pm$ 0.15	0.55 $\pm$ 0.10	0.45 $\pm$ 0.20	0.50 $\pm$ 0.20	mm

Power Derating Curve:




Performance Characteristics			
Test	Test Method	Test Specifications	Test Condition
Temperature Coefficient of Resistance (TCR)	JIS-C-5201-1 4.8 IEC-60115-1 4.8	At 25 / -55 °C and 25 °C / +125 °C, 25 °C is the reference temperature	Refer to Electrical Specification table
Short Time Overload	JIS-C-5201-1 4.13 IEC-60115-1 4.13	2.5 times RCWV or max. overload voltage whichever is less for 5 seconds	± (0.3% + 0.05 Ω)
Leaching	JIS-C-5201-1 4.18 IEC-60068-2-58 8.2.1	260 ± 5 °C for 30 seconds	>95% coverage No visual damage
Resistance to Soldering Heat	JIS-C-5201-1 4.18 IEC-60115-1 4.18	260 ± 5 °C for 10 seconds	± (0.3% + 0.05 Ω) No visual damage
Insulation Resistance	JIS-C-5201-1 4.6 IEC-60115-1 4.6	Apply 100VDC for 1 minute	≥ 10 G Ω
Temperature Cycling	JESD22 Method JA-104	1000 cycles (-55 °C to +125 °C). Measurement at 24 ± 4 hours after test conclusion. 30 minutes maximum dwell time at each temperature extreme.	± (0.3% + 0.05 Ω) No visual damage
Resistance to Solvent	MIL-STD-202 Method 215	Add aqueous wash chemical - OKEM clean or equivalent	± (0.3% + 0.05 Ω) No visual damage
Biased Humidity	MIL-STD-202 Method 103	1000 hours; 85 °C / 85% RH, 10% of operating power. Measurement at 24 ± 4 hours after test conclusion.	± (0.3% + 0.05 Ω)
High Temperature Exposure (Storage)	MIL-STD-202 Method 108	1000 hours at T=155 °C. Unpowered. Measurement at 24 ± 4 hours after test conclusion.	± (0.5% + 0.05 Ω)
Operation Life	MIL-STD-202 Method 108	Condition D Steady State TA = 125 °C at derated power. Measurement at 24 ± 4 hours after test conclusion.	± (0.3% + 0.05 Ω)
External Visual	MIL-STD-883 Method 2009	Electrical test not required Inspect device construction, marking and workmanship.	-
Mechanical Shock	MIL-STD-202 Method 213	Test 1/2 sine pulse, peak value: 100 g, normal duration: 6 ms. Velocity change: 12.3 ft/sec. 10 shocks in each direction, total of 30 shocks	± (0.3% + 0.05 Ω)

Performance Characteristics (cont.)			
Test	Test Method	Test Specifications	Test Condition
Vibration	MIL-STD-202 Method 204	5 g's for 20 minutes, 12 cycles each of 3 orientations. Note: test from 10 - 2000 H	$\pm (0.3\% + 0.05 \Omega)$
ESD	AEC-Q200-002 or ISO/DIS 10605	Human body model 0402: 400V, 0603: 1000V 0805: 1500V, 1206: 2000V	$\pm (0.3\% + 0.05 \Omega)$
Solderability	J-STD-002	(1) 4 hours 155 °C dry heat (2) 245 $\pm$ 5 °C 3 seconds	$\pm (0.3\% + 0.05 \Omega)$
Terminal Strength (SMD)	AEC Q200-006	Pressurizing force for 60 seconds 0402 / 0603: 8N 0805 / 1206: 17.7N	No breakage
Board Flex	AEC Q200-005	Bending once for 60 seconds. 3mm	$\pm (0.3\% + 0.05 \Omega)$
Sulfur Test (FoS)	ASTM B809-95 ANSI/EIA-977	60 $\pm$ 2 °C, no power rating for 1000 hours	$\pm (1\% + 0.05 \Omega)$
		105 $\pm$ 2 °C, no power rating for 1000 hours	$\pm (4\% + 0.05 \Omega)$

Operating temperature range is -55 °C to +155 °C


### Soldering Condition

Wave solder temperature condition:



Wave Soldering (Flow Soldering)


Solder reflow temperature condition:



IR Reflow Soldering


- Rework temperature (hot air equipment): 350 °C, 3 ~ 5 seconds
- Recommended reflow methods:
  - IR, vapor phase oven, hot air oven. If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

## Recommended Land Pattern




Type / Code	A	B	C	Unit
RNCA0402	0.020	0.063	0.028	inches
	0.50	1.60	0.70	mm
RNCA0603	0.031	0.094	0.039	inches
	0.80	2.40	1.00	mm
RNCA0805	0.051	0.114	0.055	inches
	1.30	2.90	1.40	mm
RNCA1206	0.087	0.165	0.067	inches
	2.20	4.20	1.70	mm

## Reel Specifications



Type / Code	ØA	ØB	ØC	ØD	W	ØM	Unit
All sizes	0.079 ± 0.020	0.531 ± 0.039	0.827 ± 0.039	2.362 ± 0.039	0.453 ± 0.079	7.008 ± 0.079	inches
	2.00 ± 0.50	13.50 ± 1.00	21.00 ± 1.00	60.00 ± 1.00	11.50 ± 2.00	178.00 ± 2.00	mm

## Packaging Specifications – Paper Tape




Type / Code	A	B	W	E	F	Unit
RNCA0402	0.028 ± 0.004	0.047 ± 0.004	0.315 ± 0.008	0.069 ± 0.004	0.138 ± 0.002	inches
	0.70 ± 0.10	1.20 ± 0.10	8.00 ± 0.20	1.75 ± 0.10	3.50 ± 0.05	mm
RNCA0603	0.041 ± 0.008	0.071 ± 0.008	0.315 ± 0.008	0.069 ± 0.004	0.138 ± 0.002	inches
	1.05 ± 0.20	1.80 ± 0.20	8.00 ± 0.20	1.75 ± 0.10	3.50 ± 0.05	mm
RNCA0805	0.061 ± 0.008	0.091 ± 0.008	0.315 ± 0.008	0.069 ± 0.004	0.138 ± 0.002	inches
	1.55 ± 0.20	2.30 ± 0.20	8.00 ± 0.20	1.75 ± 0.10	3.50 ± 0.05	mm
RNCA1206	0.075 ± 0.008	0.138 ± 0.008	0.315 ± 0.008	0.069 ± 0.004	0.138 ± 0.002	inches
	1.90 ± 0.20	3.50 ± 0.20	8.00 ± 0.20	1.75 ± 0.10	3.50 ± 0.05	mm

Packaging Specifications – Paper Tape (cont.)						
Type / Code	G	H	T	ØD	P	Unit
RNCA0402	0.157 ± 0.004	0.079 ± 0.002	0.018 ± 0.004	0.059 +0.004 / -0	0.079 ± 0.004	inches
	4.00 ± 0.10	2.00 ± 0.05	0.45 ± 0.10	1.50 +0.1 / -0	2.00 ± 0.10	mm
RNCA0603	0.157 ± 0.004	0.079 ± 0.002	0.024 ± 0.004	0.059 +0.004 / -0	0.157 ± 0.004	inches
	4.00 ± 0.10	2.00 ± 0.05	0.60 ± 0.10	1.50 +0.1 / -0	4.00 ± 0.10	mm
RNCA0805	0.157 ± 0.004	0.079 ± 0.002	0.030 ± 0.004	0.059 +0.004 / -0	0.157 ± 0.004	inches
	4.00 ± 0.10	2.00 ± 0.05	0.75 ± 0.10	1.50 +0.1 / -0	4.00 ± 0.10	mm
RNCA1206	0.157 ± 0.004	0.079 ± 0.002	0.030 ± 0.004	0.059 +0.004 / -0	0.157 ± 0.004	inches
	4.00 ± 0.10	2.00 ± 0.05	0.75 ± 0.10	1.50 +0.1 / -0	4.00 ± 0.10	mm

### Peel Force of Top Cover Tape

(1) The peel speed shall be about 300mm/min ± 5%  
 (2) The peel force of top cover tape shall be between 8gf to 60gf



### RoHS Compliance

Stackpole Electronics has joined the worldwide effort to reduce the amount of lead in electronic components and to meet the various regulatory requirements now prevalent, such as the European Union’s directive regarding “Restrictions on Hazardous Substances” (RoHS 3). As part of this ongoing program, we periodically update this document with the status regarding the availability of our compliant components. All our standard part numbers are compliant to EU Directive 2011/65/EU of the European Parliament as amended by Directive (EU) 2015/863/EU as regards the list of restricted substances.

### “Conflict Metals” Commitment

We at Stackpole Electronics, Inc. are joined with our industry in opposing the use of metals mined in the “conflict region” of the eastern Democratic Republic of the Congo (DRC) in our products. Recognizing that the supply chain for metals used in the electronics industry is very complex, we work closely with our own suppliers to verify to the extent possible that the materials and products we supply do not contain metals sourced from this conflict region. As such, we are in compliance with the requirements of Dodd-Frank Act regarding Conflict Minerals.


**Compliance to “REACH”**

We certify that all passive components supplied by Stackpole Electronics, Inc. are SVHC (Substances of Very High Concern) free and compliant with the requirements of EU Directive 1907/2006/EC, “The Registration, Evaluation, Authorization and Restriction of Chemicals”, otherwise referred to as REACH. Contact us for complete list of REACH Substance Candidate List.

**Environmental Policy**

It is the policy of Stackpole Electronics, Inc. to protect the environment in all localities in which we operate. We continually strive to improve our effect on the environment. We observe all applicable laws and regulations regarding the protection of our environment and all requests related to the environment to which we have agreed. We are committed to the prevention of all forms of pollution.

**How to Order**



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SEI Stackpole:](#)

[RNCA0603BTE10R0](#) [RNCA0603BTE2K00](#) [RNCA0805BTE10K0](#) [RNCA0805BTE10R0](#) [RNCA1206BTE1K00](#)  
[RNCA0402BTE10K0](#) [RNCA0805BTE100R](#) [RNCA0603BTE1K00](#) [RNCA0603BTE10K0](#) [RNCA0805BTE1K00](#)  
[RNCA1206BTE100R](#) [RNCA1206BTE10K0](#) [RNCA0603BTE100R](#)