



NOTE:  
 UNIT IS SUPPLIED WITH A 7.00 [177.8] DIA.  
 0-100 GRADUATED DIAL PLATE FOR PANEL  
 MOUNTING.



COIL SCHEMATIC  
 AS VIEWED FROM BASE END  
 FUSE RECOMMENDED BUT  
 NOT SUPPLIED



SPECIFICATIONS											
WIRING	INPUT		OUTPUT				SHAFT ROTATION TO INCREASE VOLTAGE	TERMINAL CONNECTIONS			
	VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD		CONSTANT IMPEDANCE LOAD		FOR INCREASING VOLTAGE AS VIEWED FROM BASE END			
				MAX. AMPS	MAX. KVA	MAX. AMPS		MAX. KVA	INPUT	JUMPER	OUTPUT
SINGLE PHASE	120	50/60	0-120	25	3.00	30	3.6	CW	2-4	---	4-3
			0-140	25	3.50	---	---	CCW	2-4	---	2-3
								CW	1-4	---	4-3
								CCW	2-5	---	2-3

UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ±  
 DECIMALS .005 HOLES .01 ANGLES DRAFT 1° UNITS IN [mm]  
 .XX .0001 .06 .0002 .01 1° 1-1/2°  
 .XXX .005  
 MATERIAL: ALL DIMENSIONS APPLY AFTER PLATING  
 TITLE: SPEC. CONTROL DRAWING VARIABLE TRANSFORMER MODEL: 2510CT  
 STACO ENERGY PRODUCTS CO. A COMPONENTS CORPORATION OF AMERICA COMPANY DAYTON, OHIO U.S.A.  
 DRAWN BY S.A. SMITH DATE 1/3/2001 FIRST USED ON 2510CT DO NOT SCALE DWG. CUSTOMER APPROVAL DATE  
 CHECKER DATE WEIGHT APPROX. 21 LBS CODE IDENT. NO. 83008 DWG. NO. 031-5001  
 ENGINEER DATE SCALE 1=1 SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Staco:](#)

[2510CT](#)