

FEATURES:

- 7 pin SMD package
- No-load input current as low as 5mA
- Continuous short-circuit protection
- High Efficiency up to 87%
- Unregulated Output Types
- 1.5KVDC ~ 3KVDC Isolation
- Industry Standard Pinout
- Designed to IEC62368, UL62368, EN62368
- UL Recognized

Specifications typical at TA=25°C nominal input voltage and rated output current unless otherwise specified

Part Number	Input Voltage Range	Output Voltage	Output Current	Efficiency	Capacitive Load(μF)
	Vdc	Vdc	mA	%TYP	Max.
EC4-05S05	4.5~5.5	5	200	82	2400
EC4-05S05P	4.5~5.5	5	200	82	2400
EC4-12S05P	9.6~14.4	5	200	82	2400
EC4-12S12P	9.6~14.4	12	84	85	680
EC4-12D05P	9.6~14.4	±5	±100	82	±1200
EC4-15D12P	12~18	±12	±42	85	±330

Note:

1: No suffix is standard isolation (1.5KVDC) e.g., EC4-05S05
*add suffix "3" for 3KVDC isolation

2: No "P" suffix = no short circuit protection, e.g., EC4-05S05
*add suffix "P" for short circuit protection, e.g., EC4-05S05P, EC4-05S12P3


3: Character after "-" is Input Voltage: 12=12Vdc, 15=15Vdc, 24=24Vdc
e.g., EC4-12S05P, EC4-15S12P3, EC4-24S15P.

ADAM TECH


DC-DC Converter EC4 Series

1 Watt

1.5KV ~ 3KV Isolated
Single & Dual Output
SIP7



Temperature Derating Graph



Input Specifications

Parameters	Conditions	Min	Typ	Max	Units
Voltage Range	Vo,Io Nom@Vin:5V		±10		%
	Vo,Io Nom@ Vin:12V,15V,24V		±20		%
Filter	Capacitor				

Output Specifications

Parameters	Conditions	Min	Typ	Max	Units
Voltage Tolerance	100% full load			±5	%
Short Circuit Protection	without suffix "P"			1	Sec
	With Suffix "P"		Continuous		
Line Regulation	For 1.0% OF Vin		1.2		%
Load Regulation	3.3V (10% To 100% F.L)		15	20	%
	5V (10% To 100% F.L)		10	15	%
	9V (10% To 100% F.L)		8	10	%
	12V (10% To 100% F.L)		7	10	%
	15V (10% To 100% F.L)		6	10	%
Ripple & Noise	24V (10% To 100% F.L)		5	10	%
	BW=DC To 20MHz @Vo:3.3V,5V,9V,12V,15V		30	75	mVp-p
	BW=DC To 20MHz @ Vo:24V		50	100	mVp-p

General Specifications


Parameters	Conditions	Min	Typ	Max	Units
Isolation Resistance	500Vdc	1000			MΩ
Isolation Capacitance	Input-output, 100KHz/0.1V		20		pF
Switching Frequency	Full load, nominal input @5V Vin		370		KHz
	Full load, nominal input @other Vin		250		KHz
Operating Temperature		-40		+105	°C
Storage Temperature		-55		+125	°C
Humidity	Non Condensing			95	%
Cooling	Free air Convection				
Case Material	DAP				
MTBF	MIL-HDBK-217F@25°C	3,500,000			Hours
Weight			2.1		g
Dimensions			19.5x6.0x10.0		mm

Part Number

EC4 - XX X XX X X X
A B C D E F G

A: Series
B: Input Voltage
C: Single (S) / Dual Output (D)
D: Output Voltage
E: Regulated (R)
F: Protection (P)
G: Isolation Voltage


Tolerance Envelope Graph



Electromagnetic Compatibility (EMC)


EMI	CE	CISPR32/EN55032 CLASS B (see Fig. 1 for recommended circuit)
	RE	CISPR32/EN55032 CLASS B (see Fig. 1 for recommended circuit)
EMS	ESD	IEC/EN61000-4-2 Air ±8kV , Contact ±4kV perf. Criteria B

Recommended Test Circuit




Vin	Cin	Single Vout	Cout	Dual Vout	Cout
5Vdc	4.7µF/25V	3.3Vdc	10µF/16V	±3.3Vdc	±4.7µF/16V
12Vdc	2.2µF/25V	5Vdc	10µF/16V	±5Vdc	±4.7µF/16V
15Vdc	2.2µF/25V	9Vdc	2.2µF/16V	±9Vdc	±1µF/16V
24Vdc	1µF/50V	12Vdc	2.2µF/25V	±12Vdc	±1µF/25V
--	--	15Vdc	1µF/25V	±15Vdc	±1µF/25V
--	--	24Vdc	1µF/50V	±24Vdc	±1µF/50V

EMC (CLASS B) Compliance Circuit



EMC Recommended Circuit Value Table		
EMI	C1	4.7μF /50V
	C2	4.7μF /50V
	CY	1nF/4kV
	C3	Recommended Test Circuit
	L	6.8μH

Markings and Dimensions




UNIT: mm unless otherwise specified, all tolerances are ±0.25

PIN Connection

PIN	1	2	4	5	6
Single	+Vin	-Vin	-Vout	No Pin	+Vout
Dual	+Vin	-Vin	-Vout	Com	+Vout

Packaging



Size (mm)			
A	B	C	D
9.5	16.5	522	5.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[EC4-12D05P](#)