



SECTION A-A
CUSTOMER DRAWING

- NOTES:
1. RECOMMENDED MOUNTING HOLE: Ø1.000 [25.40].
 2. IP68 RATED WHEN PROPERLY ASSEMBLED. IMMERSED IN 1.8M WATER FOR 24 HOURS.
 3. PARTS ARE SHIPPED ASSEMBLED.
 4. CABLE RANGE: Ø0.118– 0.236 [3.0-6.0] - TYP 2 PLACES.
 5. MATERIALS:
SEAL NUT, CLAMP NUT, HEX NUT - BLACK, THERMOPLASTIC UL746C (F1) UV RATED
GASKET, SEAL RING AND SEAL PLUGS - BLACK, SILICONE.
 6. THIS PRODUCT IS RoHS COMPLIANT.

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.						
					SIZE	WIDTH	MULT	LBS/M	TEMPER		
					FINISH			MATERIAL			
					SPEC No.			SPEC No.			
					FIRST USED ON			SCALE 1:1			
C	28375	03/30/21	PC	TJK	DATE DRAWN	BY	CHKD	APVD	Switchcraft®		
B	28315	09/09/20	PC	TJK	5/6/20	FM	FM	TJK			
A	28308	07/31/20	PC	TJK	5/6/20	FM	7/16/20				
REV	ECO NUMBER	DATE	BY	APVD	NAME M25 x 1.5 CABLE GLAND, 2 HOLE, CABLE RANGE Ø3.0 - 6.0mm			PART No.	REV		
REVISIONS					DO NOT SCALE DRAWING					CGM25N24X2	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[CGM25N24X2](#)