

Computer with DisplayPort 1.2-compatible graphics card (e.g. AMD Radeon with AMD Eyefinity) required for video wall mode. Backward compatible with most DisplayPort 1.1a equipment running current graphics drivers with feature set limited to that of your equipment. Compatibility with older graphics cards not guaranteed. MST compliant DisplayPort 1.2 graphics cards are limited to a bandwidth of 21.6 Gbps amongst all monitors, with higher resolution monitors using up more bandwidth. 1080p monitors will use up approximately 22% of bandwidth, whereas 4K monitors will use 40% or more. As each monitor will be different, it is necessary to verify the percentage of bandwidth being used by each monitor in the display settings interface for your graphics card. If the total percentage of bandwidth taken up by all of the connected monitors exceeds 100%, an image will not display on one or more of them. Maximum supported video resolutions and number of monitors depend on your graphics card. Check graphics card specifications to determine its capabilities.

## 2-Port DisplayPort to DVI Multi-Monitor Splitter, MST Hub, DP1.2, TAA

MODEL NUMBER: **B156-002-DVI-V2**



Displays the same image on 2 DVI monitors, extends the desktop across them, or combines both into one large monitor. Ideal for digital signage in schools, churches, conference rooms, trade shows and retail outlets.

### Description

The B156-002-DVI-V2 2-Port DisplayPort 1.2 to DVI MST Hub connects two DVI monitors to the DisplayPort output on your computer. Ideal for digital signage in schools, churches, conference rooms, trade shows, hotels and retail outlets, this hub allows you to display the same image on both monitors, extend the desktop across them, or combine both as one large monitor in video wall mode.

The B156-002-DVI-V2 is compliant with DisplayPort 1.2 and backward compatible with versions 1.1 and 1.1a with the feature set being limited to that of your equipment. It supports high-definition video resolutions up to 1080p @ 60 Hz (1920 x 1080). Expanded video resolutions are supported when displaying in video wall mode, such as 3840 x 1080 in a horizontal 1 x 2 monitor configuration or 1920 x 2160 in a vertical 2 x 1 monitor configuration. The B156-002-DVI-V2 also supports HDCP, EDID, DDC and 48-bit Deep Color (16 bits per channel), as well as DTS-HD, Dolby TrueHD and 7.1-channel surround sound audio.

This MST hub works with all operating systems. Plug-and-play convenience means no software, drivers or external power supply is needed. A built-in six-inch cable connects directly to a DisplayPort source. LEDs indicate when the monitors are receiving a signal. The B156-002-DVI-V2 complies with the Federal Trade

### Highlights

- Supports HD video resolutions up to 1080p @ 60 Hz (1920 x 1080)
- Built-in 6 in. cable connects directly to DisplayPort source
- Supports up to 48-bit Deep Color (16 bits per channel)
- Works with all operating systems
- Supports DTS-HD, Dolby TrueHD and 7.1-channel surround sound

### System Requirements

- Computer with DisplayPort 1.2-compatible graphics card (e.g. AMD Radeon with AMD Eyefinity) required for video wall mode.
- Backward compatible with most DisplayPort 1.1a equipment running current graphics drivers with feature set limited to that of your equipment. Compatibility with older graphics cards not guaranteed.
- Mac OS X does not support MST for NVIDIA and Intel Graphics Processor Units, limiting video display on connected monitors to mirror mode.
- Maximum supported video resolutions and number of monitors depend on your graphics card. Check graphics card specifications to determine its capabilities.



Agreements Act (TAA) for GSA Schedule purchases.

**Features**

**Connects 2 DVI Monitors to Your Computer's DisplayPort Output**Ideal for digital signs in schools, churches, conference rooms, trade shows and retail settings  
 Displays same image on 2 monitors simultaneously in mirror mode  
 Extends desktop across 2 monitors in extended mode  
 Combines 2 monitors into one large monitor in video wall mode  
 Built-in 6 in. cable connects directly to DisplayPort source  
 LEDs indicate when monitors are receiving a signal

**Meets the Latest Performance Standards**Supports HD video resolutions up to 1080p @ 60 Hz (1920 x 1080)  
 Expanded video resolutions are supported in video wall mode, such as 3840 x 1080 in a horizontal 1 x 2 configuration or 1920 x 2160 in a vertical 2 x 1 configuration  
 Supports HDCP, EDID and DDC  
 Supports 48-bit Deep Color (16 bits per channel)  
 Supports DTS-HD, Dolby TrueHD and 7.1-channel surround sound audio

**Easy to Use Almost Anywhere**Works with all operating systems  
 Plug and play—no software, drivers or external power supply required  
 Included USB Micro-B cable provides power

**TAA Compliant**Complies with Federal Trade Agreements Act (TAA) for GSA Schedule purchases

- Monitor(s) with DVI input.

**Package Includes**

- B156-002-DVI-V2 2-Port DisplayPort to DVI Multi-Monitor Splitter, MST Hub, DP1.2, TAA
- USB Micro-B cable, 3 ft.
- Owner's manual

**Specifications**

OVERVIEW	
UPC Code	037332193377
AC Adapter	N/A
Technology	DVI; DisplayPort
Host Connector	DISPLAYPORT (MALE)
VIDEO	
Max Supported Video Resolution	1080p @ 60 Hz (1920 x 1080)
Max Supported Color Depth	48-bit Deep Color
3D Video Supported	Yes
AUDIO	
Audio Specification	DTS-HD, Dolby TrueHD and 7.1-channel surround sound audio
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	(x2) Orange (Monitor Signal)
PHYSICAL	
Color	Black
Material of Construction	Plastic
Rackmountable	No
Shipping Dimensions (hwd / cm)	20.07 x 14.22 x 4.32
Shipping Dimensions (hwd / in.)	7.90 x 5.60 x 1.70
Shipping Weight (kg)	0.19



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Shipping Weight (lbs.)	0.41
Unit Dimensions (hwd / cm)	7.6 x 6.15 x 2.55
Unit Dimensions (hwd / in.)	3.0 x 2.4 x 1.0
Unit Dimensions (hwd / mm)	76 x 61.5 x 25.5
Unit Packaging Type	Box
Unit Weight (kg)	0.07
Unit Weight (lbs.)	0.154
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14 to 167 °F (-10 to 75 °C)
Storage Temperature Range	-4 to 176 °F (-20 to 80 °C)
Relative Humidity	0% to 85%, Non-Condensing
BTUs	14 BTU/Hr
Power Consumption (Watts)	4.1
<b>COMMUNICATIONS</b>	
EDID Compatible	Yes
<b>CONNECTIONS</b>	
Ports	2
Side A - Connector 1	DISPLAYPORT (MALE)
Side A - Connector 2	MICRO-USB B (FEMALE)
Side B - Connector 1	(2) DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Connector Plating	Nickel
Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
Displayport Specification	1.2
HDCP Specification	1.3
Driver Required	No
<b>SPECIAL FEATURES</b>	
MST Support	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	CE, FCC, RoHS, and REACH
<b>WARRANTY</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B156-002-DVI-V2](#)