

## 0.5A, 20V - 100V Schottky Barrier Rectifier

### FEATURES

- AEC-Q101 qualified available
- Low forward voltage drop
- Low power loss, high efficiency
- Guard ring for overvoltage protection
- High surge current capability
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

### APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters
- DC to DC converter

### MECHANICAL DATA

- Case: DO-204AL (DO-41)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Pure tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: Indicated by cathode band
- Weight: 0.330g (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
$I_F$	0.5	A
$V_{RRM}$	20 - 100	V
$I_{FSM}$	30	A
$T_{JMAX}$	125, 150	°C
Package	DO-204AL (DO-41)	
Configuration	Single die	



**DO-204AL (DO-41)**



ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)									
PARAMETER	SYMBOL	SR 002	SR 003	SR 004	SR 005	SR 006	SR 009	SR 010	UNIT
Marking code on the device		SR 002	SR 003	SR 004	SR 005	SR 006	SR 009	SR 010	
Repetitive peak reverse voltage	$V_{RRM}$	20	30	40	50	60	90	100	V
Reverse voltage, total rms value	$V_{R(RMS)}$	14	21	28	35	42	63	70	V
Forward current	$I_F$	0.5							A
Surge peak forward current, 8.3ms single half sine wave superimposed on rated load	$I_{FSM}$	30							A
Junction temperature	$T_J$	-55 to +125			-55 to +150				°C
Storage temperature	$T_{STG}$	-55 to +150							°C

<b>THERMAL PERFORMANCE</b>			
PARAMETER	SYMBOL	TYP	UNIT
Junction-to-ambient thermal resistance	$R_{\theta JA}$	50	°C/W

<b>ELECTRICAL SPECIFICATIONS</b> ( $T_A = 25^\circ\text{C}$ unless otherwise noted)						
PARAMETER		CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage <sup>(1)</sup>	SR002 SR003 SR004	$I_F = 0.5\text{A}, T_J = 25^\circ\text{C}$	$V_F$	-	0.55	V
	SR005 SR006			-	0.70	V
	SR009 SR010			-	0.85	V
Reverse current @ rated $V_R$ <sup>(2)</sup>	SR002 SR003 SR004 SR006	$T_J = 25^\circ\text{C}$	$I_R$	-	500	$\mu\text{A}$
	SR009 SR010	$T_J = 100^\circ\text{C}$		-	100	$\mu\text{A}$
	SR002 SR003 SR004			-	10	mA
	SR005 SR006			-	5	mA
	SR009 SR010	$T_J = 125^\circ\text{C}$		-	-	mA
	SR002 SR003 SR004			-	-	mA
	SR005 SR006			-	-	mA
	SR009 SR010			-	2	mA
	Junction capacitance	SR002 SR003 SR004		$1\text{MHz}, V_R = 4.0\text{V}$	$C_J$	110
SR005 SR006		80	-			pF
SR009 SR010		65	-			pF

**Notes:**

1. Pulse test with PW = 0.3ms
2. Pulse test with PW = 30ms

<b>ORDERING INFORMATION</b>		
ORDERING CODE <sup>(1)(2)</sup>	PACKAGE	PACKING
SR0x	DO-204AL (DO-41)	5,000 / Tape & Reel
SR0x A0G	DO-204AL (DO-41)	3,000 / Ammo box
SR0xH	DO-204AL (DO-41)	5,000 / Tape & Reel
SR0xHA0G	DO-204AL (DO-41)	3,000 / Ammo box


**Notes:**

1. "x" defines voltage from 20V (SR002) to 100V (SR010)
2. "H" means AEC-Q101 qualified


**CHARACTERISTICS CURVES**

( $T_A = 25^\circ\text{C}$  unless otherwise noted)


**Fig.1 Forward Current Derating Curve**




**Fig.2 Typical Junction Capacitance**




**Fig.3 Typical Reverse Characteristics**



**Fig.4 Typical Forward Characteristics**




**Fig.5 Maximum Non-Repetitive Forward Surge Current**



**CHARACTERISTICS CURVES**


( $T_A = 25^\circ\text{C}$  unless otherwise noted)

**Fig.6 Typical Transient Thermal Characteristics**



**PACKAGE OUTLINE DIMENSIONS**

DO-204AL (DO-41)



DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	25.40	-	1.000	-
B	4.20	5.20	0.165	0.205
C	0.71	0.86	0.028	0.034
D	2.00	2.70	0.079	0.106

**MARKING DIAGRAM**



- P/N = Marking Code
- G = Green Compound
- YWW = Date Code
- F = Factory Code

## **Notice**

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taiwan Semiconductor:](#)

[SR002 R0](#)