


Product Description

The QM14068 is a bypass switch and LNA to support wireless technology in the 6.2-8.3GHz frequency range. (UWB Channel 5 and 9.) Control is via a single bit GPIO pin.

Functional Block Diagram



1mm*1.2mm*0.54mm

Feature Overview

- Typical NF of 1.8 dB across frequency range
- Typical Gain 15 dB
- Rx gain flatness in LNA mode -1.0 to +1.0dB over max BW (500MHz)
- 1.8V typical supply voltage
- Internal DC blocking on input and output pins
- Bypass to High Gain Switching Speed 400nS

Applications

- 6.2 to 8.3 GHz Wireless Technology

Ordering Information

PART NO.	DESCRIPTION
QM14068SB	5-pc Sample Bag
QM14068SR	100-pc, 7" Reel
QM14068TR13	10,000-pc, 13" Reel
QM14068EVB	Fully Assembled EVB + Sample Bag with 5 pieces

Absolute Maximum Ratings

PARAMETER	CONDITIONS	RATING	UNITS
Storage Temperature		-40 to 150	°C
VDD		2.2	V
Absolute max input power	HG Mode, 6:1 VSWR	9	dBm
Absolute max input power	Bypass Mode, 90°C, 50 Ohms	22	dBm
Max DC voltage on RF pins		2.6	V

Recommended Operating Conditions

PARAMETER	MIN	TYP	MAX	UNITS
Supply voltage VDD	1.62	1.8	1.98	V
Control voltage High	0.75 x VDD		1.98	V
Control voltage Low		0	0.4	V
Temperature	-40	25	85	°C


Electrical Specs

Test conditions unless otherwise stated: Input and Output = 50Ω, T = 25 °C
V_{DD} = 1.8 V / 0 V.


FREQUENCY RANGE: 6200MHz TO 6800MHz					
PARAMETER	MODE	MIN	TYP	MAX	UNITS
Gain	HG		15.0		dB
	Bypass		-0.86		dB
Gain Flatness	HG		0.0		dB
Noise Figure	HG		1.85		dB
Input Return Loss	HG		12.3		dB
	Bypass		18.2		dB
Output Return Loss	HG		8.5		dB
	Bypass		19.7		dB
Vdd Current	HG		10.4		mA
	Bypass		6		nA
HG → Bypass switching time (10-90%)	HG		128		ns
Bypass → HG switching time (10-90%)	Bypass		255		ns
Input P1dB	HG		-9		dBm

FREQUENCY RANGE: 7700MHz TO 8300MHz					
PARAMETER	MODE	MIN	TYP	MAX	UNITS
Gain	HG		15.3		dB
	Bypass		-0.9		dB
Gain Flatness	HG		0.0		dB
Noise Figure	HG		1.7		dB
Input Return Loss	HG		19.7		dB
	Bypass		27		dB
Output Return Loss	HG		11.7		dB
	Bypass		24.5		dB
VDD Current	HG		10.6		mA
	Bypass		6		nA
HG → Bypass switching time (10-90%)	HG		123		ns
Bypass → HG switching time (10-90%)	Bypass		321		ns
Input P1dB	HG		-11		dBm

Input/output return loss LNA (HG) mode




Input/output return loss bypass (LG) mode



Truth Table

VDD	VCTRL	DESCRIPTION	PARAMETERS
High	1	HG Mode	LNA On
High	0	Bypass Mode	LNA Off


Pin Configuration and Description



Top View


PIN NO.	LABEL	DESCRIPTION	PIN NO.	LABEL	DESCRIPTION
1	VDD	Voltage Supply	6	LNA OUT	LNA Output
2	LNA IN	LNA Input	7	GND	Ground
3	GND	Ground	8	VCTRL	GPIO Control Line
4	GND	Ground	9	GND	Ground
5	GND	Ground			

Schematic Diagram





DESCRIPTION	DESIGNATOR	FOOTPRINT
CAP, 250pF, +/-0.25pF, 25V, C0G, 0201	C1	0201_C
CAP, 1µF 5%, 25V, C0G, 0201	C2	0201_C
RES, 0 OHM 1%, 1/20W, 0201	R1,R2	0201_R

Evaluation Board details



Mechanical Information

Package Drawing




Tape and Reel Information

Feature	Measure	Symbol	Size (mm)
Flange	Diameter	D1	330.0
	Thickness	W2	14.2
	Space Between Flange	W1	8.8
Hub	Outer Diameter	D2	102.0
	Arbor Hole Diameter	D3	13.0
	Key Slit Width	B	2.0
	Key Slit Diameter	D4	20.2
Cavity	Length	Ao	1.17
	Width	Bo	1.40
	Depth	Ko	0.65
	Pitch	P1	4.0
Centerline Distance	Cavity to Perforation (Length)	P2	2.0
	Cavity to Perforation (Width)	P3	3.5
Carrier Tape	Width	W	8.0

(Unless otherwise specified, all dimension tolerances per EIA-481)

Marking Diagram



Handling Precaution

PARAMETER	RATING	STANDARD
ESD – Human Body Model (HBM)	Class 1C	ANSI/ESD/JEDEC JS-001
ESD – Charged Device Model (CDM)	Class C3	ANSI/ESDA/JEDEC JS-002
MSL – Moisture Sensitivity Level	Level 3	IPC/JEDEC J-STD-020



Caution!
ESD sensitive device

Solderability

Compatible with both lead-free (260 °C max. reflow temperature) and tin/lead (245 °C max. reflow temperature) soldering processes.

Package lead plating: Electrolytic plated Au over Ni

RoHS Compliance

This part is compliant with the 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment), as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Lead free
- Halogen Free (Chlorine, Bromine)
- Antimony Free
- TBBP-A (C₁₅H₁₂Br₄O₂) Free
- SVHC Free

Revision History

Data sheet Revision Code	Comments
A	Initial Release
B	Update Mechanical Drawing
C	Electrical Performance update
D	Updated Package Dimensions
E	Updated ESD rating, pin labelling
F	Updated MSL to Level 3 and pin number update
G	Updated Control Voltages and Ordering Information
H	Updated AMR, Electrical Specs, and EVB Information
I	Updated AMR, Operating Conditions, and Handling Precautions
J	Added Tape and Reel Information
K	Removed "Preliminary" Watermark and updated AMR

Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

Web: www.qorvo.com

Tel: 1-844-890-8163

Email: customer.support@qorvo.com

Important Notice

The information contained herein is believed to be reliable; however, Qorvo makes no warranties regarding the information contained herein and assumes no responsibility or liability whatsoever for the use of the information contained herein. All information contained herein is subject to change without notice. Customers should obtain and verify the latest relevant information before placing orders for Qorvo products. The information contained herein or any use of such information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights, whether with regard to such information itself or anything described by such information. **THIS INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.**

Without limiting the generality of the foregoing, Qorvo products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death.

Copyright 2016 © Qorvo, Inc. | Qorvo is a registered trademark of Qorvo, Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Qorvo:](#)

[QM14068TR13](#) [QM14068TR7](#) [QM14068SB](#) [QM14068SR](#)