





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/8/05	
A		REVISED DIM.	8/29/11	



PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 20
A = .100 [2.54] x No. of Positions
B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES	HOLES	DATE	TITLE	SIZE	PART NO.	REV.	
.X ± .10	ØXX ± .10		.100 [2.54] LOCKING HEADER	X	LHS-XX-TRA	A	
.XX ± .020	ØXXX ± .015		SHORT BACK, RIGHT ANGLE, PCB				
.XXX ± .015	ØXXX ± .010						
APPROVALS	DATE						
DRAWN	SS	4/8/05					
CHECKED							
APPROVED							
REF:	S00016T	SCALE: NTS	SHEET 1 OF 1				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[LHS-02-TRA](#) [LHS-05-TRA](#) [LHS-09-TRA](#) [LHS-06-TRA](#) [LHS-11-TRA](#) [LHS-08-TRA](#) [LHS-10-TRA](#) [LHS-07-TRA](#)
[LHS-04-TRA](#) [LHS-03-TRA](#) [LHS-12-TRA](#)