
Series 9177





The 917X series of surface mount Insulation Displacement Connectors (IDC) were developed to meet the harsh automotive and industrial market applications for connecting individual wires directly to a PCB ranging from 14 AWG to 28 AWG. This industry proven contact system has been tested to automotive levels of shock, vibration, and temperature cycling to prove their reliability and robustness. The simplicity of inserting a wire into the connector with a small tool allows a wide range of devices to be connected to the PCB without soldering. In SSL applications specifically, these connectors are used to bring power and signal onto the PCB or are used to daisy chain multiple boards together in a long string. While the IDC contact provides a gas-tight connection to conductor of the wire, the housing has been designed to grab the insulation of the wire to provide a positive strain relief even in the harshest conditions. In case of repair, the wires can be removed and replace up to three times.

The 9177 series accepts 14 AWG to 20 AWG wires with an insulation diameter ranging from 2.75mm to 4.25mm. These dual contact connectors support a 15 amp current rating with two large SMT solder tails per wire to provide maximum stability on the PCB. Available in 1p-3p configuration, these connectors can be end stackable for higher pin counts.

APPLICATIONS

- Connecting discrete wire components directly to the PCB
- Bringing power and signals onto a PCB
- Daisy chaining PCB's together to create a continuous string of boards
- Application Notes: refer to 201-01-124

FEATURES AND BENEFITS

- IDC contact provides a gas-tight connection to the PCB for long term reliability
- Connector housing captures the wire insulation for positive strain relief
- Tested to automotive levels on shock, vibration and temperature cycling for reliability
- Low and high volume assembly tools to match production volumes
- Reduced total applied cost versus solder or crimp processes
- High temperature insulator capable to 260°C reflow soldering processes

ELECTRICAL

• Current Rating: 15 Amp / Contact

Voltage Rating: 600 VAC

ENVIRONMENTAL

• Operating Temperature: -40°C to +125°C

MECHANICAL

• Insulator Material: Nylon 46: UL94V0


• Contact Material: Phosphor Bronze

• Plating: Tin over Nickel


• Durability: 3 Cycles

HOW TO ORDER 9177

00



00X



00X






Certification: UL File #E320991



Series 9177





14-20 AWG 1 WAY IDC CONNECTOR



NOTES:


- 1. CONNECTOR FOR IDC WIRE TO BOARD CONNECTION.
- 2. CONTACT MATERIAL: PHOSPHORE BRONZE. INSULATION MATERIAL: HIGH TEMPERATURE NYLON 46. COLOR REFER TO PAGE 61.
- 3. CONNECTOR DESIGNED TO ACCEPT BETWEEN 14 AND 20 GAUGE STRANDED WIRE.
- 4. ALL DIMENSIONS FOR REFERENCE UNLESS OTHERWISE STATED.
- 5. FOR FULL PRODUCT SPECIFICATION REFER TO ELCO SPEC 201-01-109.
- 6. FOR PCB SPACE RESTRICTED BY ASSEMBLY TOOLING REFER TO PAGE 65.






Code	Accepted Wire Gauge	Α	Wire Insulation	В
001	14 Gauge Stranded	1.10	Ø 4.25 max	4.25
012	16 Gauge Stranded	0.82	Ø 3.50 max	3.50
022	18 Gauge Stranded	0.72	Ø 3.50 max	3.50
033	20 Gauge Stranded	0.60	Ø 2.75 max	2.75






SMT PCB LAYOUT


PURE TIN PADS



PACKING DETAILS

REEL QTY	400
LEADER	500MM
TRAILER	400MM
REEL/BOX	4
PACK QTY	1600






Series 9177





14-20 AWG 2 WAY IDC CONNECTOR




NOTES:


- 1. CONNECTOR FOR IDC WIRE TO BOARD CONNECTION.
- 2. CONTACT MATERIAL: PHOSPHORE BRONZE. INSULATION MATERIAL: HIGH TEMPERATURE NYLON 46. COLOR REFER TO PAGE 61.
- 3. CONNECTOR DESIGNED TO ACCEPT BETWEEN 14 AND 20 GAUGE STRANDED WIRE.
- 4. ALL DIMENSIONS FOR REFERENCE UNLESS OTHERWISE STATED.
- 5. FOR FULL PRODUCT SPECIFICATION REFER TO ELCO SPEC 201-01-109.
- 6. FOR PCB SPACE RESTRICTED BY ASSEMBLY TOOLING REFER TO PAGE 65.






Code	Accepted Wire Gauge	Α	Wire Insulation	В
001	14 Gauge Stranded	1.10	Ø 4.25 max	4.25
012	16 Gauge Stranded	0.82	Ø 3.50 max	3.50
022	18 Gauge Stranded	0.72	Ø 3.50 max	3.50
033	20 Gauge Stranded	0.60	Ø 2.75 max	2.75






SMT PCB LAYOUT


PURE TIN PADS



PACKING DETAILS

REEL QTY	400
LEADER	500MM
TRAILER	400MM
REEL/BOX	4
PACK QTY	1600






CONNECTOR OUTLINE-







14-20 AWG 3 WAY IDC CONNECTOR



16.00 REF

Series 9177




INSERTION TOOLING - REQUIRES HAND PRESS WITH FLAT ROCK PLATES

1 WAY







HIGH PRODUCTION

No. of Ways	Max Insulation Dia (AWG)	Tool Part Number
	4.25 (14)	06 9177 7017 01 001
1	3.50 (16-18)	06 9177 7017 02 001
	2.75 (20)	06 9177 7017 03 001
	4.25 (14)	06 9177 7017 01 002
2	3.50 (16-18)	06 9177 7017 02 002
	2.75 (20)	06 9177 7017 03 002
	4.25 (14)	06 9177 7017 01 003
3	3.50 (16-18)	06 9177 7017 02 003
	2.75 (20)	06 9177 7017 03 003

MEDIUM PRODUCTION Plastic

No. of Ways	Max Insulation Dia (AWG)	Tool Part Number
	4.25 (14)	06 9177 7016 01 001
1	3.50 (16-18)	06 9177 7016 02 001
	2.75 (20)	06 9177 7016 03 001
	4.25 (14)	06 9177 7016 01 002
2	3.50 (16-18)	06 9177 7016 02 002
	2.75 (20)	06 9177 7016 03 002
	4.25 (14)	06 9177 7016 01 003
3	3.50 (16-18)	06 9177 7016 02 003
	2.75 (20)	06 9177 7016 03 003


The assembly tooling restricts the available space/component heights on the PCB.

For details see below.

NOTES


- 1. ALL DIMENSIONS FOR REFERENCE DIMENSIONS.
- 2. MAXIMUM COMPONENT HEIGHT 0.80MM IN THIS AREA.
- 3. MAXIMUM COMPONENT HEIGHT 11.00 MM IN THIS AREA.
- 4. THE SAME RESTRICTIONS APPLY TO ALL WIRE INSULATION DIAMETERS.


INSERTION TOOLING - PCB RESTRICTED AREAS FOR ASSEMBLY TOOLING


























Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AVX:

0691777016003001 069177500001000