

Preliminary Specification

Note: This is a draft specification and may change.

Drawing No.	TKY1D-H2-23022-00 [14]
Issued Date.	January 23, 2023

TO: Mouser

Note: In case of specification change, KYOCERA Part Number also will be changed.

Product Name	Temperature Compensated Crystal Oscillator
Product Model	KT1612A
Frequency	48.0MHz
Customer Part Number	_____
Customer Specification Number	_____
KYOCERA Part Number	KT1612A48000ZAY18NAG
Remarks	RoHS Compliant, MSL=1

Customer Acceptance

Accept Signature	Accept Date	
	Department	
	Person in charge	

Seller
KYOCERA Corporation
Corporate Electronic Components Group
Electronic Components Sales Division
6 Takeda Tobadono-cho, Fushimi-ku, Kyoto
612-8501 Japan
TEL. No. 075-604-3500
FAX. No. 075-604-3501

Manufacturer
KYOCERA Corporation
Corporate Electronic Components Group
RF Devices Division
Yamagata higashine Plant
5850, Higashine-koh, Higashine-shi, Yamagata
999-3701 Japan
TEL. No. 0237-43-5611
FAX. No. 0237-43-5615

Design Department	Quality Assurance	Approved by	Examined by	Examined by	Written by
RF Devices Engineering Department Crystal Components Application Engineering Section	Y. Kakuta 	W. Muraoka 	Y. Hosoya 	F. Horie 	C. Nitoube 

KYOCERA Corporation

1. Purpose and scope

This document contains specification related to CRYSTAL OSCILLATOR model
KT1612A48000ZAY18NAG for Mouser

2. Nominal condition

	Item	MIN.	TYP.	MAX	Unit	Conditions
1	Operating temperature range	-40	---	+105	deg.C	
2	Storage temperature range	-40	---	+105	deg.C	
3	Nominal frequency	---	48.0	---	MHz	
4	Supply voltage	1.68	---	3.63	V	
5	Absolute maximum rating voltage (Supply voltage)	-0.6	---	+4.6	V	
	Absolute maximum rating voltage (Control voltage)	-0.6	---	Vcc+0.6	V	
6	Load impedance	9	10	11	kohm	
		9	10	11	pF	
7	Output signal condition	---	Clipped sine	---	---	

3. Electrical characteristics (T.B.D.)

Ta= -40 deg.C to +105 deg.C, Vcc=1.68V to 3.63V,
1pin =Enable/Disable Control , Load=10kohm//10pF


	Item	MIN.	TYP.	MAX	Unit	Conditions	Remarks
1	Temp characteristics	-5.0	---	+5.0	$\times 10^{-6}$	Ta=-40 to +85deg.C	Referenced to the mid point between minimum and maximum frequency value over the specified temperature range (Ta=-40 to +85deg.C)
		-10.0	---	+10.0	$\times 10^{-6}$	Ta=+85 to +105deg.C	Referenced to the mid point between minimum and maximum frequency value over the specified temperature range (Ta=+85 to +105deg.C)
2	Voltage characteristics	-0.2	---	+0.2	$\times 10^{-6}$	Vcc+/-5%	Vcc=1.68V+5%min, 3.63V-5%max
3	Load characteristics	-0.3	---	+0.3	$\times 10^{-6}$	10kohm+/-10%, 10pF+/-10%	
4	Aging characteristics	-1.0	---	+1.0	$\times 10^{-6}/Y$	1year	at 25+/-2 deg.C
		-3.0	---	+3.0	$\times 10^{-6}/5Y$	5years	
5	Frequency tolerance	-1.5	---	+1.5	$\times 10^{-6}$	After 2 times reflow soldering	at 25+/-2 deg.C
6	Current	---	---	3.0	mA		
7	Output voltage	0.8	0.95	1.2	Vp-p		
8	Harmonics	---	---	-8.0	dBc		
9	Start up time	---	0.2	1.0	msec	90% of final output amplitude	
		---	0.4	1.0	msec	Within +/-5.0ppm	
10	Duty	45	---	55	%	@GND	
11	Phase noise	---	-60	---	dBc/Hz	@ 1Hz offset	at 25+/-2 deg.C
		---	-88	---	dBc/Hz	@ 10Hz offset	
		---	-114	---	dBc/Hz	@ 100Hz offset	
		---	-136	---	dBc/Hz	@ 1kHz offset	
		---	-156	---	dBc/Hz	@ 10kHz offset	
		---	-164	---	dBc/Hz	@ 100kHz offset	
		---	-165	---	dBc/Hz	@ 1MHz offset	

12	Enable / Disable	80%Vcc	---	---	V	Enable Active Hi	
		---	---	20%Vcc	V	Disable Active Low	
13	Current of Disable	---	---	10.0	uA		

Note. There is possibility to change standard values of electrical characteristics.


4. Circuit

Bypass Capacitor and DC- Blocking Capacitor do not build in this TCXO.
So, Bypass Capacitor and DC- Blocking Capacitor are attached outside and please use it.
And these Capacitor should be placed as close as possible to the pin(No.3 and No.4).



5. Test circuit

*Load 10kohm//10pF contains the internal impedance of FET probe.



6. Environment mechanical characteristics

	Item	Conditions	Remark
1	High temperature storage	Ta=+85deg.C, judge on 240H storage	It must be met to the characteristics Judging criterion. Measurement shall be taken at room ambient within 2 to 24hours after each test.
2	Low temperature storage	Ta=-40deg.C, judge on 240H storage	
3	High temperature and high humidity storage	Ta=+85deg.C, RH=85%RH, judge on 240H storage	
4	Temperature cycle test	Ta=-40 to +85deg.C 30min. each 10cycles	
5	Drop test	A test piece (100g) made of Teflon is dropped 3cycles (1cycle: 6 directions) from the height of 150cm on hard board	
6	Vibration test	10 to 55 to 10Hz 1.5mm constant amplitude 1min. period X, Y, Z direction each 2H total 6H.	
7	Solder heat test	All terminal electrode shall be soldered at temperature of 350+/-5deg.C for 3+/-1sec. using a soldering iron.	
8	Solderability	Dip each of terminal electrode into 230+/-5deg.C solder pod for 5+/-0.5sec. after close, the test area of loads surfaces must be covered loads 90% by solder.	
9	Reflow soldering	Reflow soldering at 2 times.	

Normal Condition: Temperature 25+/-2deg.C
Humidity 30 to 70%RH

Judge

Item	Specification
At 25deg.C frequency	+/-2.0ppm max(Before and After)

7. Reflow profile

7-1. Preheat: $180 \pm 0/-10^{\circ}\text{C}$, 120sec (max)7-2. Peak Temperature: $260 \pm 0/-10^{\circ}\text{C}$, 10sec (max)

7-3. PC-Board


Material : FR-4

Size : 140mm*110mm


Thickness : $t=0.8\text{mm}$

7-4. Condition of Measurement Temperature: Surface of PC-BOARD

Reflow Soldering Condition





8. Marking contents



*Laser Marking

	Contents	Example
1	Pin-1 identifier	○
2	Control Code1	K
3	Control Code2	XX
4	Monthly Code	A3 *The 2023 January B3 *The 2023 February
5	Control Code3	X *Specification Code (Blank or “—” mark)


9. Dimensions



Note1

Terminal Coplanarity: 60um max

Note2


Electrode: Mo + Ni 2.0 to 8.89um
+ Au 0.3 to 1.0um

Enable/Disable Function	
#1 Input	#3 Output
Open	Oscillation
"H" Level	Oscillation
"L" Level	High Z

	Pin Connection
# 1 pin	Enable / Disable
# 2 pin	GND
# 3 pin	Output
# 4 pin	Vcc


Unit: mm

Recommended Land Pattern



10. Tape & Reel

10-1. Tape specification



10-1-1. Carrier Tape material: PS Included Carbon

10-1-2. #1pin Mark is positioned on right side against the direction of feed.


Unit: mm

Symbol	A	B	C	D	E
Dimension	1.45+/-0.1	1.85+/-0.1	8.0+/-0.2	3.5+/-0.05	1.75+/-0.1

Symbol	F	G	H	I	J
Dimension	4.0+/-0.1	2.0+/-0.05	4.0+/-0.05	Φ1.5+0.1/-0	Φ0.5+0.05

Symbol	K	t
Dimension	0.65+/-0.05	0.20+/-0.05

10-2. Reel specification



Unit: mm


10-2-1. Reel material: PS Included Carbon

10-2-2. Reel unit: 18,000pcs max. /1Reel

10-3.Packing

10-3-1.Trailer & Leader

As for the trailer and leader of taping, there are empty pockets as following drawing.
Sprocket hole is positioned on upper side against the direction of feed.
No missing components, excluding empty place.



10-4. Shipping label

Following item shall be listed on reel, bag and box.

“Customer’s name”, “Parts No”, “Lot No”, “Quantity”, “Order No”, “Date of manufacture”

The form of the label conforms to JEITA standard pattern C-3.

11. Top Cover breaking and peeling force


11-1. Reel Angle: 165 to 180deg

11-2. Tape Break Force: 10N min

11-3. Top Cover Tape Strength: 10N min

11-4. Top Cover Tape Peel Force: 0.1 to 1.0N

11-5. Top Cover Tape Peel Speed: 300+/-10mm / minute



12. Notice

12-1. Please use soldering iron and the spot heater within the range of a solder heat test condition.

12-2. Units should be stored in a dry environment keeping away from the sun.

12-3. Don't leave units in High-temperature and High-humidity environment due to terminal solderability.

(Please keep 0 to 40deg.C and 30 to 70%RH for recommendable storage condition)

12-4. The term of a guarantee of taping packing is 6 months. (0 deg.C to 40 deg.C,RH30% to 70%)

12-5. Disapprove of washing.

12-6. Please contact us if you are considering molding by transfer or compression.

12-7. Unless we receive request for modification within 1 month from the issue date of this KC specification sheet, we will supply products according to this specification.

Also, if you'd like to modify specification of order, which has been placed with delivery within 1 month from the issue data of this specification sheet, we would like to discuss with you separately.

12-8. This product is intended to be used for general electronic equipment (information equipment, communication equipment, audio visual equipment, measuring equipment, home electric appliances, etc.). Devices and systems that are required for special quality and reliability, and whose failure or malfunction directly threatens human lives or that may cause harm to the human body (traffic equipment, safety equipment, aircraft and space, nuclear power control, life support equipment Please contact us in advance in case of using it for medical equipment including medical equipment etc.). It is not intended for use in applications directly related to basic driving functions (run, turn, or stop), collision safety, or driving safety in traffic equipment. In the unlikely event that this product is used for any of these purposes, our company shall not be liable for any damages resulting from such use.

12-9. In no event shall the company be liable for any product failure resulting from an inappropriate handling or operation of the product beyond the scope of its guarantee.

12-10. Information contained in this specification must not be quoted, reproduced or used for other purposes including processing either in part or in full without obtaining prior approval from the company.

12-11. Please keep it at the place that was the ESD protective.

Human model 1.5kohm 100pF : +/-1000V

Machine model 0kohm 200pF : +/-200V

13. Production place

13-1. Manufacturer

KYOCERA Corporation.

13-2. The site of the Factory

5850 Higashine-Koh, Higashine-shi, Yamagata, 999-3701, Japan
 158-15 Chuo-kogyo-danchi, Sagae-shi, Yamagata, 991-0061, Japan
 115-1 Jinmachi-aza-nishihara, Higashine-shi, Yamagata, 999-3761, Japan

14. Quality guarantee

In case when Kyocera Corporation rooted failure occurred within 1year after its delivery, substitute product will be arranged based on discussion. Quality guarantee of product after 1year of its delivery is waived.

15. Parts Numbering Guide

KT1612A 48000 Z A Y 18 N AG
 A B C D E F G H

- A. Series (1.6x1.2 SMD KT1612A)
- B. Frequency (48.0MHz)
- C. Frequency temperature accuracy (Z: Special specification)
- D. Minimum temperature range (A: -40degC)
- E. Maximum temperature range (Y: +105deg.C)
- F. Supply voltage (18:1.8 V)
- G. Control voltage stability (N: Enable/Disable)
- H. Customer special model Suffix