

Features

- Frequency range : 32.768 kHz
- DIP : Cylinder type
- External dimensions (mm)
 Φ : 2.0 x L : 6.2
- RoHS compliant & Pb free


Applications

- Watch, Clock
- Real-time clock (RTC)
- Security devices
- Consumer products


Electrical Characteristics

Item	Symbol	QT26	Conditions
Nominal Frequency	f_0	32.768 kHz	
Frequency Tolerance	$\Delta f/f_0$	$\pm 5\text{ppm}$, $\pm 10\text{ppm}$, $\pm 20\text{ppm}$	at 25°C
Load Capacitance	C_L	6pF, 7pF, 9pF, 12.5pF	
Operating Temperature Range	T_{OTR}	-20°C ~ +70°C	
Storage Temperature Range	T_{STR}	-40°C ~ +85°C	
Turnover Temperature	T_M	25°C $\pm$ 5°C	
Temperature Coefficient	β	-0.034 $\pm$ 0.006ppm/°C ²	
Motional Resistance (ESR)	R_1	35 k Ω Max.	at 25°C
Drive Level	D_L	1 μ W Max.	
Aging	$\Delta f/f_0$	± 3 ppm Max.	at 25°C $\pm$ 3°C, first year
Shunt Capacitance	C_0	1.2 pF Typ.	

Dimensions



Ordering Information



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

[QT26-32.768KDZB-B](#) [QT26-32.768KDZF-B](#) [QT26-32.768KEZB-B](#) [QT26-32.768KEZF-B](#) [QT26-32.768KHZB-B](#)
[QT26-32.768KHZF-B](#) [QT26-32.768KEZC-B](#) [QT26-32.768KDZC-B](#) [QT26-32.768KEZY-B](#) [QT26-32.768KDZY-B](#)