

Features

- Frequency range : 10MHz to 52MHz
- SMD seam sealing ceramic package
- Supply voltage : 3.3V
- Free Run Stability for 20 Years : ± 4.6 ppm (Stratum 3)
- CMOS output
- Voltage control function available
- External dimensions (mm)
L : 7.0 x W : 5.0 x H : 2.0
- RoHS compliant & Pb free

Applications

- Wireless communications, Smallcell, Base station
- Precise timing & synchronization network (IEEE1588, Sync.E), OTN, PTN, Switch
- Test and measurement equipment
- Smart grid
- Stratum 3


Electrical Characteristics

Item		QTS750C	Conditions
Nominal Frequency Range (F_0)		10MHz ~ 52MHz	
Frequency Tolerance (F_{tol})		± 2.0 ppm Max.	Note [1]
Frequency Stability	vs Temperature	$\pm 0.1, \pm 0.28, \pm 0.5, \pm 1.0$ ppm	Note [2]
	vs Load	± 0.1 ppm Max.	Load $\pm 5\%$
	vs Supply Voltage	± 0.1 ppm Max.	$V_{DD} \pm 5\%$
Operating Temperature Range (T_{OTR})		$-40^\circ\text{C} \sim +85^\circ\text{C}$	
Supply Voltage (V_{DD})		3.3V	
Current Consumption (I_{DD})		5.0 mA Max.	
Output Type		CMOS	
Output Load		15 pF	
Output Voltage High (V_{OH})		90% V_{DD} Min.	
Output Voltage Low (V_{OL})		10% V_{DD} Max.	
Start-up Time		2.5 ms Max.	
Auto Frequency Control (AFC) Range		± 5 ppm ~ ± 16 ppm	VCTCXO, optional $V_C = 1.5 \pm 1.0\text{V}$
Phase Noise		-135 dBc/Hz Typ.	at 1kHz offset
Aging (F_{aging})		± 1 ppm Max.	at 25°C , first year
24 Hours Holdover Stability		± 40 ppb Max.	Note [3]
Free Run Stability for 20 Years		± 4.6 ppm Max.	Note [4]
Storage Temperature Range (T_{STR})		$-55^\circ\text{C} \sim +125^\circ\text{C}$	

Notes:

- [1] Refer to nominal frequency, operation after 2 times of reflow at 25°C.
- [2] Refer to $(F_{max} + F_{min})/2$.
- [3] 24 hours at constant temperature after 48 hours operation
- [4] Inclusive of initial tolerance at 25°C, variations over temperature, supply voltage, load, reflow soldering and aging for 20 years.

Dimensions




(Unit: mm)

Pin function

Pin	Function	
	TCXO	VCTCXO
Pin 1	GND or NC	AFC
Pin 2	GND	
Pin 3	OUTPUT	
Pin 4	V_{DD}	

Recommended pad layout



Ordering Information

QTS750C - 19.200M B P - T

Frequency in Hz

Please contact us for available frequencies

Supply Voltage

B 3.3 V


Packaging Method

T Tape & Reel

Frequency Stability (over Temp.)

I	± 1.0 ppm	(-40°C ~ +85°C), TCXO
F	± 0.5 ppm	(-40°C ~ +85°C), VCTCXO
G	± 0.5 ppm	(-40°C ~ +85°C), TCXO
O	± 0.28 ppm	(-40°C ~ +85°C), VCTCXO
P	± 0.28 ppm	(-40°C ~ +85°C), TCXO
T	± 0.1 ppm	(-40°C ~ +85°C), VCTCXO
U	± 0.1 ppm	(-40°C ~ +85°C), TCXO

Packing




DIMENSIONS	A	B	C	D	E	L	L1	W	W1
	2.00	7.90	5.45	8.00	16.0	180.0	13.0	20.5	16.0

(Unit: mm)

Reflow Profile

Solder melting point : $220^{\circ}\text{C} \pm 10^{\circ}\text{C}$, 60 sec. Min., 200 sec. Max.

Peak temperature : $260^{\circ}\text{C} \pm 10^{\circ}\text{C}$, 10 sec. Min., 30 sec. Max.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

[QTS750C-12.800MBP-T](#) [QTS750C-19.440MBP-T](#) [QTS750C-26.000MBP-T](#) [QTS750C-27.000MBP-T](#) [QTS750C-12.800MBG-T](#) [QTS750C-24.576MBG-T](#) [QTS750C-38.400MBG-T](#) [QTS750C-20.000MBO-T](#) [QTS750C-50.000MBG-T](#) [QTS750C-15.360MBG-T](#) [QTS750C-19.440MBG-T](#) [QTS750C-38.880MBO-T](#) [QTS750C-20.000MBG-T](#) [QTS750C-20.000MBP-T](#) [QTS750C-12.800MBF-T](#) [QTS750C-12.800MBO-T](#) [QTS750C-38.400MBF-T](#) [QTS750C-38.400MBO-T](#) [QTS750C-13.000MBG-T](#) [QTS750C-25.000MBP-T](#) [QTS750C-40.000MBP-T](#) [QTS750C-19.200MBP-T](#) [QTS750C-30.000MBG-T](#) [QTS750C-40.000MBG-T](#) [QTS750C-20.000MBF-T](#) [QTS750C-32.000MBO-T](#) [QTS750C-51.200MBG-T](#) [QTS750C-19.200MBO-T](#) [QTS750C-19.440MBF-T](#) [QTS750C-30.720MBG-T](#) [QTS750C-49.152MBG-T](#) [QTS750C-24.576MBP-T](#) [QTS750C-32.000MBF-T](#) [QTS750C-38.880MBG-T](#) [QTS750C-48.000MBG-T](#) [QTS750C-19.200MBG-T](#) [QTS750C-38.880MBP-T](#) [QTS750C-45.1584MBG-T](#) [QTS750C-19.440MBO-T](#) [QTS750C-38.880MBF-T](#) [QTS750C-19.200MBF-T](#) [QTS750C-26.000MBG-T](#) [QTS750C-10.000MBG-T](#) [QTS750C-25.000MBG-T](#) [QTS750C-10.000MBP-T](#) [QTS750C-54.000MBG-T](#) [QTS750C-25.000MBF-T](#) [QTS750C-25.000MBO-T](#) [QTS750C-96.000MBG-T](#)