

SPECIFICATION CONTROL DRAWING

55A6373


TITLE TWO CONDUCTOR CABLE, SILVER-COATED HIGH STRENGTH
COPPER ALLOY, UNSHIELDED, UNJACKETED, 600 VOLT

Date 5-14-93

Revision B

This specification sheet forms a part of the latest issue of Raychem Specification 55A.

COMPONENT WIRES - 55A6359



CABLE CONSTRUCTION DETAILS				
PART NUMBER	CONDUCTOR SIZE (AWG)	OUTSIDE DIAMETER (inches)		MAXIMUM WEIGHT (lbs/1000 ft.)
		NOMINAL	MAXIMUM	
55A6373-28-*	28	.054	.058	1.9
55A6373-26-*	26	.064	.068	2.8
55A6373-24-*	24	.074	.078	4.0
55A6373-22-*	22	.086	.090	5.8

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

- TEMPERATURE RATING: 200°C
Maximum continuous conductor temperature
- VOLTAGE RATING: 600 volts (rms)
- * BLOCKING: 200 ± 3°C for 6 hours
 - DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz
 - * FLAMMABILITY:
Procedure 1, 3 seconds (maximum); 3 inch (maximum); no flaming of facial tissue

PART NUMBER:
The "*" in the part numbers above shall be replaced by a color code designator with a slash separating the component wire colors.
Example: AWG 28, white and black component wires: 55A6373-28-9/0

* Qualification Test

NOTE: Nominal values are for information only.
Nominal values are not requirements.

COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-881.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

Raychem

Raychem Corporation
300 Constitution Drive, Menlo Park, California 94025
(415) 361 3333 TWX 910 373 1728

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55A6373-22-5/59CS2063](#) [55A6373-26-0/09CS2063](#)