


**MECHANICAL DATA**

Dimensions in mm.

**GOLD METALLISED  
MULTI-PURPOSE SILICON  
DMOS RF FET  
5W – 12.5V – 1GHz  
SINGLE ENDED**



**F-0127 PACKAGE**

- PIN 1 – SOURCE
- PIN 2 – DRAIN
- PIN 3 – DRAIN
- PIN 4 – SOURCE
- PIN 5 – SOURCE
- PIN 6 – GATE
- PIN 7 – GATE
- PIN 8 – SOURCE

**FEATURES**

- SIMPLIFIED AMPLIFIER DESIGN
- SUITABLE FOR BROAD BAND APPLICATIONS
- VERY LOW  $C_{rss}$
- SIMPLE BIAS CIRCUITS
- LOW NOISE
- HIGH GAIN – 10 dB MINIMUM

**Ceramic Material: Alumina.**  
Parts can also be supplied with AlN or BeO for improved thermal resistance.  
Contact Semelab for details.

**APPLICATIONS**

- HF/VHF/UHF COMMUNICATIONS  
from 1 MHz to 2 GHz

**ABSOLUTE MAXIMUM RATINGS** ( $T_{case} = 25^{\circ}C$  unless otherwise stated)

$P_D$	Power Dissipation	17.5W
$BV_{DSS}$	Drain – Source Breakdown Voltage	40V
$BV_{GSS}$	Gate – Source Breakdown Voltage	±20V
$I_{D(sat)}$	Drain Current	4A
$T_{stg}$	Storage Temperature	-65 to 150°C
$T_j$	Maximum Operating Junction Temperature	200°C

Semelab Plc reserves the right to change test conditions, parameter limits and package dimensions without notice. Information furnished by Semelab is believed to be both accurate and reliable at the time of going to press. However Semelab assumes no responsibility for any errors or omissions discovered in its use. Semelab encourages customers to verify that datasheets are current before placing orders.

## ELECTRICAL CHARACTERISTICS (T<sub>case</sub> = 25°C unless otherwise stated)

Parameter	Test Conditions	Min.	Typ.	Max.	Unit
BV <sub>DSS</sub> Drain-Source Breakdown Voltage	V <sub>GS</sub> = 0 I <sub>D</sub> = 10mA	40			V
I <sub>DSS</sub> Zero Gate Voltage Drain Current	V <sub>DS</sub> = 12.5V V <sub>GS</sub> = 0			2	mA
I <sub>GSS</sub> Gate Leakage Current	V <sub>GS</sub> = 20V V <sub>DS</sub> = 0			1	μA
V <sub>GS(th)</sub> Gate Threshold Voltage*	I <sub>D</sub> = 10mA V <sub>DS</sub> = V <sub>GS</sub>	0.5		7	V
g <sub>fs</sub> Forward Transconductance*	V <sub>DS</sub> = 10V I <sub>D</sub> = 0.4A	0.36			S
G <sub>PS</sub> Common Source Power Gain	P <sub>O</sub> = 5W	10			dB
η Drain Efficiency	V <sub>DS</sub> = 12.5V I <sub>DQ</sub> = 0.2A	40			%
VSWR Load Mismatch Tolerance	f = 1GHz	20:1			—
C <sub>iss</sub> Input Capacitance	V <sub>DS</sub> = 0V V <sub>GS</sub> = -5V f = 1MHz			24	pF
C <sub>oss</sub> Output Capacitance	V <sub>DS</sub> = 12.5V V <sub>GS</sub> = 0 f = 1MHz			20	pF
C <sub>rss</sub> Reverse Transfer Capacitance	V <sub>DS</sub> = 12.5V V <sub>GS</sub> = 0 f = 1MHz			2	pF

\* Pulse Test: Pulse Duration = 300 μs , Duty Cycle ≤ 2%

## THERMAL DATA

R <sub>THj-case</sub>	Thermal Resistance Junction – Case	Max. 6°C / W
-----------------------	------------------------------------	--------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TT Electronics:](#)

[D2230UK](#)