



RECOMMENDED HOLE LAYOUT

- 1 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- 2 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 4 HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK. POST: COPPER ALLOY
- 5 FINISH: 0.00254-0.00508 [0.000100-.000200] MATTE TIN-LEAD OVER 0.00127 [0.000050] NICKEL ENTIRE POST.
- 6 FINISH: 0.00254-0.00508 [0.000100-.000200] MATTE TIN OVER 0.00127 [0.000050] NICKEL ENTIRE POST.

PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER
6	101.19 [3.984]	99.06 [3.900]	39	40	9-146456-0
6	98.65 [3.884]	96.52 [3.800]	38	39	8-146456-9
6	96.1 [3.784]	93.98 [3.700]	37	38	8-146456-8
6	93.57 [3.684]	91.44 [3.600]	36	37	8-146456-7
6	91.03 [3.584]	88.90 [3.500]	35	36	8-146456-6
6	88.49 [3.484]	86.36 [3.400]	34	35	8-146456-5
6	85.95 [3.384]	83.82 [3.300]	33	34	8-146456-4
6	83.41 [3.284]	81.28 [3.200]	32	33	8-146456-3
6	80.87 [3.184]	78.74 [3.100]	31	32	8-146456-2
6	78.33 [3.084]	76.20 [3.000]	30	31	8-146456-1
6	75.79 [2.984]	73.66 [2.900]	29	30	8-146456-0
6	73.25 [2.884]	71.12 [2.800]	28	29	7-146456-9
6	70.71 [2.784]	68.58 [2.700]	27	28	7-146456-8
6	68.17 [2.684]	66.04 [2.600]	26	27	7-146456-7
6	65.63 [2.584]	63.50 [2.500]	25	26	7-146456-6
6	63.09 [2.484]	60.96 [2.400]	24	25	7-146456-5
6	60.55 [2.384]	58.42 [2.300]	23	24	7-146456-4
6	58.01 [2.284]	55.88 [2.200]	22	23	7-146456-3
6	55.47 [2.184]	53.34 [2.100]	21	22	7-146456-2
6	52.93 [2.084]	50.80 [2.000]	20	21	7-146456-1
6	50.39 [1.984]	48.26 [1.900]	19	20	7-146456-0
6	47.85 [1.884]	45.72 [1.800]	18	19	6-146456-9
6	45.31 [1.784]	43.18 [1.700]	17	18	6-146456-8
6	42.77 [1.684]	40.64 [1.600]	16	17	6-146456-7
6	40.23 [1.584]	38.10 [1.500]	15	16	6-146456-6
6	37.69 [1.484]	35.56 [1.400]	14	15	6-146456-5
6	35.15 [1.384]	33.02 [1.300]	13	14	6-146456-4
6	32.61 [1.284]	30.48 [1.200]	12	13	6-146456-3
6	30.07 [1.184]	27.94 [1.100]	11	12	6-146456-2
6	27.53 [1.084]	25.40 [1.000]	10	11	6-146456-1
6	24.99 [0.984]	22.86 [0.900]	9	10	6-146456-0
6	22.45 [0.884]	20.32 [0.800]	8	9	5-146456-9
6	19.91 [0.784]	17.78 [0.700]	7	8	5-146456-8
6	17.37 [0.684]	15.24 [0.600]	6	7	5-146456-7
6	14.83 [0.584]	12.70 [0.500]	5	6	5-146456-6
6	12.29 [0.484]	10.16 [0.400]	4	5	5-146456-5
6	9.75 [0.384]	7.62 [0.300]	3	4	5-146456-4
6	7.21 [0.284]	5.08 [0.200]	2	3	5-146456-3
6	4.67 [0.184]	2.54 [0.100]	1	2	5-146456-2
6	2.13 [0.084]	-	-	1	5-146456-1

PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER
5	101.19 [3.984]	99.06 [3.900]	39	40	4-146456-0
5	98.65 [3.884]	96.52 [3.800]	38	39	3-146456-9
5	96.1 [3.784]	93.98 [3.700]	37	38	3-146456-8
5	93.57 [3.684]	91.44 [3.600]	36	37	3-146456-7
5	91.03 [3.584]	88.90 [3.500]	35	36	3-146456-6
5	88.49 [3.484]	86.36 [3.400]	34	35	3-146456-5
5	85.95 [3.384]	83.82 [3.300]	33	34	3-146456-4
5	83.41 [3.284]	81.28 [3.200]	32	33	3-146456-3
5	80.87 [3.184]	78.74 [3.100]	31	32	3-146456-2
5	78.33 [3.084]	76.20 [3.000]	30	31	3-146456-1
5	75.79 [2.984]	73.66 [2.900]	29	30	3-146456-0
5	73.25 [2.884]	71.12 [2.800]	28	29	2-146456-9
5	70.71 [2.784]	68.58 [2.700]	27	28	2-146456-8
5	68.17 [2.684]	66.04 [2.600]	26	27	2-146456-7
5	65.63 [2.584]	63.50 [2.500]	25	26	2-146456-6
5	63.09 [2.484]	60.96 [2.400]	24	25	2-146456-5
5	60.55 [2.384]	58.42 [2.300]	23	24	2-146456-4
5	58.01 [2.284]	55.88 [2.200]	22	23	2-146456-3
5	55.47 [2.184]	53.34 [2.100]	21	22	2-146456-2
5	52.93 [2.084]	50.80 [2.000]	20	21	2-146456-1
5	50.39 [1.984]	48.26 [1.900]	19	20	2-146456-0
5	47.85 [1.884]	45.72 [1.800]	18	19	1-146456-9
5	45.31 [1.784]	43.18 [1.700]	17	18	1-146456-8
5	42.77 [1.684]	40.64 [1.600]	16	17	1-146456-7
5	40.23 [1.584]	38.10 [1.500]	15	16	1-146456-6
5	37.69 [1.484]	35.56 [1.400]	14	15	1-146456-5
5	35.15 [1.384]	33.02 [1.300]	13	14	1-146456-4
5	32.61 [1.284]	30.48 [1.200]	12	13	1-146456-3
5	30.07 [1.184]	27.94 [1.100]	11	12	1-146456-2
5	27.53 [1.084]	25.40 [1.000]	10	11	1-146456-1
5	24.99 [0.984]	22.86 [0.900]	9	10	1-146456-0
5	22.45 [0.884]	20.32 [0.800]	8	9	146456-9
5	19.91 [0.784]	17.78 [0.700]	7	8	146456-8
5	17.37 [0.684]	15.24 [0.600]	6	7	146456-7
5	14.83 [0.584]	12.70 [0.500]	5	6	146456-6
5	12.29 [0.484]	10.16 [0.400]	4	5	146456-5
5	9.75 [0.384]	7.62 [0.300]	3	4	146456-4
5	7.21 [0.284]	5.08 [0.200]	2	3	146456-3
5	4.67 [0.184]	2.54 [0.100]	1	2	146456-2
5	2.13 [0.084]	-	-	1	146456-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	0 PLC ± -	1 PLC ± -	2 PLC ± 0.51[02]	3 PLC ± 0.127[005]	4 PLC ± 0.0127[0005]	ANGLES ±	
MATERIAL	FINISH	SEE TABLE	WEIGHT	—	SIZE	CAGE CODE	DRAWING NO.	RESTRICTED TO
4					A1	00779	146456	—

CUSTOMER DRAWING SCALE 4:1 SHEET 1 OF 1 REV B

STE TE Connectivity

HEADER ASSEMBLY, MOD II, STACKING, SINGLE ROW, .025 SQ.POST, UNSHROUDED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-146456-7](#)