



RECOMMENDED HOLE LAYOUT

- ① ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- ② TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- ③ THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- ④ HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK. CONTACT: COPPER ALLOY
- ⑤ FINISH: 0.00254-0.00508 [0.000100-0.000200] MATTE TIN-LEAD OVER 0.00127 [0.000050] NICKEL ENTIRE POST.
- ⑥ FINISH: 0.00254-0.00508 [0.000100-0.000200] MATTE TIN OVER 0.00127 [0.000050] NICKEL ENTIRE POST.

PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER
⑥	101.19 [3.984]	99.06 [3.900]	39	80	9-146483-0
⑥	98.65 [3.884]	96.52 [3.800]	38	78	8-146483-9
⑥	96.11 [3.784]	93.98 [3.700]	37	76	8-146483-8
⑥	93.57 [3.684]	91.44 [3.600]	36	74	8-146483-7
⑥	91.03 [3.584]	88.90 [3.500]	35	72	8-146483-6
⑥	88.49 [3.484]	86.36 [3.400]	34	70	8-146483-5
⑥	85.95 [3.384]	83.82 [3.300]	33	68	8-146483-4
⑥	83.41 [3.284]	81.28 [3.200]	32	66	8-146483-3
⑥	80.87 [3.184]	78.74 [3.100]	31	64	8-146483-2
⑥	78.33 [3.084]	76.20 [3.000]	30	62	8-146483-1
⑥	75.79 [2.984]	73.66 [2.900]	29	60	8-146483-0
⑥	73.25 [2.884]	71.12 [2.800]	28	58	7-146483-9
⑥	70.71 [2.784]	68.58 [2.700]	27	56	7-146483-8
⑥	68.17 [2.684]	66.04 [2.600]	26	54	7-146483-7
⑥	65.63 [2.584]	63.50 [2.500]	25	52	7-146483-6
⑥	63.09 [2.484]	60.96 [2.400]	24	50	7-146483-5
⑥	60.55 [2.384]	58.42 [2.300]	23	48	7-146483-4
⑥	58.01 [2.284]	55.88 [2.200]	22	46	7-146483-3
⑥	55.47 [2.184]	53.34 [2.100]	21	44	7-146483-2
⑥	52.93 [2.084]	50.80 [2.000]	20	42	7-146483-1
⑥	50.39 [1.984]	48.26 [1.900]	19	40	7-146483-0
⑥	47.85 [1.884]	45.72 [1.800]	18	38	6-146483-9
⑥	45.31 [1.784]	43.18 [1.700]	17	36	6-146483-8
⑥	42.77 [1.684]	40.64 [1.600]	16	34	6-146483-7
⑥	40.23 [1.584]	38.10 [1.500]	15	32	6-146483-6
⑥	37.69 [1.484]	35.56 [1.400]	14	30	6-146483-5
⑥	35.15 [1.384]	33.02 [1.300]	13	28	6-146483-4
⑥	32.61 [1.284]	30.48 [1.200]	12	26	6-146483-3
⑥	30.07 [1.184]	27.94 [1.100]	11	24	6-146483-2
⑥	27.53 [1.084]	25.40 [1.000]	10	22	6-146483-1
⑥	24.99 [0.984]	22.86 [0.900]	9	20	6-146483-0
⑥	22.45 [0.884]	20.32 [0.800]	8	18	5-146483-9
⑥	19.91 [0.784]	17.78 [0.700]	7	16	5-146483-8
⑥	17.37 [0.684]	15.24 [0.600]	6	14	5-146483-7
⑥	14.83 [0.584]	12.70 [0.500]	5	12	5-146483-6
⑥	12.29 [0.484]	10.16 [0.400]	4	10	5-146483-5
⑥	9.75 [0.384]	7.62 [0.300]	3	8	5-146483-4
⑥	7.21 [0.284]	5.08 [0.200]	2	6	5-146483-3
⑥	4.67 [0.184]	2.54 [0.100]	1	4	5-146483-2
⑥	2.13 [0.084]	-	-	2	5-146483-1

PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER
⑤	101.19 [3.984]	99.06 [3.900]	39	80	4-146483-0
⑤	98.65 [3.884]	96.52 [3.800]	38	78	3-146483-9
⑤	96.11 [3.784]	93.98 [3.700]	37	76	3-146483-8
⑤	93.57 [3.684]	91.44 [3.600]	36	74	3-146483-7
⑤	91.03 [3.584]	88.90 [3.500]	35	72	3-146483-6
⑤	88.49 [3.484]	86.36 [3.400]	34	70	3-146483-5
⑤	85.95 [3.384]	83.82 [3.300]	33	68	3-146483-4
⑤	83.41 [3.284]	81.28 [3.200]	32	66	3-146483-3
⑤	80.87 [3.184]	78.74 [3.100]	31	64	3-146483-2
⑤	78.33 [3.084]	76.20 [3.000]	30	62	3-146483-1
⑤	75.79 [2.984]	73.66 [2.900]	29	60	3-146483-0
⑤	73.25 [2.884]	71.12 [2.800]	28	58	2-146483-9
⑤	70.71 [2.784]	68.58 [2.700]	27	56	2-146483-8
⑤	68.17 [2.684]	66.04 [2.600]	26	54	2-146483-7
⑤	65.63 [2.584]	63.50 [2.500]	25	52	2-146483-6
⑤	63.09 [2.484]	60.96 [2.400]	24	50	2-146483-5
⑤	60.55 [2.384]	58.42 [2.300]	23	48	2-146483-4
⑤	58.01 [2.284]	55.88 [2.200]	22	46	2-146483-3
⑤	55.47 [2.184]	53.34 [2.100]	21	44	2-146483-2
⑤	52.93 [2.084]	50.80 [2.000]	20	42	2-146483-1
⑤	50.39 [1.984]	48.26 [1.900]	19	40	2-146483-0
⑤	47.85 [1.884]	45.72 [1.800]	18	38	1-146483-9
⑤	45.31 [1.784]	43.18 [1.700]	17	36	1-146483-8
⑤	42.77 [1.684]	40.64 [1.600]	16	34	1-146483-7
⑤	40.23 [1.584]	38.10 [1.500]	15	32	1-146483-6
⑤	37.69 [1.484]	35.56 [1.400]	14	30	1-146483-5
⑤	35.15 [1.384]	33.02 [1.300]	13	28	1-146483-4
⑤	32.61 [1.284]	30.48 [1.200]	12	26	1-146483-3
⑤	30.07 [1.184]	27.94 [1.100]	11	24	1-146483-2
⑤	27.53 [1.084]	25.40 [1.000]	10	22	1-146483-1
⑤	24.99 [0.984]	22.86 [0.900]	9	20	1-146483-0
⑤	22.45 [0.884]	20.32 [0.800]	8	18	146483-9
⑤	19.91 [0.784]	17.78 [0.700]	7	16	146483-8
⑤	17.37 [0.684]	15.24 [0.600]	6	14	146483-7
⑤	14.83 [0.584]	12.70 [0.500]	5	12	146483-6
⑤	12.29 [0.484]	10.16 [0.400]	4	10	146483-5
⑤	9.75 [0.384]	7.62 [0.300]	3	8	146483-4
⑤	7.21 [0.284]	5.08 [0.200]	2	6	146483-3
⑤	4.67 [0.184]	2.54 [0.100]	1	4	146483-2
⑤	2.13 [0.084]	-	-	2	146483-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN T. HOFFMAN 1/19/96	APVO G. DUBNICZKI 3/18/96	NAME
0 PLC ± -	1 PLC ± 0.15[02]	APVO G. DUBNICZKI 3/18/96	PRODUCT SPEC	SIZE CASE CODE DRAWING NO
2 PLC ± 0.12[005]	3 PLC ± 0.0127[0005]	APVO G. DUBNICZKI 3/18/96	APPLICATION SPEC	RESTRICTED TO
4 PLC ± 0.0127[0005]	ANGLES ±	WEIGHT	SCALE 4:1	SHEET 1 OF 1
MATERIAL ④	FINISH SEE TABLE	CUSTOMER DRAWING	00779	146483

STE TE Connectivity
 HEADER ASSEMBLY, MOD II, STACKING, DOUBLE ROW, .025 SQ.POST, UNSHROUDED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[146483-5](#)