

Features

Frequency range : 24MHz to 80MHz
 Extremely small SMD type crystal
 4 pad AuSn sealing, ceramic package
 High precision and frequency stability
 External dimensions (mm)
 L : 1.2 x W : 1.0 x H : 0.33
 RoHS and REACH compliant & Pb free

Applications

Wearable devices
 Wi-Fi, BT or other wireless module
 IoT devices
 Smart phone
 Space limited application



Electrical Characteristics

Item		8J	Conditions
Frequency Range	F_0	24MHz ~ 80MHz	
Frequency Tolerance	F_{tol}	$\pm 30\text{ppm}$, $\pm 20\text{ppm}$, $\pm 10\text{ppm}$	at 25°C
Frequency Stability over Operating Temperature Range (refer to 25°C)	F_{stab}	$\pm 30\text{ ppm}$	-20°C ~ +70°C
		$\pm 20\text{ ppm}$	
		$\pm 10\text{ ppm}$	
		$\pm 10\text{ ppm}$	-30°C ~ +85°C
		$\pm 30\text{ ppm}$	-40°C ~ +85°C
		$\pm 20\text{ ppm}$	
Operating Temperature Range	T_{OTR}	-20°C ~ +70°C	
		-40°C ~ +85°C	
Shunt Capacitance	C_0	3pF Max.	
Drive Level	D_L	1 ~ 200μW (100μW Typ.)	
Load Capacitance	C_L	6pF, 7pF, 8pF, 9pF, 10pF, 12pF, 16pF, 18pF	
Aging	F_{aging}	$\pm 3\text{ ppm Max.}$	at 25°C $\pm 3^\circ\text{C}$, first year
Storage Temperature Range	T_{STR}	-55°C ~ +125°C	

Motional Resistance (ESR)

Fundamental	
24 ~ 32 MHz	100Ω Max.
37.4 ~ 48 MHz	80Ω Max.
> 48 MHz	60Ω Max.

Dimensions



(Unit: mm)

Ordering Information

8J - 30.000M A H E - T

Frequency in Hz

Please contact us for available frequencies

Frequency Tolerance (at 25°C)

A	$\pm 30 \text{ ppm}$
D	$\pm 20 \text{ ppm}$
E	$\pm 10 \text{ ppm}$

Frequency Stability (over Temp.)

A	$\pm 30 \text{ ppm}$ ($-20^\circ\text{C} \sim +70^\circ\text{C}$)
D	$\pm 20 \text{ ppm}$ ($-20^\circ\text{C} \sim +70^\circ\text{C}$)
E	$\pm 10 \text{ ppm}$ ($-20^\circ\text{C} \sim +70^\circ\text{C}$)
T	$\pm 10 \text{ ppm}$ ($-30^\circ\text{C} \sim +85^\circ\text{C}$)
H	$\pm 30 \text{ ppm}$ ($-40^\circ\text{C} \sim +85^\circ\text{C}$)
I	$\pm 20 \text{ ppm}$ ($-40^\circ\text{C} \sim +85^\circ\text{C}$)


Packaging Method

T	Tape & Reel
---	-------------

Load Capacitance


B	6 pF
Y	7 pF
V	8 pF
C	9 pF
Q	10 pF
E	12 pF
I	16 pF
J	18 pF

Packing



DIMENSIONS	A	B	C	D	E	F	G	H
	0.45 ±0.05	1.30 ±0.05	1.10 ±0.05	4.00 ±0.10	8.00 ±0.20	4.00 ±0.10	1.55 ±0.05	1.75 ±0.10

(Unit: mm)




DIMENSIONS	L	L1	W	W1
	178 ±1.00	60.2 ±0.50	11.5 ±0.2	8 +1/-0

(Unit: mm)

Reflow Profile

Solder melting point : 220°C ± 10°C, 60 sec. Min.

Peak temperature : 260°C ± 10°C, 10 sec. Min.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

<u>8J-32.000MEEV-T</u>	<u>8J-27.120MEEV-T</u>	<u>8J-37.400MEEV-T</u>	<u>8J-38.400MEEV-T</u>	<u>8J-40.000MEEV-T</u>	<u>8J-48.000MEEV-T</u>
<u>8J-52.000MEEV-T</u>	<u>8J-26.000MEEV-T</u>	<u>8J-76.800MEEV-T</u>	<u>8J-60.000MEEV-T</u>	<u>8J-38.400METV-T</u>	<u>8J-48.000METV-T</u>
<u>8J-24.000METV-T</u>	<u>8J-80.000MEEV-T</u>	<u>8J-32.000METV-T</u>	<u>8J-37.400METV-T</u>	<u>8J-80.000METV-T</u>	<u>8J-27.000METV-T</u>
<u>8J-25.000METV-T</u>	<u>8J-26.000METV-T</u>	<u>8J-40.000METV-T</u>	<u>8J-25.000MEEV-T</u>	<u>8J-60.000METV-T</u>	<u>8J-76.800METV-T</u>
<u>8J-27.000MEEV-T</u>	<u>8J-24.000MEEV-T</u>	<u>8J-27.120METV-T</u>	<u>8J-27.120MEDB-T</u>	<u>8J-24.000MEDQ-T</u>	<u>8J-26.000MDIV-T</u>
<u>8J-37.400METQ-T</u>	<u>8J-38.400MAAY-T</u>				