

Features

- Frequency range : 32.768 kHz
- SMD : Ceramic package
- External dimensions (mm)
L : 3.2 x W : 1.5 x H : 0.75
- RoHS compliant & Pb free


Applications

- Small mobile devices
- Communication devices
- Consumer products
- Commercial & industrial applications

Electrical Characteristics

Item	Symbol	QT3C	Conditions
Nominal Frequency	f_0	32.768 kHz	
Frequency Tolerance	$\Delta f/f_0$	$\pm 10\text{ppm}$, $\pm 20\text{ppm}$, $\pm 30\text{ppm}$, $\pm 50\text{ppm}$	at 25°C
Load Capacitance	C_L	6pF, 7pF, 9pF, 12.5pF	
Operating Temperature Range	T_{OTR}	-40°C ~ +85°C	
		-40°C ~ +125°C	
Storage Temperature Range	T_{STR}	-55°C ~ +125°C	
Turnover Temperature	T_M	25°C \pm 5°C	
Temperature Coefficient	β	-0.04 ppm/°C ² Max.	
Motional Capacitance	C_1	3.1 fF Typ.	
Motional Resistance (ESR)	R_1	70 kΩ Max.	at 25°C
Drive Level	D_L	0.1μW Typ. / 1.0μW Max.	
Aging	$\Delta f/f_0$	± 3 ppm Max.	at 25°C \pm 3°C, first year
Shunt Capacitance	C_0	1.0 pF Typ.	

Dimensions



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

[QT3C-32.768KAZF-T](#) [QT3C-32.768KBZY-T](#) [QT3C-32.768KDWF-T](#) [QT3C-32.768KDZB-T](#) [QT3C-32.768KDZC-T](#)
[QT3C-32.768KDZF-T](#) [QT3C-32.768KDZY-T](#) [QT3C-32.768KEZF-T](#) [QT3C-32.768KAZY-T](#) [QT3C-32.768KBZB-T](#)
[QT3C-32.768KEZC-T](#) [QT3C-32.768KAZB-T](#) [QT3C-32.768KBZC-T](#) [QT3C-32.768KAZC-T](#) [QT3C-32.768KBZF-T](#)
[QT3C-32.768KEZY-T](#)