



RECOMMENDED HOLE LAYOUT

1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
4. HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
5. FINISH: 0.000381 [.000015] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN-LEAD ON SOLDER TAIL, 0.00127 [.000050] NICKEL ENTIRE POST.
6. FINISH: 0.000381 [.000015] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN ON SOLDER TAIL, 0.00127 [.000050] NICKEL ENTIRE POST.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN	R BROWN	19OCT2006	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK	J GESFORD	19OCT2006			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	J GESFORD	19OCT2006	NAME		
0 PLC	± -	APPLICATION SPEC			HEADER ASSEMBLY, MOD II, STACKING, DOUBLE ROW, .025 SQ.POST, UNSHROUDED		
1 PLC	± 0.5[.02]	PRODUCT SPEC			SIZE		
2 PLC	± 0.13[.005]	WEIGHT			SCALE		
3 PLC	± -	CUSTOMER DRAWING			SHEET		
4 PLC	± -	DRAWING NO			REV		
ANGLES	± -	A1 00779 C=146506			1 OF 2		
MATERIAL	SEE TABLE	A1 00779 C=146506			4:1		

△6	101.19 [3.984]	99.06 [3.900]	39	80	9-146506-0
△6	98.65 [3.884]	96.52 [3.800]	38	78	8-146506-9
△6	96.11 [3.784]	93.98 [3.700]	37	76	8-146506-8
△6	93.57 [3.684]	91.44 [3.600]	36	74	8-146506-7
△6	91.03 [3.584]	88.90 [3.500]	35	72	8-146506-6
△6	88.49 [3.484]	86.36 [3.400]	34	70	8-146506-5
△6	85.95 [3.384]	83.82 [3.300]	33	68	8-146506-4
△6	83.41 [3.284]	81.28 [3.200]	32	66	8-146506-3
△6	80.87 [3.184]	78.74 [3.100]	31	64	8-146506-2
△6	78.33 [3.084]	76.20 [3.000]	30	62	8-146506-1
△6	75.79 [2.984]	73.66 [2.900]	29	60	8-146506-0
△6	73.25 [2.884]	71.12 [2.800]	28	58	7-146506-9
△6	70.71 [2.784]	68.58 [2.700]	27	56	7-146506-8
△6	68.17 [2.684]	66.04 [2.600]	26	54	7-146506-7
△6	65.63 [2.584]	63.50 [2.500]	25	52	7-146506-6
△6	63.09 [2.484]	60.96 [2.400]	24	50	7-146506-5
△6	60.55 [2.384]	58.42 [2.300]	23	48	7-146506-4
△6	58.01 [2.284]	55.88 [2.200]	22	46	7-146506-3
△6	55.47 [2.184]	53.34 [2.100]	21	44	7-146506-2
△6	52.93 [2.084]	50.80 [2.000]	20	42	7-146506-1
△6	50.39 [1.984]	48.26 [1.900]	19	40	7-146506-0
△6	47.85 [1.884]	45.72 [1.800]	18	38	6-146506-9
△6	45.31 [1.784]	43.18 [1.700]	17	36	6-146506-8
△6	42.77 [1.684]	40.64 [1.600]	16	34	6-146506-7
△6	40.23 [1.584]	38.10 [1.500]	15	32	6-146506-6
△6	37.69 [1.484]	35.56 [1.400]	14	30	6-146506-5
△6	35.15 [1.384]	33.02 [1.300]	13	28	6-146506-4
△6	32.61 [1.284]	30.48 [1.200]	12	26	6-146506-3
△6	30.07 [1.184]	27.94 [1.100]	11	24	6-146506-2
△6	27.53 [1.084]	25.40 [1.000]	10	22	6-146506-1
△6	24.99 [.984]	22.86 [.900]	9	20	6-146506-0
△6	22.45 [.884]	20.32 [.800]	8	18	5-146506-9
△6	19.91 [.784]	17.78 [.700]	7	16	5-146506-8
△6	17.37 [.684]	15.24 [.600]	6	14	5-146506-7
△6	14.83 [.584]	12.70 [.500]	5	12	5-146506-6
△6	12.29 [.484]	10.16 [.400]	4	10	5-146506-5
△6	9.75 [.384]	7.62 [.300]	3	8	5-146506-4
△6	7.21 [.284]	5.08 [.200]	2	6	5-146506-3
△6	4.67 [.184]	2.54 [.100]	1	4	5-146506-2
△6	2.13 [.084]	-	-	2	5-146506-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

△5	101.19 [3.984]	99.06 [3.900]	39	80	4-146506-0
△5	98.65 [3.884]	96.52 [3.800]	38	78	3-146506-9
△5	96.11 [3.784]	93.98 [3.700]	37	76	3-146506-8
△5	93.57 [3.684]	91.44 [3.600]	36	74	3-146506-7
△5	91.03 [3.584]	88.90 [3.500]	35	72	3-146506-6
△5	88.49 [3.484]	86.36 [3.400]	34	70	3-146506-5
△5	85.95 [3.384]	83.82 [3.300]	33	68	3-146506-4
△5	83.41 [3.284]	81.28 [3.200]	32	66	3-146506-3
△5	80.87 [3.184]	78.74 [3.100]	31	64	3-146506-2
△5	78.33 [3.084]	76.20 [3.000]	30	62	3-146506-1
△5	75.79 [2.984]	73.66 [2.900]	29	60	3-146506-0
△5	73.25 [2.884]	71.12 [2.800]	28	58	2-146506-9
△5	70.71 [2.784]	68.58 [2.700]	27	56	2-146506-8
△5	68.17 [2.684]	66.04 [2.600]	26	54	2-146506-7
△5	65.63 [2.584]	63.50 [2.500]	25	52	2-146506-6
△5	63.09 [2.484]	60.96 [2.400]	24	50	2-146506-5
△5	60.55 [2.384]	58.42 [2.300]	23	48	2-146506-4
△5	58.01 [2.284]	55.88 [2.200]	22	46	2-146506-3
△5	55.47 [2.184]	53.34 [2.100]	21	44	2-146506-2
△5	52.93 [2.084]	50.80 [2.000]	20	42	2-146506-1
△5	50.39 [1.984]	48.26 [1.900]	19	40	2-146506-0
△5	47.85 [1.884]	45.72 [1.800]	18	38	1-146506-9
△5	45.31 [1.784]	43.18 [1.700]	17	36	1-146506-8
△5	42.77 [1.684]	40.64 [1.600]	16	34	1-146506-7
△5	40.23 [1.584]	38.10 [1.500]	15	32	1-146506-6
△5	37.69 [1.484]	35.56 [1.400]	14	30	1-146506-5
△5	35.15 [1.384]	33.02 [1.300]	13	28	1-146506-4
△5	32.61 [1.284]	30.48 [1.200]	12	26	1-146506-3
△5	30.07 [1.184]	27.94 [1.100]	11	24	1-146506-2
△5	27.53 [1.084]	25.40 [1.000]	10	22	1-146506-1
△5	24.99 [.984]	22.86 [.900]	9	20	1-146506-0
△5	22.45 [.884]	20.32 [.800]	8	18	146506-9
△5	19.91 [.784]	17.78 [.700]	7	16	146506-8
△5	17.37 [.684]	15.24 [.600]	6	14	146506-7
△5	14.83 [.584]	12.70 [.500]	5	12	146506-6
△5	12.29 [.484]	10.16 [.400]	4	10	146506-5
△5	9.75 [.384]	7.62 [.300]	3	8	146506-4
△5	7.21 [.284]	5.08 [.200]	2	6	146506-3
△5	4.67 [.184]	2.54 [.100]	1	4	146506-2
△5	2.13 [.084]	-	-	2	146506-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.05[.02] 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -	DIN R BROWN 19OCT2006 CHK J GESFORD 19OCT2006 APVO J GESFORD 19OCT2006	NAME TE Connectivity
MATERIAL △4	FINISH SEE TABLE	PRODUCT SPEC APPLICATION SPEC	SIZE A1
CUSTOMER DRAWING		SCALE 4:1	SHEET 2 OF 2

4805 (3/11)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-146506-7](#)