



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
H	-	B	ECR-11-004693	01APR2011	RC	AH	



FIBER CONNECTIVITY	
ODC PLUG	LC CONN.
PIN 1	A
PIN 2	B



STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1920950	
PART NUMBER	"L" (meter) <sup>3</sup>
X-2064140-Y	XY.0

NOTES:

- 1 REFER TO TE CONNECTIVITY CUSTOMER DRAWING 2064160 FOR CABLE ASSEMBLY LOSS AND WAVELENGTHS THAT CABLE ASSEMBLY LOSS WILL BE TESTED TO
- 2 MINIMUM RETURN LOSS: 45 dB FOR BOTH ODC AND LC CONNECTORS RETURN LOSS WILL BE TESTED AT 1310 nm AND 1550 nm WAVELENGTHS
- <sup>3</sup> STANDARD LENGTHS AND LENGTH TOLERANCE ACC. TO TE CONNECTIVITY CUSTOMER DRAWING 1920950
- <sup>4</sup> INFORMATION ON LABEL SEE DETAIL:
  - BARCODE
  - UNIQUE SERIAL NUMBER
  - ASSEMBLY LENGTH
  - TE CONNECTIVITY PART NUMBER
  - TE CONNECTIVITY ORDER NUMBER
- <sup>5</sup> ALLOWABLE TORQUE: 1 Nm TO 2 Nm WHEN TIGHTENING PLUG NUT
- <sup>6</sup> LENGTH DIFFERENCE BETWEEN LC CONNECTORS < 5 mm

Qty	Description	Item
2	LABEL "A" OR "B"	7
1	FOAC INFORMATION LABEL	6
2	FOAC ODC PROTECTIVE TUBING, BLACK	5
1	FOAC HEAT SHRINK TUBING, BLACK	4
2	LC CONNECTOR ASSEMBLY, SINGLE MODE, BLUE	3
1	FOKIT ODC PLUG ASSEMBLY, 2 FIBER, SINGLE MODE, VINYL CAP	2
L	FOCAB ODC 5.5 mm 2FOLD, SINGLE MODE 9/125, BLACK	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 07APR2009														
DIMENSIONS: METERS		CHK A. HENGELMOLEN 07APR2009														
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. HENGELMOLEN 07APR2009	NAME FIBER OPTIC ODC LEAD 2 FOLD PLUG - LC/PC DUAL SINGLE MODE 9/125													
<table border="1"> <tr> <td>0 PLC</td> <td>± -</td> </tr> <tr> <td>1 PLC</td> <td>± -</td> </tr> <tr> <td>2 PLC</td> <td>± -</td> </tr> <tr> <td>3 PLC</td> <td>± -</td> </tr> <tr> <td>4 PLC</td> <td>± -</td> </tr> <tr> <td>ANGLES</td> <td>± -</td> </tr> </table>		0 PLC	± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± -	PRODUCT SPEC	SIZE A2	
0 PLC	± -															
1 PLC	± -															
2 PLC	± -															
3 PLC	± -															
4 PLC	± -															
ANGLES	± -															
MATERIAL		FINISH	WEIGHT	CAGE CODE 00779												
-		-	-	DRAWING NO C-2064140												
-		-	-	RESTRICTED TO												
-		-	-	SCALE NTS												
-		-	-	SHEET 1 of 1												
-		-	-	REV B												

ODC IS A TRADEMARK OF HUBER & SUHNER AG CORPORATION

2064140

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2064140-7](#)