




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
D5		REVISED PER ECR-18-001421	30JAN2018	JH PKS



- 1 SPECIFICATIONS:
 MAGNET WIRE #18 - #34 AWG,
 0.16MM(.006")-1.02MM(.040") DIA COPPER.
 OTHER SIZES MAY BE ACCOMMODATED,
 CONSULT TYCO ELECTRONICS FOR APPROVAL.
 MALE BLADE 0.5MM(.020") THICK BRASS
- 2 POCKET RECOMMENDATION: #1601425
- 3 TERMINALS TO BE APPLIED PER TYCO ELECTRONICS SPECIFICATION 114-13166 FIGURE 11.
- 4 PRODUCT SPECIFICATION: STANDARD SIAMEZE 108-2085
- 5 PRODUCT SPECIFICATION: HIGH TEMPERATURE 108-2293
- 6 PRELIMINARY-FOR QUOTATION



5	EXTRA HARD CU ALLOY	UNPLATED	-	6	4-1601075-4
5	EXTRA HARD CU ALLOY	UNPLATED	-	6	2-1601075-4
4	BRASS, SPRING HARD	PRE-TIN PLATE OVER COPPER UNDERPLATE	031-145-014		4-1601075-2
4	BRASS, SPRING HARD	UNPLATED	031-145-014		4-1601075-1
4	BRASS, SPRING HARD	POST TIN PLATE OVER NICKEL UNDERPLATE	-		2-1601075-3
4	BRASS, SPRING HARD	PRE-TIN PLATE OVER COPPER UNDERPLATE	131-146-014		2-1601075-2
4	BRASS, SPRING HARD	UNPLATED	131-146-000		2-1601075-1
4	BRASS, SPRING HARD	PRE-TIN PLATE OVER COPPER UNDERPLATE	131-145-014		1601075-2
4	BRASS, SPRING HARD	UNPLATED	131-145-000		1601075-1
	MATERIAL	FINISH	REFERENCE PART NUMBER		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.WELLER 11JAN2002	TE Connectivity Ltd.	
DIMENSIONS: mm [INCHES]		CHK M.FEHER 11JAN2002		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K.RANDOLPH 11JAN2002	NAME	
0 PLC ± - 1 PLC ± 0.25 [.010] 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± 2°		PRODUCT SPEC	STANDARD RANGE WIRE TO BLADE, SIAMEZE TERMINAL	
MATERIAL SEE TABLE		FINISH SEE TABLE	WEIGHT 0.000000	RESTRICTED TO
		SEE TABLE	SIZE A2	SCALE 6:1
		SEE TABLE	CAGE CODE 00779	SHEET 1 of 1
		SEE TABLE	DRAWING NO C=1601075	REV D5
		SEE TABLE	CUSTOMER DRAWING	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-1601075-1](#)