



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - TE Connectivity Ltd. ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A3	REVISED PER ECR-09-018681	20AUG2009	VKH	RRP
	A4	REVISED PER ECR-09-018681	28JAN2010	KK	HMR
	A5	REVISED PER ECO-19-003069	01OCT2019	RS	DR




ORDER NO. BESTELL-NR.	CROSS SECTION QUERSCHNITT		STRIP LENGTH ABISOLIER-LÄNGE /mm	TYPE AUSFÜHRUNG	COLOUR FARBE	L <sub>1</sub> /mm	L <sub>2</sub> /mm	d <sub>1</sub> /mm	s <sub>1</sub> /mm	d <sub>2</sub> /mm	s <sub>2</sub> /mm	PACKING UNIT VERPACKUNGSEINHEIT PARTS/STÜCK STRIP/STREIFEN
	mm <sup>2</sup>	AWG										
966 288-4	0.75	18	8	SHORT KURZ	GREY GRAU	12.0 ±1.5	6.0 ±0.4	1.2 +0.14	0.15 ±0.05	2.8 ±0.2	0.25 ±0.1	1000
1-966 288-0	1.00	17	12	HALFLONG HALBLANG	RED ROT	16.0 ±1.5	10.0 ±0.4	1.4 +0.14	0.15 ±0.05	3.0 ±0.2	0.25 ±0.1	1000
1-966 288-1	1.00	17	14	LONG LANG	RED ROT	18.0 ±1.5	12.0 ±0.6	1.4 +0.14	0.15 ±0.05	3.0 ±0.2	0.25 ±0.1	1000
1-966 288-3	1.50	16	12	HALFLONG HALBLANG	BLACK SCHWARZ	16.0 ±1.5	10.0 ±0.4	1.7 +0.25	0.15 ±0.05	3.5 ±0.2	0.25 ±0.1	1000
1-966 288-4	1.50	16	14	HALFLONG+ HALBLANG+	BLACK SCHWARZ	18.0 ±1.5	12.0 ±0.6	1.7 +0.25	0.15 ±0.05	3.5 ±0.2	0.25 ±0.1	1000
1-966 288-5	1.50	16	20	LONG LANG	BLACK SCHWARZ	24.0 ±2.0	18.0 ±0.6	1.7 +0.25	0.15 ±0.05	3.5 ±0.2	0.25 ±0.1	1000
1-966 288-8	2.50	14	20	LONG LANG	BLUE BLAU	24.0 ±2.0	18.0 ±0.6	2.2 +0.25	0.15 ±0.05	4.2 ±0.2	0.25 ±0.1	1000
2-966 288-1	4.00	11	20	LONG LANG	GREY GRAU	26.0 ±2.0	18.0 ±0.6	2.8 +0.25	0.20 ±0.05	4.8 ±0.4	0.30 ±0.1	1000



PACKING UNIT:  
VERPACKUNGSEINHEIT:

STRIP PACKING (FOR EXAMPLE) OF PN 966 288-1  
DARGESTELLT IST STREIFENVERPACKUNG (ZUM BEISPIEL) FÜR PN 966 288-1



- ① THE AWG CROSS-SECTION CAN SLIGHT DEVIATING OF THE DIN-STANDARD CROSS-SECTION VALUES
  - ② RECOMMENDED STRIP LENGTH
  - ③ STRIPS PER 10 PE-BAGS OF 100 PIECES TUBULAR END-SLEEVES
  - ④ MAX. INSULATION-DIA. OF WIRE: d<sub>2</sub> MIN.- 0.1
  - ⑤ TUBULAR END-SLEEVE WITH PLASTIC SLEEVE ACCORDING TO DIN 46228 PART 4
  - + SPECIAL
  - 6. USE HAND TOOL 539660-1
  - 7. NOTE DELETED.
  - ⑧ LENGTH "L1" INCLUDES MOLDING FLASH PRESENT IN THIS ZONE.
- ① DER AWG-QUERSCHNITT KANN VON DEN DIN-NORM QUERSCHNITTSWERTEN GERINGFÜGIG ABWEICHEN.
  - ② EMPFOHLENE ABISOLIERLÄNGE
  - ③ STREIFEN ZU JE 10 PE-BEUTEL à 100 STÜCK ADERENDHÜLSEN
  - ④ MAX. ISOLATIONS-Ø DER LEITUNG: d<sub>2</sub> MIN.- 0.1
  - ⑤ ADERENDHÜLSE MIT KUNSTSTOFFHÜLSE NACH DIN 46228 TEIL 4
  - + SPEZIAL
  - 6. BENUTZEN SIE HANDWERKZEUG 539660-1

TOLERANCES UNLESS OTHERWISE SPECIFIED: n. ISO 8015 n. ISO 2768 - mH -E n. DIN 16901 - 140		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. SCHMIDT 23SEP1993 CHK W. BOCK 15JUN1994			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G. FELDMEIER 12SEP2000			
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC		NAME	
MATERIAL		FINISH		APPLICATION SPEC		TUBULAR END-SLEEVE WITH PLASTIC SLEEVE (STRIP PACKING) ⑤	
				WEIGHT		ADERENDHÜLSE MIT KUNSTSTOFFHÜLSE (STREIFENVERPACKUNG)	
				SCALE NTS		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
				CUSTOMER DRAWING		A2 00779 C=966288	
				SHEET 1 of 1		REV A5	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-966288-8](#)