

REV. 2


DCO 102764

COIL: @ 25°C	
RESISTANCE	300 OHMS ±10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	14.4 VDC
MUST RELEASE	1.8 VDC

ENVIRONMENT:	
VIBRATION	10 CPS TO 2000 CPS @ 20 g's
SHOCK	50 g's 11 MS. DURATION
TEMPERATURE	-55 °C TO +85 °C

NOTES: OPERATE & RELEASE 10 MS MAX.  
 OPERATE BOUNCE 2 MS MAX.  
 RELEASE BOUNCE 5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING:	10 AMPS 28 VDC
	5 AMPS 115 VAC/400 Hz RESISTIVE
	100,000 OPERATIONS

DR. ASB 11/16/01 CK. TLG 11-16-01

**CII Technologies**  
 advanced control electronic solutions

CUST. CII  
 CUST. NO. STD REV.

"07" RELAY

B07B055AC1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[B07B055AC1](#)