




Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Wire Seal**

Primary Product Material: **Silicone Rubber**

Primary Product Color: **Blue**

Operating Temperature (Max): **105 °C [221 °F]**

Number of Positions: **2**

Features

Product Type Features

Connector Seal & Plug Type	Wire Seal
----------------------------	-----------

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Material	Silicone Rubber
Primary Product Color	Blue

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought





TE Part #1903415-1
GHC 9.0 3POS HDR ASSY



TE Part #737440-2
250 FASTON REC 17-14 AWG TPBR




TE Part #770642-1
TIMER CONNECTOR TERMINAL 20-14 AWG PTPBR



TE Part #2232111-1
250 FASTON, FLAG, REC., 12-20 AWG, TPBR



TE Part #2232327-2
CLUSTER BLOCK HSG .090 DIA



TE Part #2292843-3
3P, POSITIVE-LOCK HOUSING, MKIII .250 SE

Documents

Product Drawings

[REAR WIRE SEAL 3PIN, #2 BLOCKED](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-2321922-3_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2321922-3_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-2321922-3_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2321922-3](#)