


LOC		DIST		REVISIONS			
AD	39	P	LTR	DESCRIPTION	DATE	DWN	APVD
		P		REVISED PER ECO-11-004820	21MAR11	RK	HMR

- ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
- FINISH: 0.000381 [.000015] GOLD ON CONTACT AREA, ALL OVER 0.00127 [.000050] NICKEL ENTIRE POST.



RECOMMENDED HOLE LAYOUT

101.19	99.06	39	40	4-146482-0
[3.984]	[3.900]			
98.65	96.52	38	39	3-146482-9
[3.884]	[3.800]			
96.11	93.98	37	38	3-146482-8
[3.784]	[3.700]			
93.57	91.44	36	37	3-146482-7
[3.684]	[3.600]			
91.03	88.90	35	36	3-146482-6
[3.584]	[3.500]			
88.49	86.36	34	35	3-146482-5
[3.484]	[3.400]			
85.95	83.82	33	34	3-146482-4
[3.384]	[3.300]			
83.41	81.28	32	33	3-146482-3
[3.284]	[3.200]			
80.87	78.74	31	32	3-146482-2
[3.184]	[3.100]			
78.33	76.20	30	31	3-146482-1
[3.084]	[3.000]			
75.79	73.66	29	30	3-146482-0
[2.984]	[2.900]			
73.25	71.12	28	29	2-146482-9
[2.884]	[2.800]			
70.71	68.58	27	28	2-146482-8
[2.784]	[2.700]			
68.17	66.04	26	27	2-146482-7
[2.684]	[2.600]			
65.63	63.50	25	26	2-146482-6
[2.584]	[2.500]			
63.09	60.96	24	25	2-146482-5
[2.484]	[2.400]			
60.55	58.42	23	24	2-146482-4
[2.384]	[2.300]			
58.01	55.88	22	23	2-146482-3
[2.284]	[2.200]			
55.47	53.34	21	22	2-146482-2
[2.184]	[2.100]			
52.93	50.80	20	21	2-146482-1
[2.084]	[2.000]			
50.39	48.26	19	20	2-146482-0
[1.984]	[1.900]			
47.85	45.72	18	19	1-146482-9
[1.884]	[1.800]			
45.31	43.18	17	18	1-146482-8
[1.784]	[1.700]			
42.77	40.64	16	17	1-146482-7
[1.684]	[1.600]			
40.23	38.10	15	16	1-146482-6
[1.584]	[1.500]			
37.69	35.56	14	15	1-146482-5
[1.484]	[1.400]			
35.15	33.02	13	14	1-146482-4
[1.384]	[1.300]			
32.61	30.48	12	13	1-146482-3
[1.284]	[1.200]			
30.07	27.94	11	12	1-146482-2
[1.184]	[1.100]			
27.53	25.40	10	11	1-146482-1
[1.084]	[1.000]			
24.99	22.86	9	10	1-146482-0
[.984]	[.900]			
22.45	20.32	8	9	146482-9
[.884]	[.800]			
19.91	17.78	7	8	146482-8
[.784]	[.700]			
17.37	15.24	6	7	146482-7
[.684]	[.600]			
14.83	12.70	5	6	146482-6
[.584]	[.500]			
12.29	10.16	4	5	146482-5
[.484]	[.400]			
9.75	7.62	3	4	146482-4
[.384]	[.300]			
7.21	5.08	2	3	146482-3
[.284]	[.200]			
4.67	2.54	1	2	146482-2
[.184]	[.100]			
2.13	-	-	1	146482-1
[.084]	-	-		
G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0. PLC	± -
1. PLC	± -
2. PLC	± 0.51[.02]
3. PLC	± 0.12[.005]
4. PLC	± 0.012[.0005]
ANGLES	± -

MATERIAL: FINISH:

THIS DRAWING IS A CONTROLLED DOCUMENT. DWN: E. BRANDBERG 14-MAR-97. CHK: G. DUBNICZKI 14-MAR-97. APVD: G. DUBNICZKI 14-MAR-97. NAME: G. DUBNICZKI. PRODUCT SPEC: -. APPLICATION SPEC: -. WEIGHT: -. SIZE: A1. CASE CODE: 00779. DRAWING NO: 146482. RESTRICTED TO: -. CUSTOMER DRAWING. SCALE: 4:1. SHEET: 1 OF 1. REV: P.

STE TE Connectivity

HEADER ASSEMBLY, MOD II, STACKING, SINGLE ROW, .025 SQ.POST, UNSHROUDED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[146482-9](#)