


SPECIFICATION CONTROL DRAWING			0026M3424
<b>CHEMINAX</b>	100 OHM, AWG 26, 19 STRANDS OF AWG 38, TWINAXIAL CABLE, OPTIMIZED DOUBLE SHIELD	Date	11-13-07
		Revision	D
THIS SPECIFICATION SHEET FORMS A PART OF THE LATEST ISSUE OF RAYCHEM SPECIFICATION 1200.			
CONSTRUCTION DETAILS		ELECTRICAL CHARACTERISTICS	
DIMENSIONS ARE NOMINAL VALUES IN INCHES UNLESS OTHERWISE DESIGNATED.  <p><b>CONDUCTOR</b> AWG 26, 19 strands of AWG 38, Silver-Coated High Strength Copper Alloy</p> <p><b>DIELECTRICS</b> Rayfoam H Color - White/Light Blue</p> <p><b>FILLERS</b> Radiation-Crosslinked, Modified ETFE</p> <p><b>1ST SHIELD</b> AWG 38, Nickel-Coated Copper Optimized</p> <p><b>2ND SHIELD</b> AWG 38, Nickel-Coated Copper Optimized</p> <p><b>JACKET</b> Modified FEP</p> <p>Dimensions: .0185, .044, .029, .105, .122, .146</p>		<p>CHARACTERISTIC IMPEDANCE 110 ± 10 ohms at 1 MHz 100 ± 10 ohms at 10 MHz</p> <p>MUTUAL CAPACITANCE 13.8 pF/ft. (nominal)</p> <p>VELOCITY OF PROPAGATION 75% (nominal)</p> <p>SURFACE TRANSFER IMPEDANCE 10 milliohms/meter (maximum) at 30 MHz on a 0.7 meter test length</p>	
		ADDITIONAL REQUIREMENTS	
		<b>ELECTRICAL</b>	
		<p>CONDUCTOR RESISTANCE 43.9 ohms/1000 ft. (nominal)</p> <p>INSULATION RESISTANCE 10,000 megohms (minimum) for 1000 ft.</p> <p>JACKET FLAWS SPARK TEST 1.0 kV (rms) IMPULSE TEST 6.0 kV (peak)</p> <p>VOLTAGE WITHSTAND (DIELECTRIC) 1000 volts (rms) (minimum)</p>	
		<b>ENVIRONMENTAL</b>	
		<p>FLAMMABILITY Method B</p> <p>HEAT SHOCK 225°C</p> <p>LOW TEMPERATURE-COLD BEND -55°C/4.00 inch mandrel</p> <p>VOLTAGE WITHSTAND (Post Environmental) 1000 volts (rms), 1 minute</p>	
		<b>PHYSICAL</b>	
		<p>INSULATION (DIELECTRIC) ELONGATION 50% (minimum) TENSILE STRENGTH 600 lbf/in<sup>2</sup> (minimum)</p> <p>JACKET ELONGATION 200% (minimum) TENSILE STRENGTH 2000 lbf/in<sup>2</sup> (minimum)</p> <p>JACKET THICKNESS .012 inch (nominal)</p> <p>SHIELD COVERAGE (EACH) 90% (minimum)</p> <p>WEIGHT 21.5 lbs/1000 ft. (nominal)</p>	
<p>Outer jacket color will be translucent white (designated by a "-9X" appended to the part number, e.g. 0026M3424-9X) unless otherwise specified.</p> <p>Designate outer jacket color with a dash number in accordance with MIL-STD-681. Other codes and suffixes may be added to the part number, as necessary, to capture any additional requirements imposed by the purchase order.</p>			
<p>Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.</p>			
<p>The TE logo, Tyco Electronics, Cheminax, Raychem and Rayfoam are trademarks.</p>			



Raychem Wire & Cable  
501 Oakside Avenue  
Redwood City, California 94063-3800  
1-800-227-8816 Fax: 1-650-361-6297

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[CL6824-000](#)