



- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 2 .000030 GOLD ON AREA D, .000100 - .000200 MATTE TIN-LEAD ON AREA F, ALL OVER .000050 NICKEL ENTIRE POST
- 3 .000100 - .000200 BRIGHT TIN-LEAD OVER .000050 NICKEL ENTIRE POST
- 4. RECOMMENDED P.C.BOARD HOLE SIZE:

P C BOARD THICKNESS	PLATED HOLE SIZE	UNPLATED HOLE SIZE
.062	.034 ± .002	.036 ± .002
.093	.034 ± .002	.036 ± .002
.125	.034 ± .002	.036 ± .002

- 5 .000015 GOLD ON AREA D, .000100 - .000200 MATTE TIN-LEAD ON AREA F, ALL OVER .000050 NICKEL ENTIRE POST.
- 6 DIMENSION PERTAINS TO THE LENGTH OF THE INTERFERENCE AREA OF THE STAR.
- 7 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- 8 .000030 GOLD ON AREA D, .000100-.000200 MATTE TIN ON AREA F. ALL OVER .000050 NICKEL ENTIRE POST.
- 9 .000100-.000200 MATTE TIN OVER .000050 NICKEL ENTIRE PAST.
- 10 .000015 GOLD ON AREA D, .000100-.000200 MATTE TIN ON AREA F, ALL OVER .000050 NICKEL ENTIRE POST.
- 11 ROHS 2002/95/EC COMPLIANT.
- 12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

7	.245	10	.015	.080	.080	.230	.451	.071	.380	11	6-103577-9
12	OBSOLETE	10	.015	.080	.100	.185	.341	.071	.270	11	6-103577-7
	.283	9	.015	.080	.100	.185	.389	.071	.318	11	6-103577-5
12	OBSOLETE	10	.015	.080	.100	.200	.424	.071	.353	11	6-103577-3
	.235	9	-	-	-	.341	.071	.270	11	6-103577-1	
12	OBSOLETE	9	-	-	-	.389	.071	.318	11	5-103577-9	
12	OBSOLETE	9	-	-	-	.424	.071	.353	11	5-103577-7	
	.235	8	.015	.080	.100	.185	.341	.071	.270	11	5-103577-5
	.283	8	.015	.080	.100	.185	.389	.071	.318	11	5-103577-3
	.318	8	.015	.080	.100	.200	.424	.071	.353	11	5-103577-1
7	.245	5	.015	.080	.080	.230	.451	.071	.380		1-103577-9
	.235	5	.015	.080	.100	.185	.341	.071	.270		1-103577-7
	.283	3	.015	.080	.100	.185	.389	.071	.318		1-103577-5
	.318	5	.015	.080	.100	.200	.424	.071	.353		1-103577-3
	.235	3	-	-	-	.341	.071	.270			1-103577-1
12	OBSOLETE	3	-	-	-	.389	.071	.318			103577-9
	.318	3	-	-	-	.424	.071	.353			103577-7
	.235	2	.015	.080	.100	.185	.341	.071	.270		103577-5
	.283	2	.015	.080	.100	.185	.389	.071	.318		103577-3
	.318	2	.015	.080	.100	.200	.424	.071	.353		103577-1
MATING HEIGHT ABOVE BOARD (REF)		FINISH	G	F	E	D	C	B	A	ASSEMBLY PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0. PLC	± .005
1. PLC	± .005
2. PLC	± .005
3. PLC	± .005
4. PLC	± .005

MATERIAL: BANDOLIER - BRASS, POST - PHOS BRONZE

FINISH: BANDOLIER - NONE, POST - SEE TABLE

APPROVED: R. FELICKER

DATE: 12SEP87

SIZE: A1

SCALE: 10:1

SHEET: 1 OF 1

REV: G3

STE TE Connectivity

ASSEMBLY, BANDOLIER, .100 CL, .025 SQUARE POSTS

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103577-5](#)