



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

| LOC | | DIST | | REVISIONS | | | | |
|-----|----|------|-----|---------------------------|--|-----------|-----|------|
| AD | 00 | P | LTR | DESCRIPTION | | DATE | DWN | APVD |
| | | J | | REVISED PER ECO-14-000068 | | 28APR2014 | NK | MM |



RECOMMENDED HOLE LAYOUT

- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 2 ASSEMBLIES MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- 3 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 4 .000030 GOLD ON THE CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON THE SOLDER TAIL, ALL OVER .000050 NICKEL
- 5 PARTS PACKAGED IN SINGLE TUBES.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

| | | | | | | | |
|---|----------|--------------------------|-------|-------|----|-----------|----------------------|
| 6 | 5 | OBSOLETE | .184 | .100 | 1 | 2 | 4-103747-1 |
| | | | 3.984 | 3.900 | 39 | 40 | 4-103747-0 |
| 6 | OBSOLETE | | 3.884 | 3.800 | 38 | 39 | 3- - -9 |
| | | | 3.784 | 3.700 | 37 | 38 | 3- - -8 |
| 6 | OBSOLETE | | 3.684 | 3.600 | 36 | 37 | 3- - -7 |
| | | SUPERCEDED BY 6-146285-3 | 3.584 | 3.500 | 35 | 36 | 3- - -6 |
| 6 | OBSOLETE | | 3.484 | 3.400 | 34 | 35 | 3- - -5 |
| | | | 3.284 | 3.300 | 33 | 34 | 3- - -4 |
| 6 | OBSOLETE | | 3.284 | 3.200 | 32 | 33 | 3- - -3 |
| | | | 3.184 | 3.100 | 31 | 32 | 3- - -2 |
| 6 | OBSOLETE | | 3.084 | 3.000 | 30 | 31 | 3- - -1 |
| | | | 2.984 | 2.900 | 29 | 30 | 3- - -0 |
| 6 | OBSOLETE | | 2.884 | 2.800 | 28 | 29 | 2- - -9 |
| | | | 2.784 | 2.700 | 27 | 28 | 2- - -8 |
| 6 | OBSOLETE | | 2.684 | 2.600 | 26 | 27 | 2- - -7 |
| | | | 2.584 | 2.500 | 25 | 26 | 2- - -6 |
| 6 | OBSOLETE | | 2.484 | 2.400 | 24 | 25 | 2- - -5 |
| | | | 2.384 | 2.300 | 23 | 24 | 2- - -4 |
| 6 | OBSOLETE | | 2.284 | 2.200 | 22 | 23 | 2- - -3 |
| | | | 2.184 | 2.100 | 21 | 22 | 2- - -2 |
| 6 | OBSOLETE | | 2.084 | 2.000 | 20 | 21 | 2- - -1 |
| | | | 1.984 | 1.900 | 19 | 20 | 2- - -0 |
| 6 | OBSOLETE | | 1.884 | 1.800 | 18 | 19 | 1- - -9 |
| | | | 1.784 | 1.700 | 17 | 18 | 1- - -8 |
| 6 | OBSOLETE | | 1.684 | 1.600 | 16 | 17 | 1- - -7 |
| | | | 1.584 | 1.500 | 15 | 16 | 1- - -6 |
| 6 | OBSOLETE | | 1.484 | 1.400 | 14 | 15 | 1- - -5 |
| | | | 1.384 | 1.300 | 13 | 14 | 1- - -4 |
| 6 | OBSOLETE | SUPERCEDED BY 6-146285-3 | 1.284 | 1.200 | 12 | 13 | 1- - -3 |
| | | | 1.184 | 1.100 | 11 | 12 | 1- - -2 |
| 6 | OBSOLETE | | 1.084 | 1.000 | 10 | 11 | 1- - -1 |
| | | | .984 | .900 | 9 | 10 | 1- - -0 |
| 6 | OBSOLETE | | .884 | .800 | 8 | 9 | - - -9 |
| | | | .784 | .700 | 7 | 8 | - - -8 |
| 6 | OBSOLETE | | .684 | .600 | 6 | 7 | - - -7 |
| | | | .584 | .500 | 5 | 6 | - - -6 |
| 6 | OBSOLETE | | .484 | .400 | 4 | 5 | - - -5 |
| | | | .384 | .300 | 3 | 4 | - - -4 |
| 6 | OBSOLETE | | .284 | .200 | 2 | 3 | - - -3 |
| | | | .184 | .100 | 1 | 2 | - - -2 |
| 6 | OBSOLETE | | .084 | - | - | 1 | 103747-1 |
| | | | C | B | A | NO OF POS | ASSEMBLY PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: L.D.RINGLEY 7-24-85
 CHK: R.FLICKER 7-24-85
 APVD: R.FLICKER 7-24-85

TE Connectivity

ASSEMBLY, MOD II, HEADER, BREAKAWAY, SINGLE ROW, .100 CL VERTICAL, WITH .025 SQ POSTS

SIZE: A2 CAGE CODE: 00779 DRAWING NO: 103747 RESTRICTED TO: -

MATERIAL: HOUSING-FLAME RETARDANT THERMOPLASTIC COLOR-BLACK POSTS: COPPER ALLOY

FINISH: POSTS 4

SCALE: 4:1 SHEET: 1 of 1 REV: J

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103747-5](#)