


3 1.07 ± 0.20 [.042 ± 0.008] 4 PLC



RECOMMENDED HOLE LAYOUT

1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 4 HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
- 5 FINISH: 0.000381 [.000015] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN-LEAD ON SOLDER TAIL, 0.00127 [.000050] NICKEL ENTIRE POST.
- 6 FINISH: 0.000381 [.000015] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN ON SOLDER TAIL, 0.00127 [.000050] NICKEL ENTIRE POST.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN R BROWN 19OCT2006	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK J GEFSEFORD 19OCT2006		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J GEFSEFORD 19OCT2006	NAME	
0 PLC ± -			HEADER ASSEMBLY, MOD II, STACKING, DOUBLE ROW, .025 SQ.POST, UNSHROUDED	
1 PLC ± 0.5[.02]			PRODUCT SPEC	
2 PLC ± 0.13[.005]			APPLICATION SPEC	
3 PLC ± -			MATERIAL	
4 PLC ± -			WEIGHT	
ANGLES ± -			SIZE CAGE CODE DRAWING NO	
FINISH SEE TABLE			A1 00779 C=146506	
			CUSTOMER DRAWING	
			SCALE 4:1	SHEET 1 OF 2 REV A1

△6	101.19 [3.984]	99.06 [3.900]	39	80	9-146506-0
△6	98.65 [3.884]	96.52 [3.800]	38	78	8-146506-9
△6	96.11 [3.784]	93.98 [3.700]	37	76	8-146506-8
△6	93.57 [3.684]	91.44 [3.600]	36	74	8-146506-7
△6	91.03 [3.584]	88.90 [3.500]	35	72	8-146506-6
△6	88.49 [3.484]	86.36 [3.400]	34	70	8-146506-5
△6	85.95 [3.384]	83.82 [3.300]	33	68	8-146506-4
△6	83.41 [3.284]	81.28 [3.200]	32	66	8-146506-3
△6	80.87 [3.184]	78.74 [3.100]	31	64	8-146506-2
△6	78.33 [3.084]	76.20 [3.000]	30	62	8-146506-1
△6	75.79 [2.984]	73.66 [2.900]	29	60	8-146506-0
△6	73.25 [2.884]	71.12 [2.800]	28	58	7-146506-9
△6	70.71 [2.784]	68.58 [2.700]	27	56	7-146506-8
△6	68.17 [2.684]	66.04 [2.600]	26	54	7-146506-7
△6	65.63 [2.584]	63.50 [2.500]	25	52	7-146506-6
△6	63.09 [2.484]	60.96 [2.400]	24	50	7-146506-5
△6	60.55 [2.384]	58.42 [2.300]	23	48	7-146506-4
△6	58.01 [2.284]	55.88 [2.200]	22	46	7-146506-3
△6	55.47 [2.184]	53.34 [2.100]	21	44	7-146506-2
△6	52.93 [2.084]	50.80 [2.000]	20	42	7-146506-1
△6	50.39 [1.984]	48.26 [1.900]	19	40	7-146506-0
△6	47.85 [1.884]	45.72 [1.800]	18	38	6-146506-9
△6	45.31 [1.784]	43.18 [1.700]	17	36	6-146506-8
△6	42.77 [1.684]	40.64 [1.600]	16	34	6-146506-7
△6	40.23 [1.584]	38.10 [1.500]	15	32	6-146506-6
△6	37.69 [1.484]	35.56 [1.400]	14	30	6-146506-5
△6	35.15 [1.384]	33.02 [1.300]	13	28	6-146506-4
△6	32.61 [1.284]	30.48 [1.200]	12	26	6-146506-3
△6	30.07 [1.184]	27.94 [1.100]	11	24	6-146506-2
△6	27.53 [1.084]	25.40 [1.000]	10	22	6-146506-1
△6	24.99 [.984]	22.86 [.900]	9	20	6-146506-0
△6	22.45 [.884]	20.32 [.800]	8	18	5-146506-9
△6	19.91 [.784]	17.78 [.700]	7	16	5-146506-8
△6	17.37 [.684]	15.24 [.600]	6	14	5-146506-7
△6	14.83 [.584]	12.70 [.500]	5	12	5-146506-6
△6	12.29 [.484]	10.16 [.400]	4	10	5-146506-5
△6	9.75 [.384]	7.62 [.300]	3	8	5-146506-4
△6	7.21 [.284]	5.08 [.200]	2	6	5-146506-3
△6	4.67 [.184]	2.54 [.100]	1	4	5-146506-2
△6	2.13 [.084]	-	-	2	5-146506-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

△5	101.19 [3.984]	99.06 [3.900]	39	80	4-146506-0
△5	98.65 [3.884]	96.52 [3.800]	38	78	3-146506-9
△5	96.11 [3.784]	93.98 [3.700]	37	76	3-146506-8
△5	93.57 [3.684]	91.44 [3.600]	36	74	3-146506-7
△5	91.03 [3.584]	88.90 [3.500]	35	72	3-146506-6
△5	88.49 [3.484]	86.36 [3.400]	34	70	3-146506-5
△5	85.95 [3.384]	83.82 [3.300]	33	68	3-146506-4
△5	83.41 [3.284]	81.28 [3.200]	32	66	3-146506-3
△5	80.87 [3.184]	78.74 [3.100]	31	64	3-146506-2
△5	78.33 [3.084]	76.20 [3.000]	30	62	3-146506-1
△5	75.79 [2.984]	73.66 [2.900]	29	60	3-146506-0
△5	73.25 [2.884]	71.12 [2.800]	28	58	2-146506-9
△5	70.71 [2.784]	68.58 [2.700]	27	56	2-146506-8
△5	68.17 [2.684]	66.04 [2.600]	26	54	2-146506-7
△5	65.63 [2.584]	63.50 [2.500]	25	52	2-146506-6
△5	63.09 [2.484]	60.96 [2.400]	24	50	2-146506-5
△5	60.55 [2.384]	58.42 [2.300]	23	48	2-146506-4
△5	58.01 [2.284]	55.88 [2.200]	22	46	2-146506-3
△5	55.47 [2.184]	53.34 [2.100]	21	44	2-146506-2
△5	52.93 [2.084]	50.80 [2.000]	20	42	2-146506-1
△5	50.39 [1.984]	48.26 [1.900]	19	40	2-146506-0
△5	47.85 [1.884]	45.72 [1.800]	18	38	1-146506-9
△5	45.31 [1.784]	43.18 [1.700]	17	36	1-146506-8
△5	42.77 [1.684]	40.64 [1.600]	16	34	1-146506-7
△5	40.23 [1.584]	38.10 [1.500]	15	32	1-146506-6
△5	37.69 [1.484]	35.56 [1.400]	14	30	1-146506-5
△5	35.15 [1.384]	33.02 [1.300]	13	28	1-146506-4
△5	32.61 [1.284]	30.48 [1.200]	12	26	1-146506-3
△5	30.07 [1.184]	27.94 [1.100]	11	24	1-146506-2
△5	27.53 [1.084]	25.40 [1.000]	10	22	1-146506-1
△5	24.99 [.984]	22.86 [.900]	9	20	1-146506-0
△5	22.45 [.884]	20.32 [.800]	8	18	146506-9
△5	19.91 [.784]	17.78 [.700]	7	16	146506-8
△5	17.37 [.684]	15.24 [.600]	6	14	146506-7
△5	14.83 [.584]	12.70 [.500]	5	12	146506-6
△5	12.29 [.484]	10.16 [.400]	4	10	146506-5
△5	9.75 [.384]	7.62 [.300]	3	8	146506-4
△5	7.21 [.284]	5.08 [.200]	2	6	146506-3
△5	4.67 [.184]	2.54 [.100]	1	4	146506-2
△5	2.13 [.084]	-	-	2	146506-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.05[.02] 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -	DIN R BROWN 19OCT2006 CHK J GESFORD 19OCT2006 APVO J GESFORD 19OCT2006	NAME TE Connectivity
MATERIAL 4	FINISH SEE TABLE	PRODUCT SPEC APPLICATION SPEC	SIZE CASE CODE DRAWING NO A1 00779 146506
CUSTOMER DRAWING		RESTRICTED TO	SCALE 4:1 SHEET 2 OF 2 REV A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-146506-1](#)