


REVISED PER		ECO-11-004820	DATE	BY	APPROVED
P	REVISED PER	ECO-11-004820	21MAR11	RK	HMR

- ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
- FINISH: 0.000381 [.000015] GOLD ON CONTACT AREA, OVER 0.00127 [.000050] NICKEL, ENTIRE POST.



THIS DRAWING HAS BEEN TRANSLATED AND REFLECTS THE PREVIOUS REVISION. IT WILL REQUIRE A COMPLETE DRAWING CHECK BY PRODUCT ENGINEERING WHEN THE NEXT ECO CHANGE IS WRITTEN - THIS MAY REQUIRE A CHANGE TO THE REVISION OF THE DOCUMENT MANAGER FOLDER AND THIS DRAWING.

PLC	PLC	PLC	PLC	PLC	PLC
101.19	99.06	39	80	4-146510-0	
[3.984]	[3.900]				
98.65	96.52	38	78	3-146510-9	
[3.884]	[3.800]				
96.11	93.98	37	76	3-146510-8	
[3.784]	[3.700]				
93.57	91.44	36	74	3-146510-7	
[3.684]	[3.600]				
91.03	88.90	35	72	3-146510-6	
[3.584]	[3.500]				
88.49	86.36	34	70	3-146510-5	
[3.484]	[3.400]				
85.95	83.82	33	68	3-146510-4	
[3.384]	[3.300]				
83.41	81.28	32	66	3-146510-3	
[3.284]	[3.200]				
80.87	78.74	31	64	3-146510-2	
[3.184]	[3.100]				
78.33	76.20	30	62	3-146510-1	
[3.084]	[3.000]				
75.79	73.66	29	60	3-146510-0	
[2.984]	[2.900]				
73.25	71.12	28	58	2-146510-9	
[2.884]	[2.800]				
70.71	68.58	27	56	2-146510-8	
[2.784]	[2.700]				
68.17	66.04	26	54	2-146510-7	
[2.684]	[2.600]				
65.63	63.50	25	52	2-146510-6	
[2.584]	[2.500]				
63.09	60.96	24	50	2-146510-5	
[2.484]	[2.400]				
60.55	58.42	23	48	2-146510-4	
[2.384]	[2.300]				
58.01	55.88	22	46	2-146510-3	
[2.284]	[2.200]				
55.47	53.34	21	44	2-146510-2	
[2.184]	[2.100]				
52.93	50.80	20	42	2-146510-1	
[2.084]	[2.000]				
50.39	48.26	19	40	2-146510-0	
[1.984]	[1.900]				
47.85	45.72	18	38	1-146510-9	
[1.884]	[1.800]				
45.31	43.18	17	36	1-146510-8	
[1.784]	[1.700]				
42.77	40.64	16	34	1-146510-7	
[1.684]	[1.600]				
40.23	38.10	15	32	1-146510-6	
[1.584]	[1.500]				
37.69	35.56	14	30	1-146510-5	
[1.484]	[1.400]				
35.15	33.02	13	28	1-146510-4	
[1.384]	[1.300]				
32.61	30.48	12	26	1-146510-3	
[1.284]	[1.200]				
30.07	27.94	11	24	1-146510-2	
[1.184]	[1.100]				
27.53	25.40	10	22	1-146510-1	
[1.084]	[1.000]				
24.99	22.86	9	20	1-146510-0	
[.984]	[.900]				
22.45	20.32	8	18	146510-9	
[.884]	[.800]				
19.91	17.78	7	16	146510-8	
[.784]	[.700]				
17.37	15.24	6	14	146510-7	
[.684]	[.600]				
14.83	12.70	5	12	146510-6	
[.584]	[.500]				
12.29	10.16	4	10	146510-5	
[.484]	[.400]				
9.75	7.62	3	8	146510-4	
[.384]	[.300]				
7.21	5.08	2	6	146510-3	
[.284]	[.200]				
4.67	2.54	1	4	146510-2	
[.184]	[.100]				
2.13	-	-	2	146510-1	
[.084]	-	-			
G	F	E	NO. OF POSITIONS	PART NUMBER	

RECOMMENDED HOLE LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPROVED	DATE
0 PLC ± -	1 PLC ± -	12NOV96	
1 PLC ± -	2 PLC ± 0.51[.02]	12NOV96	
2 PLC ± -	3 PLC ± 0.12[.005]		
3 PLC ± -	4 PLC ± 0.012[.0005]		
4 PLC ± -	ANGLES ± -		

MATERIAL: 4 FINISH: 5

WEIGHT: -

CUSTOMER DRAWING

SCALE: 4:1 SHEET 1 OF 1 REV P

STE TE Connectivity

HEADER ASSEMBLY, MOD II, STACKING, DOUBLE ROW, .025 SQ.POST, UNSHROUDED

00779-146510

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[146510-8](#)