



RECOMMENDED MOUNTING HOLE PATTERN FOR .063 THK PRINTED CIRCUIT BOARD

- 1 MATERIAL: HEADER - POLYESTER UL94V-0 (BLACK)
POST - COPPER ALLOY.
- 2 SOLDER SIDE OF P.C. BOARD SHOWN.
- 3 PARTS COMPLY WITH AMP SOLDERABILITY SPEC 109-11-2.
- 4 ONE HOLE MAY BE UNDERSIZED (.032-.035 DIA) FOR ASSEMBLY RETENTION DURING WAVE SOLDERING.
- 5 LATCH DETENT FEATURE OCCURS 2 PLACES ON EACH END (MAXIMUM OF FOUR PER PART). FOR 2 THRU 5 CIRCUIT HEADERS, LATCH FEATURE OCCURS BETWEEN EACH CIRCUIT.
- 6 COORDINATE DIMENSION APPLIES FROM CENTER OF ACTUAL FEATURE.
- 7 POST: 93/7 BRIGHT TIN-LEAD PLATING (-2 THRU -14) OR 100% MATTE TIN PLATING (-32 THRU -44).
- 8 POST MUST WITHSTAND 3.0 LBS (13.34 NEWTONS) MIN FORCE WITHOUT DISLODGING, EITHER DIRECTION.
- 9 TWO SIDES OF TAPER, AS SHOWN, MUST BE PLATED. TYPICAL, BOTH ENDS.
- 10 TWO SIDES OF TAPER, AS SHOWN, AND TIP MAY BE UNPLATED. TYPICAL, BOTH ENDS.
- 11 SLOTS MAY OR MAY NOT APPEAR ON THESE PARTS.
- 12 UL RECOGNIZED (UR) LOGO AND CSA LOGO WILL APPEAR ON THE SIDE OF THE PART. THE AMP LOGO MAY APPEAR ON THE SIDE OR ON BOTTOM OF PART.
- 13 OBSOLETE PART NUMBER

.030	0.76	.107	2.72	-	-
.025	0.64	.100	2.54	-	-
.010	0.25	.092	2.34	.410	10.41
.005	0.13	.063	1.60	.313	7.95
.001	0.03	.040	1.02	.300	7.62
.0003500	0.00889	.036	0.91	.280	7.11
.0001500	0.00381	.035	0.89	.176	4.47
.000	0.00	.032	0.81	.130	3.30
IN	MM	IN	MM	IN	MM

CONVERSION TABLE

1.484	37.69	14	4-644894-4
1.384	35.15	13	4-644894-3
1.284	32.61	12	4-644894-2
1.184	30.07	11	4-644894-1
1.084	27.53	10	4-644894-0
.984	24.99	9	3-644894-9
.884	22.45	8	3-644894-8
.784	19.91	7	3-644894-7
.684	17.37	6	3-644894-6
.584	14.83	5	3-644894-5
.484	12.29	4	3-644894-4
.384	9.75	3	3-644894-3
.284	7.21	2	3-644894-2

13	1.484	37.69	14	1-644894-4
	1.384	35.15	13	1-644894-3
	1.284	32.61	12	1-644894-2
	1.184	30.07	11	1-644894-1
	1.084	27.53	10	1-644894-0
	.984	24.99	9	644894-9
	.884	22.45	8	644894-8
	.784	19.91	7	644894-7
	.684	17.37	6	644894-6
	.584	14.83	5	644894-5
	.484	12.29	4	644894-4
	.384	9.75	3	644894-3
	.284	7.21	2	644894-2
	IN	MM	NO OF POSITIONS	PART NUMBER
	L		HEADER ASSEMBLY	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN K. WHITAKER 25JUNE2005	CHK D. BOSSI 25JUNE2005	APVD D. BOSSI 25JUNE2005	NAME
0 PLC ± -	1 PLC ± -	2 PLC ± -	3 PLC ± .005	4 PLC ± -	ANGLES ± -
MATERIAL 1	FINISH 7	SIZE A1	CAGE CODE 00779	DRAWING NO. 644894	RESTRICTED TO
CUSTOMER DRAWING		SCALE 10:1	SHEET 1 OF 1	REV G2	

STE TE Connectivity
CST-100 SHROUDED HEADER ASSEMBLY, FRICTION LOCK, RIGHT ANGLE POST, TIN OR TIN LEAD PLATED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[644894-4](#)