


NOTES:
 1 .000030 GOLD ON CONTACT AREA, GOLD FLASH ON SOLDER AREA, ALL OVER .000050 NICKEL
 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED BOARD LAYOUT

POSTS OMITTED	Z	C	B	A	NO OF POSN	PART NUMBER		
2	1,3,6,8,9	1,3,6,7,14	2.79 [1.10]	55.47 [2.184]	53.34 [2.100]	21	44	-4-86479-9-
OBSOLETE	1,3,6,8,9	15,18,20,2	2.79 [1.10]	93.57 [3.684]	91.44 [3.600]	36	74	-4-86479-6-
OBSOLETE	1,9,15	3,11,17	2.79 [1.10]	24.99 [0.984]	22.86 [0.900]	9	20	-4-86479-5-
OBSOLETE	22,24,29,35	4	2.79 [1.10]	101.19 [3.984]	99.06 [3.900]	39	80	4-86479-4
NONE	NONE	NONE	2.79 [1.10]	98.65 [3.884]	96.52 [3.800]	38	78	4-86479-3
NONE	NONE	NONE	2.79 [1.10]	96.11 [3.784]	93.98 [3.700]	37	76	4-86479-2
NONE	NONE	NONE	2.79 [1.10]	93.57 [3.684]	91.44 [3.600]	36	74	4-86479-1
NONE	NONE	NONE	2.79 [1.10]	91.03 [3.584]	88.90 [3.500]	35	72	4-86479-0
NONE	NONE	NONE	2.79 [1.10]	88.49 [3.484]	86.36 [3.400]	34	70	3-86479-9
NONE	NONE	NONE	2.79 [1.10]	85.95 [3.384]	83.82 [3.300]	33	68	3-86479-8
NONE	NONE	NONE	2.79 [1.10]	83.41 [3.284]	81.28 [3.200]	32	66	3-86479-7
NONE	NONE	NONE	2.79 [1.10]	80.87 [3.184]	78.74 [3.100]	31	64	3-86479-6
NONE	NONE	NONE	2.79 [1.10]	78.33 [3.084]	76.20 [3.000]	30	62	3-86479-5
NONE	NONE	NONE	2.79 [1.10]	75.79 [2.984]	73.66 [2.900]	29	60	3-86479-4
NONE	NONE	NONE	2.79 [1.10]	73.25 [2.884]	71.12 [2.800]	28	58	3-86479-3
NONE	NONE	NONE	2.79 [1.10]	70.71 [2.784]	68.58 [2.700]	27	56	3-86479-2
NONE	NONE	NONE	2.79 [1.10]	68.17 [2.684]	66.04 [2.600]	26	54	3-86479-1
NONE	NONE	NONE	2.79 [1.10]	65.63 [2.584]	63.50 [2.500]	25	52	3-86479-0
NONE	NONE	NONE	2.79 [1.10]	63.09 [2.484]	60.96 [2.400]	24	50	2-86479-9
NONE	NONE	NONE	2.79 [1.10]	60.55 [2.384]	58.42 [2.300]	23	48	2-86479-8
NONE	NONE	NONE	2.79 [1.10]	58.01 [2.284]	55.88 [2.200]	22	46	2-86479-7
NONE	NONE	NONE	2.79 [1.10]	55.47 [2.184]	53.34 [2.100]	21	44	2-86479-6
NONE	NONE	NONE	2.79 [1.10]	52.93 [2.084]	50.80 [2.000]	20	42	2-86479-5
NONE	NONE	NONE	2.79 [1.10]	50.39 [1.984]	48.26 [1.900]	19	40	2-86479-4
NONE	NONE	NONE	2.79 [1.10]	47.85 [1.884]	45.72 [1.800]	18	38	2-86479-3
NONE	NONE	NONE	2.79 [1.10]	45.31 [1.784]	43.18 [1.700]	17	36	2-86479-2
NONE	NONE	NONE	2.79 [1.10]	42.77 [1.684]	40.64 [1.600]	16	34	2-86479-1
NONE	NONE	NONE	2.79 [1.10]	40.23 [1.584]	38.10 [1.500]	15	32	2-86479-0
NONE	NONE	NONE	2.79 [1.10]	37.69 [1.484]	35.56 [1.400]	14	30	1-86479-9
NONE	NONE	NONE	2.79 [1.10]	35.15 [1.384]	33.02 [1.300]	13	28	1-86479-8
NONE	NONE	NONE	2.79 [1.10]	32.61 [1.284]	30.48 [1.200]	12	26	1-86479-7
NONE	NONE	NONE	2.79 [1.10]	30.07 [1.184]	27.94 [1.100]	11	24	1-86479-6
NONE	NONE	NONE	2.79 [1.10]	27.53 [1.084]	25.40 [1.000]	10	22	1-86479-5
NONE	NONE	NONE	2.79 [1.10]	24.99 [0.984]	22.86 [0.900]	9	20	1-86479-4
NONE	NONE	NONE	2.79 [1.10]	22.45 [0.884]	20.32 [0.800]	8	18	1-86479-3
NONE	NONE	NONE	2.79 [1.10]	20.00 [0.784]	17.78 [0.700]	7	16	1-86479-2
NONE	NONE	NONE	2.79 [1.10]	17.37 [0.684]	15.24 [0.600]	6	14	1-86479-1
NONE	NONE	NONE	2.79 [1.10]	14.83 [0.584]	12.70 [0.500]	5	12	86479-9
NONE	NONE	NONE	2.79 [1.10]	12.29 [0.484]	10.16 [0.400]	4	10	86479-8
NONE	NONE	NONE	2.79 [1.10]	10.00 [0.384]	7.62 [0.300]	3	8	86479-7
NONE	NONE	NONE	2.79 [1.10]	7.21 [0.284]	5.08 [0.200]	2	6	86479-6
NONE	NONE	NONE	2.79 [1.10]	4.67 [0.184]	2.54 [0.100]	1	4	86479-5
NONE	NONE	NONE	2.79 [1.10]	2.13 [0.084]	-	-	2	86479-4
OBSOLETE	NONE	NONE	2.79 [1.10]	-	-	-	-	86479-3
OBSOLETE	NONE	NONE	2.79 [1.10]	-	-	-	-	86479-2
NONE	NONE	6	2.79 [1.10]	24.99 [0.984]	22.86 [0.900]	9	19	86479-1
NONE	NONE	NONE	2.79 [1.10]	32.61 [1.284]	30.48 [1.200]	12	26	86479-0
SUPERSEDED BY 4-87230-2	NONE	NONE	2.79 [1.10]	-	-	-	-	86479-9
SUPERSEDED BY 4-87230-1	NONE	NONE	2.79 [1.10]	-	-	-	-	86479-8
NONE	NONE	NONE	2.79 [1.10]	30.07 [1.184]	27.94 [1.100]	11	24	86479-7
NONE	NONE	NONE	2.79 [1.10]	22.45 [0.884]	20.32 [0.800]	8	18	86479-6
NONE	NONE	NONE	2.79 [1.10]	17.37 [0.684]	15.24 [0.600]	6	14	86479-5
NONE	NONE	NONE	2.79 [1.10]	14.83 [0.584]	12.70 [0.500]	5	12	86479-4
NONE	NONE	NONE	2.79 [1.10]	12.29 [0.484]	10.16 [0.400]	4	10	86479-3
NONE	NONE	NONE	2.79 [1.10]	10.00 [0.384]	7.62 [0.300]	3	8	86479-2
NONE	NONE	NONE	2.79 [1.10]	7.21 [0.284]	5.08 [0.200]	2	6	86479-1
NONE	NONE	NONE	2.79 [1.10]	4.67 [0.184]	2.54 [0.100]	1	4	86479-0

THIS DRAWING IS A CONTROLLED DOCUMENT.

APPROVED: J. KNAUB 16MAY94
 CHK: J. KNITTLE 17MAY94
 APVD: J. KNITTLE 17MAY94

TE Connectivity

ASSEMBLY, MOD II, DOUBLE ROW
 .100 X .100 CL, RIGHT ANGLE
 WITH SPANKED TAILS

SIZE: A1
 CASE CODE: 00779
 DRAWING NO: 86479
 WEIGHT: -
 CUSTOMER DRAWING

SCALE: 4:1
 SHEET: 1 of 1
 REV: S3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[86479-1](#)