

THIS DRAWING IS A CONTROLLED DOCUMENT. DRAW NO 1583000

TOOL NUMBER 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS				CONTACT DESCRIP.	APPLIC. SPECIF.
							LOOSE PIECE 		STRIP FORM 			
91500-1 91500-3 91500-4 	0.5 - 0.9 [20-18] 1.2 - 2.1 [16-14]	1.52 - 3.30 [.060 - .130]	YES	NO	4.37 ± 0.38 [.172 ± .015]	1.27 ± 0.05 [.050 ± .002] 1.60 ± 0.05 [.063 ± .002]	350547-[] 350550-[] 350669-[] 350705-[] 770250-[] 770251-[] 770254-[]	350218-[] 350536-[] 350654-[] 350687-[] 770007-[] 770008-[] 770193-[]	Univ. MATE-N-LOK Contacts Univ. MATE-N-LOK 2 Contacts	114-1010 & 114-1011 114-1043		
91506-1 91506-3	1.21 - 2.1 [16-14]	3.3 - 5.1 [.130 - .200]	YES	NO	4.37 ± 0.38 [.172 ± .015]	1.60 ± 0.05 [.063 ± .002]	350551-[] 350552-[] 350707-[] 350919-[] 350918-[] 770249-[] 770248-[] 770255-[]	350537-[] 350538-[] 350700-[] 350874-[] 350873-[] 770006-[] 770005-[] 770194-[]	Univ. MATE-N-LOK Contacts Univ. MATE-N-LOK 2 Contacts	114-1010 & 114-1011 114-1043		
91508-1 91508-3	0.5 - 0.9 [20-18]	3.3 - 5.1 [.130 - .200]	YES	NO	4.37 ± 0.38 [.172 ± .015]	1.24 ± 0.05 [.049 ± .002]	350551-[] 350552-[] 350707-[] 350919-[] 350918-[] 770249-[] 770248-[] 770255-[]	350537-[] 350538-[] 350700-[] 350874-[] 350873-[] 770006-[] 770005-[] 770194-[]	Univ. MATE-N-LOK Contacts Univ. MATE-N-LOK 2 Contacts	114-1010 & 114-1011 114-1043		
91510-1 91510-3	0.2 - 0.38 [24-22] 0.5 - 0.9 [20-18]	1.02 - 2.54 [.040 - .100]	YES	NO	4.37 ± 0.38 [.172 ± .015]	1.02 ± 0.05 [.040 ± .002] 1.17 ± 0.05 [.046 ± .002]	350689-[] 350690-[] 350706-[] 640347-[] 770252-[] 770253-[]	350570-[] 350561-[] 350699-[] 350851-[] 770009-[] 770010-[]	Univ. MATE-N-LOK Contacts Univ. MATE-N-LOK 2 Contacts	114-1010 & 114-1011 114-1043		
91522-1 91522-3	0.32 - 0.6 [22-20] (1 wire) 0.8-0.9 [18] (2 wire) 0.31-0.38 [22]	1.50 - 2.2 [.059 - .087] (1 wire) 1.54-2.4 [.059-.095] (2 wire) 1.5-1.7 [.059-.067]	YES	NO	3.45 ± 0.25 [.136 ± .010] (1 wire) 3.45 ± 0.25 [.136 ± .010] (2 wire) 3.7 ± 0.2 [.146 ± .008]	0.79 ± 0.05 [.031 ± .002] 1.04 ± 0.05 [.041 ± .002]	170364-[] 170366-[] 794228-[] 794229-[] 770987-[] 770988-[]	170360-[] 170362-[] 794220-[] 794221-[] 770903-[] 770904-[]	Mini-Univ. MATE-N-LOK Contacts Mini-Univ. MATE-N-LOK 2 Contacts	114-5050 & 114-16017 114-13089		
91529-1 91529-3	0.12 - 0.24 [26-24] 0.32 - 0.38 [22]	1.2 - 1.75 [.047 - .069]	YES	YES	3.45 ± 0.25 [.136 ± .010]	0.69 ± 0.05 [.027 ± .002] 0.79 ± 0.05 [.031 ± .002]	170363-[] 170365-[] 770985-[]	170359-[] 170361-[] 794136-[] 770901-[]	Mini-Univ. MATE-N-LOK Contacts Mini-Univ. MATE-N-LOK 2 Contacts	114-5050 & 114-16017 114-1111 114-13089		
91536-1 91536-3	0.5 - 0.9 [20-18] (1 wire) 1.2-1.4 [16] (2 wire) 0.5-0.6 [20]	2.0 - 3.0 [.079 - .118] (1 wire) 2.5-3.2 [.098-.126] (2 wire) 2.0-2.4 [.079-.094]	YES	NO	3.45 ± 0.25 [.136 ± .010] (1 wire) 3.45 ± 0.25 [.136 ± .010] (2 wire) 3.70 ± 0.20 [.146 ± .008]	1.07 ± 0.05 [.042 ± .002] 1.27 ± 0.05 [.050 ± .002]	171638-[] 171639-[]	171636-[] 171637-[]	Mini-Univ. MATE-N-LOK Contacts	114-5050 & 114-16017		
91594-1 91594-3	0.50-0.89 [20-18] 0.50-1.42x2 [16-20x2]	2.00-3.20 [.079-.126] 2.26-3.20 [.098-.126]	YES	NO	(1 wire) 3.45 ± 0.25 [.136 ± .010] (2 wire) 3.70 ± 0.20 [.146 ± .008]	1.07 ± 0.05 [.042 ± .002] 1.29 ± 0.05 [.051 ± .002]	794230-[] 794231-[]	794222-[] 794223-[] 794406-[] 794407-[]	Mini-Univ. MATE-N-LOK 2 Contacts Mini-Univ. MATE-N-LOK CONTACTS	114-1111 114-16017		

LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

2. AMP, CERTI-CRIMP, and MATE-N-LOK are trademarks.













-1 IS A CERTICRIMP II HAND TOOL ASSEMBLY. -3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.
 SUPERSEDED
 -4 IS A CERTICRIMP II HAND TOOL ASSEMBLY FOR SMALL INSULATION DIAMETER.


6. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET


DWN: M.YOUNGER 21FEB2012		MATERIAL: -		HEAT TREAT: -	
CHK: B.A.WOLFE 22FEB2012		APVD: B.A.WOLFE 22FEB2012		NAME: B.A. WOLFE	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± -	
ANGLE: # - SURFACE TEXTURE: ✓		SCALE: -		SIZE: A1	
P LTR REVISION RECORD		DATE: 10/2019		DWN: AW SS	
1583000		DRAWING NO: 1583000		SHEET: 1 of 2	

THIS DRAWING IS A CONTROLLED DOCUMENT. DRAW NO. 1583000


TOOL NUMBER 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 		CONTACT DESCRIP.	APPLIC. SPECIF.
							LOOSE PIECE 	STRIP FORM 		
 91574-1	0.20-0.56 [24-20]	1.52-2.54 [.060-.100]	YES	NO	5.16 ± 0.38 [.203 ± .015]	1.05 ± 0.08 [.041 ± .003]	350689-[] 350690-[] 350706-[]	350570-[] 350561-[] 350699-[]	Universal MATE-N-LOK Contacts	114-1010 & 114-1011
	0.75-0.89 [18]					1.27 ± 0.08 [.050 ± .003]				
 91575-1 91575-3	0.50-0.89 [20-18]	2.54-3.31 [.100-.130]	YES	NO	5.16 ± 0.38 [.203 ± .015]	1.29-1.45 [.051-.057]	350547-[] 350705-[] 350669-[] 350550-[]	350218-[] 350687-[] 350564-[] 350536-[]	Universal MATE-N-LOK Contacts	114-1010 & 114-1011
	0.75+0.75 OR 0.75+1.25 [18+18 OR 18+16]					1.60-1.75 [.063-.069]				
1976176-1	18 GA SOLID	1.02-2.54 [.040-.100]	YES	NO	4.37-0.38 [.172-.015]	1.18 ± .025 [.044 ± .001]	350689-[] 350550-[] 350690-[] 350547-[]	350851-[] 350536-[] 350561-[] 350218-[]	Universal MATE-N-LOK Contacts	114-1010 & 114-1011
2280977-1	0.12-0.24 [26-24]	1.19-1.60 [.047-.063]	YES	NO	3.45 ± 0.25 [.136 ± .010]	0.68 ± 0.05 [.027 ± .002]	794226-[] 794227-[]	794218-[] 794219-[]	MINI UNERVERSAL MATE-N-LOK2 Contacts	114-5050
	0.32-0.38 [22]	1.50-1.75 [.059-.069]				0.79 ± 0.05 [.031 ± .002]				
2217759-1	0.05-0.15 [30-26]	0.81-1.45 [.032-.057]	YES	NO	3.68-4.32 [.145-.170]	0.71 ± 0.05 [.028 ± .002]	770416-[] 770512-[] 770672-[] 770673-[]	350924-[] 350925-[] 794042-[] 770011-[] 770012-[]	Universal MATE N LOCK Universal MATE N LOCK II	114-1010 & 114-1043
2326453-1	0.32-0.60 [22-20]	1.50-2.01 [.059-.079]	YES	NO	3.45±0.25 [.136±.001]	0.79 ± 0.05 [.031 ± .002]	-	2825156-1 2825157-1	Mini-Univ. MATE-N-LOK Contacts	114-16017
	0.81-0.96 [18]	2.01-2.18 [.079-.089]				1.04 ± 0.05 [.041 ± .002]				
2326016-1	0.32-0.60 [22-20]	1.50-2.01 [.059-.079]	YES	NO	3.45 ± 0.25 [.136 ± .001]	0.79 ± 0.05 [.031 ± .002]	-	2825156-1 2825157-1	MINI UNERVERSAL MATE-N-LOK2 Contacts	114-16017
	0.81-0.96 [18]	2.11-2.39 [.083-.094]				1.04 ± 0.05 [.041 ± .002]				
2326016-2	0.32-0.60 [22-20]	1.50-2.01 [.059-.079]	YES	NO	3.45 ± 0.25 [.136 ± .001]	0.79 ± 0.05 [.031 ± .002]	770987-[] 770988-[]	770904-[] 770903-[]	Universal MATE N LOCK	114-16017
	0.60-0.96 [18]	2.11-2.39 [.083-.094]				1.04 ± 0.05 [.041 ± .002]				

 LIST OF APPLIED CONTACT PART NUMBERS MAY NOT BE COMPLETE AND IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION ON TERMINAL PART NUMBERS, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.

2. AMP, CERTI-CRIMP, and MATE-N-LOK are trademarks.


 -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY. -3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.

 SUPERSEDED

 -4 IS A CERTICRIMP II HAND TOOL ASSEMBLY FOR SMALL INSULATION DIAMETER.

6. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DRAWN: M. YOUNGER 21FEB2012	MATERIAL: -	HEAT TREAT: -
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± -	CHK: B.A. WOLFE 22FEB2012		
		APVD: B.A. WOLFE 22FEB2012	 TE Connectivity	
NAME: CERTI-CRIMP II TOOL DATA SHEET UNIVERSAL MATE-N-LOK CONTACT FAMILY		SCALE: -	SIZE: A1	DRAWING NO: 1583000
REVISION RECORD		DATE	DN	APVD
P	LTR			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[91510-1](#)