


LOC	DIST	REVISIONS					
AD	39	P	LTR	DESCRIPTION	DATE	DWN	APVD
			0	RELEASED	12-NOV-96	EB	GD

1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
4. HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
5. FINISH: 0.000381 [0.000015] GOLD ON CONTACT AREA, OVER 0.00127 [0.000050] NICKEL, ENTIRE POST.



01.19	99.06	39	80	4-146507-0
[3.984]	[3.900]			
98.65	96.52	38	78	3-146507-9
[3.884]	[3.800]			
96.11	93.98	37	76	3-146507-8
[3.784]	[3.700]			
93.57	91.44	36	74	3-146507-7
[3.684]	[3.600]			
91.03	88.90	35	72	3-146507-6
[3.584]	[3.500]			
88.49	86.36	34	70	3-146507-5
[3.484]	[3.400]			
85.95	83.82	33	68	3-146507-4
[3.384]	[3.300]			
83.41	81.28	32	66	3-146507-3
[3.284]	[3.200]			
80.87	78.74	31	64	3-146507-2
[3.184]	[3.100]			
78.33	76.20	30	62	3-146507-1
[3.084]	[3.000]			
75.79	73.66	29	60	3-146507-0
[2.984]	[2.900]			
73.25	71.12	28	58	2-146507-9
[2.884]	[2.800]			
70.71	68.58	27	56	2-146507-8
[2.784]	[2.700]			
68.17	66.04	26	54	2-146507-7
[2.684]	[2.600]			
65.63	63.50	25	52	2-146507-6
[2.584]	[2.500]			
63.09	60.96	24	50	2-146507-5
[2.484]	[2.400]			
60.55	58.42	23	48	2-146507-4
[2.384]	[2.300]			
58.01	55.88	22	46	2-146507-3
[2.284]	[2.200]			
55.47	53.34	21	44	2-146507-2
[2.184]	[2.100]			
52.93	50.80	20	42	2-146507-1
[2.084]	[2.000]			
50.39	48.26	19	40	2-146507-0
[1.984]	[1.900]			
47.85	45.72	18	38	1-146507-9
[1.884]	[1.800]			
45.31	43.18	17	36	1-146507-8
[1.784]	[1.700]			
42.77	40.64	16	34	1-146507-7
[1.684]	[1.600]			
40.23	38.10	15	32	1-146507-6
[1.584]	[1.500]			
37.69	35.56	14	30	1-146507-5
[1.484]	[1.400]			
35.15	33.02	13	28	1-146507-4
[1.384]	[1.300]			
32.61	30.48	12	26	1-146507-3
[1.284]	[1.200]			
30.07	27.94	11	24	1-146507-2
[1.184]	[1.100]			
27.53	25.40	10	22	1-146507-1
[1.084]	[1.000]			
24.99	22.86	9	20	1-146507-0
[.984]	[.900]			
22.45	20.32	8	18	146507-9
[.884]	[.800]			
19.91	17.78	7	16	146507-8
[.784]	[.700]			
17.37	15.24	6	14	146507-7
[.684]	[.600]			
14.83	12.70	5	12	146507-6
[.584]	[.500]			
12.29	10.16	4	10	146507-5
[.484]	[.400]			
9.75	7.62	3	8	146507-4
[.384]	[.300]			
7.21	5.08	2	6	146507-3
[.284]	[.200]			
4.67	2.54	1	4	146507-2
[.184]	[.100]			
2.13	-	-	2	146507-1
[.084]	-			
G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTINUATION OF DRAWING FOR AMP MICROELECTRONICS. ALL DIMENSIONS ARE GIVEN IN INCHES AND DECIMALS THEREOF. DIMENSIONS SHOULD BE OBTAINED FOR THE LATEST REVISION.		DWN 12-NOV-56 E. BRANDBERG CIG, DUBNICKI 12-NOV-56 AMP AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm (INCH)		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 P L C ±- 1 P L C ±- 2 ±- .051(.023) 3 ±- .0127(.005) 4 P L C ±- .0127(.0005) ANGLES FINISH	
MATERIAL 		APPLICATION SPEC WEIGHT - CUSTOMER DRAWING	
		NAME HEADER ASSEMBLY, MOD II, STACKING, DOUBLE ROW, .025 SQ. POST, UNSHROUDED	
		SIZE A1	CASE CODE 00779
		DRAWING NO. C-146507	
		SCALE 4:1	SHEET 1 of 1
		REV 0	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-146507-7](#)