


REVISONS		DATE	OWN	APVD
NO.	DESCRIPTION			
0	RELEASED	12-NOV-96	EB	GD

- ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
 - TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- Δ THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
 Δ HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
 Δ FINISH: 0.000381 [0.000015] GOLD ON CONTACT AREA, OVER 0.00127 [0.000050] NICKEL, ENTIRE POST.



RECOMMENDED HOLE LAYOUT

LOC	DIST	NO. OF POSITIONS	PART NUMBER
101.19	99.06	39	4-146507-0
[3.984]	[3.900]		
98.65	96.52	38	3-146507-9
[3.884]	[3.800]		
96.11	93.98	37	3-146507-8
[3.784]	[3.700]		
93.57	91.44	36	3-146507-7
[3.684]	[3.600]		
91.03	88.90	35	3-146507-6
[3.584]	[3.500]		
88.49	86.36	34	3-146507-5
[3.484]	[3.400]		
85.95	83.82	33	3-146507-4
[3.384]	[3.300]		
83.41	81.28	32	3-146507-3
[3.284]	[3.200]		
80.87	78.74	31	3-146507-2
[3.184]	[3.100]		
78.33	76.20	30	3-146507-1
[3.084]	[3.000]		
75.79	73.66	29	3-146507-0
[2.984]	[2.900]		
73.25	71.12	28	2-146507-9
[2.884]	[2.800]		
70.71	68.58	27	2-146507-8
[2.784]	[2.700]		
68.17	66.04	26	2-146507-7
[2.684]	[2.600]		
65.63	63.50	25	2-146507-6
[2.584]	[2.500]		
63.09	60.96	24	2-146507-5
[2.484]	[2.400]		
60.55	58.42	23	2-146507-4
[2.384]	[2.300]		
58.01	55.88	22	2-146507-3
[2.284]	[2.200]		
55.47	53.34	21	2-146507-2
[2.184]	[2.100]		
52.93	50.80	20	2-146507-1
[2.084]	[2.000]		
50.39	48.26	19	2-146507-0
[1.984]	[1.900]		
47.85	45.72	18	1-146507-9
[1.884]	[1.800]		
45.31	43.18	17	1-146507-8
[1.784]	[1.700]		
42.77	40.64	16	1-146507-7
[1.684]	[1.600]		
40.23	38.10	15	1-146507-6
[1.584]	[1.500]		
37.69	35.56	14	1-146507-5
[1.484]	[1.400]		
35.15	33.02	13	1-146507-4
[1.384]	[1.300]		
32.61	30.48	12	1-146507-3
[1.284]	[1.200]		
30.07	27.94	11	1-146507-2
[1.184]	[1.100]		
27.53	25.40	10	1-146507-1
[1.084]	[1.000]		
24.99	22.86	9	1-146507-0
[0.984]	[0.900]		
22.45	20.32	8	146507-9
[0.884]	[0.800]		
19.91	17.78	7	146507-8
[0.784]	[0.700]		
17.37	15.24	6	146507-7
[0.684]	[0.600]		
14.83	12.70	5	146507-6
[0.584]	[0.500]		
12.29	10.16	4	146507-5
[0.484]	[0.400]		
9.75	7.62	3	146507-4
[0.384]	[0.300]		
7.21	5.08	2	146507-3
[0.284]	[0.200]		
4.67	2.54	1	146507-2
[0.184]	[0.100]		
2.13	-	-	146507-1
[0.084]	-	-	

<small>THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP TECHNOLOGIES. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHALL BE CONTACTED FOR THE LATEST REVISION.</small>		DWN: BRANDBERG 12-NOV-96 CHK: G. DUBNICKI 12-NOV-96 APVD: G. DUBNICKI 12-NOV-96	AMP Incorporated Harrisburg, PA 17105-3508
DIMENSIONS: mm (INCH)	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.51 (L.02) 2 PLC ±0.127 (L.005) 3 PLC ±0.0127 (L.0005) 4 PLC ±- ANGLES ±-	NAME: HEADER ASSEMBLY, MOD 11, STACKING, DOUBLE ROW, .025 SQ. POST, UNSHROUDED APPLICATION SPEC: - PRODUCT SPEC: -	SIZE: A1 CAGE CODE: 00779 DRAWING NO: 146507
MATERIAL: Δ	FINISH: Δ	WEIGHT: -	SCALE: 4:1
CUSTOMER DRAWING		SHEET: 1 OF 1	REV: 0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-146507-9](#)