


COIL: @ 25°C
 RESISTANCE 1600 OHMS ± 10%
 NOMINAL VOLTAGE 35.0-50.0 VDC
 MUST OPERATE 24.0 VDC
 MUST RELEASE 15.0 VDC MAX. 4.7 VDC MIN.

ENVIRONMENT:
 VIBRATION 10 CPS TO 2000 CPS @ 30 g's
 SHOCK 100 g's 11 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 5 MS MAX.
RELEASE 4 MS MAX.
BOUNCE 2.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2 AMPS
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 5/9/97 CK *5/20/97*

COMMUNICATIONS INSTRUMENTS, INC.

CUST. GENICOM
 CUST. NO. 3SAF5062N1

TYPE "FW" RELAY

FW11133S02

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[FW11133S02](#)