


- 1 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 2 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- 3 .000100-.000200 MATTE TIN-LEAD OVER .000050 NICKEL.
- 4 .000100-.000200 BRIGHT TIN OVER .000050 NICKEL.
- 5 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- 6 HOUSING MATERIAL: FLAME RETARDANT THERMOPLASTIC; COLOR-BLACK.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



△	△	1.684	1.600	16	34	4-103322-7	
△	△	1.184	1.100	11	24	4-103322-6	
△	△	.584	.500	5	12	4-103322-5	
△	△	.284	.200	2	6	4-103322-4	
△	△	.084	—	—	2	4-103322-3	
△	△	3.984	3.900	39	80	4-103322-2	
△	△	.484	.400	4	10	4-103322-1	
△	△	3.984	3.900	39	80	4-103322-0	
△	△	3.884	3.800	38	78	3-103322-9	
△	△	3.784	3.700	37	76	3-103322-8	
△	△	3.684	3.600	36	74	3-103322-7	
△	△	SUPERSEDED BY 8-146250-6	3.584	3.500	35	72	3-103322-6
△	△	OBSOLETE	3.484	3.400	34	70	3-103322-5
△	△	OBSOLETE	3.384	3.300	33	68	3-103322-4
△	△	OBSOLETE	3.284	3.200	32	66	3-103322-3
△	△	OBSOLETE	3.184	3.100	31	64	3-103322-2
△	△	OBSOLETE	3.084	3.000	30	62	3-103322-1
△	△	OBSOLETE	2.984	2.900	29	60	3-103322-0
△	△	OBSOLETE	2.884	2.800	28	58	2-103322-9
△	△	OBSOLETE	2.784	2.700	27	56	2-103322-8
△	△	OBSOLETE	2.684	2.600	26	54	2-103322-7
△	△	OBSOLETE	2.584	2.500	25	52	2-103322-6
△	△	OBSOLETE	2.484	2.400	24	50	2-103322-5
△	△	OBSOLETE	2.384	2.300	23	48	2-103322-4
△	△	OBSOLETE	2.284	2.200	22	46	2-103322-3
△	△	OBSOLETE	2.184	2.100	21	44	2-103322-2
△	△	OBSOLETE	2.084	2.000	20	42	2-103322-1
△	△	SUPERSEDED BY 7-146250-0	1.984	1.900	19	40	2-103322-0
△	△	OBSOLETE	1.884	1.800	18	38	1-103322-9
△	△	OBSOLETE	1.784	1.700	17	36	1-103322-8
△	△	OBSOLETE	1.684	1.600	16	34	1-103322-7
△	△	OBSOLETE	1.584	1.500	15	32	1-103322-6
△	△	OBSOLETE	1.484	1.400	14	30	1-103322-5
△	△	OBSOLETE	1.384	1.300	13	28	1-103322-4
△	△	OBSOLETE	1.284	1.200	12	26	1-103322-3
△	△	OBSOLETE	1.184	1.100	11	24	1-103322-2
△	△	OBSOLETE	1.084	1.000	10	22	1-103322-1
△	△	SUPERSEDED BY 6-146250-0	.984	.900	9	20	1-103322-0
△	△	OBSOLETE	.884	.800	8	18	103322-9
△	△	OBSOLETE	.784	.700	7	16	103322-8
△	△	OBSOLETE	.684	.600	6	14	103322-7
△	△	OBSOLETE	.584	.500	5	12	103322-6
△	△	OBSOLETE	.484	.400	4	10	103322-5
△	△	OBSOLETE	.384	.300	3	8	103322-4
△	△	OBSOLETE	.284	.200	2	6	103322-3
△	△	OBSOLETE	.184	.100	1	4	103322-2
△	△	SUPERSEDED BY 5-146250-1	.084	—	—	2	103322-1

PLATING	C	B	A	NO OF POSN	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: INCHES. TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± - MATERIAL: POST: COPPER ALLOY FINISH: SEE TABLE WEIGHT: — SIZE: A1 CAGE CODE: 00779 DRAWING NO: 103322 RESTRICTED TO: — CUSTOMER DRAWING SCALE: 4:1 SHEET 1 OF 1 REV L					

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103322-5](#)