



LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E3	REVISED PER ECO-11-005027	16MAR2011	RK	HMR
			E4	TOLERANCES UPDATED	16JAN2018	FP	PS




CLAMPING SCREW

L

POLARIZATION KEY SLOT

- | | | | | | |
|-------------|----------------|--------------|-------|------------|-------------|
| PRELIMINARY | .762μm GOLD | | 40.0 | 8 | 4-796641-4 |
| | TIN | SEE DETAIL T | 25.0 | 5 | 4-796641-2 |
| PRELIMINARY | TIN | SEE DETAIL S | 60.0 | 12 | 4-796641-1 |
| PRELIMINARY | TIN | SEE DETAIL R | 50.0 | 10 | 4-796641-0 |
| PRELIMINARY | TIN | SEE DETAIL P | 20.0 | 4 | 3-796641-9 |
| | TIN | SEE DETAIL N | 40.0 | 8 | 3-796641-8 |
| | TIN | SEE DETAIL M | 30.0 | 6 | 3-796641-6 |
| | TIN | SEE DETAIL L | 10.0 | 2 | 3-796641-2 |
| | TIN | | 125.0 | 25 | 2-796641-5 |
| | TIN | | 120.0 | 24 | 2-796641-4 |
| | TIN | | 115.0 | 23 | 2-796641-3 |
| | TIN | | 110.0 | 22 | 2-796641-2 |
| | TIN | | 105.0 | 21 | 2-796641-1 |
| | TIN | | 100.0 | 20 | 2-796641-0 |
| | TIN | | 95.0 | 19 | 1-796641-9 |
| | TIN | | 90.0 | 18 | 1-796641-8 |
| | TIN | | 85.0 | 17 | 1-796641-7 |
| | TIN | | 80.0 | 16 | 1-796641-6 |
| | TIN | | 75.0 | 15 | 1-796641-5 |
| | TIN | | 70.0 | 14 | 1-796641-4 |
| | TIN | | 65.0 | 13 | 1-796641-3 |
| | TIN | | 60.0 | 12 | 1-796641-2 |
| | TIN | | 55.0 | 11 | 1-796641-1 |
| | TIN | | 50.0 | 10 | 1-796641-0 |
| | TIN | | 45.0 | 9 | 796641-9 |
| | TIN | | 40.0 | 8 | 796641-8 |
| | TIN | | 35.0 | 7 | 796641-7 |
| | TIN | | 30.0 | 6 | 796641-6 |
| | TIN | | 25.0 | 5 | 796641-5 |
| | TIN | | 20.0 | 4 | 796641-4 |
| | TIN | | 15.0 | 3 | 796641-3 |
| | TIN | | 10.0 | 2 | 796641-2 |
| | CONTACT FINISH | MARKING | DIM L | NO OF POSN | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 180CT2000 S. WELDON CHK 180CT2000 D. BIEVENOUR APVD 180CT2000 D. BIEVENOUR		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± 1 PLC ±0.3 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		TERMI-BLOK PLUG, STACKING, 5.00mm PITCH -	
MATERIAL		WEIGHT		SIZE	CAGE CODE
		-		A2	00779
		CUSTOMER DRAWING		DRAWING NO	RESTRICTED TO
				C-796641	-
				SCALE	SHEET
				4:1	1 of 2
				REV	E4

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC
FT

DIST
0

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		- SEE SHEET 1	-	-	-

1

2

DETAIL L

SCALE 4:1

1

2

3

4

5

6

DETAIL M

SCALE 4:1

1

2

3

4

DETAIL P

SCALE 4:1

1

2

3

4

5

DETAIL T

SCALE 4:1

1

2

3

4

5

6

7

8

DETAIL N

SCALE 4:1

1

2

3

4

5

6

7

8

9

10

DETAIL R

SCALE 4:1

1

2

3

4

5

6

7

8

9

10

11

12

DETAIL S

SCALE 4:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.3

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH

DWN
S. WELDON 18OCT2000

CHK
D. BIEVENOUR 18OCT2000

APVD
D. BIEVENOUR 18OCT2000

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
TERMI-BLOK PLUG, STACKING,
5.00mm PITCH

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-796641

RESTRICTED TO
-

SCALE
4:1

SHEET
2

OF
2

REV
E4

1471-9 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-796641-2](#)