





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		J		EC 0G3C 0759 04	02FEB05	BSV	JLG
		J1		REVISED PER ECO-09-020689	02SEP09	KK	AEG



EXMPL: STRIP ASSEMBLY
SCALE 2:1

PLATING	NO OF POSN	HOUSING PART NUMBER	A	B	ASSEMBLY PART NUMBER ON STRIP	
10	2	2.40	1.198	1-103648-1	12	6-103976-1
10	2	2.20	1.098	1-103648-0	11	6-103976-0
11 OBSOLETE	2	2.00	.998	103648-9	10	5-103971-9
11 OBSOLETE	2	1.80	.898	103648-8	9	5-103971-8
10	2	1.60	.798	103648-7	8	5-103971-7
11 OBSOLETE	2	1.40	.698	103648-6	7	5-103971-6
11 OBSOLETE	4	2.39	.598	103648-5	6	5-103971-5
10	4	1.99	.498	103648-4	5	5-103971-4
10	5	1.99	.398	103648-3	4	5-103971-3
10	8	2.40	.298	103648-2	3	5-103971-2
10	10	2.00	.198	103648-1	2	5-103971-1
11 OBSOLETE	2	2.40	1.198	1-103648-1	12	1-103971-1
11 OBSOLETE	2	2.20	1.098	1-103648-0	11	1-103971-0
11 OBSOLETE	2	2.00	.998	103648-9	10	103971-9
11 OBSOLETE	2	1.80	.898	103648-8	9	103971-8
11 SUPERSEDED	2	1.60	.798	103648-7	8	103971-7
11 OBSOLETE	2	1.40	.698	103648-6	7	103971-6
11 OBSOLETE	4	2.39	.598	103648-5	6	103971-5
9	4	1.99	.498	103648-4	5	103971-4
9	5	1.99	.398	103648-3	4	103971-3
9	8	2.40	.298	103648-2	3	103971-2
9	10	2.00	.198	103648-1	2	103971-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN L. MAYER 05 NOV 1986
 CHK P.C.DEJONG 12-11-86
 APVD P.C.DEJONG 12-11-86

TOLERANCES UNLESS OTHERWISE SPECIFIED:
 0 PLC ± -
 1 PLC ± -
 2 PLC ± .02
 3 PLC ± .005
 4 PLC ± -
 ANGLES ± -

MATERIAL HOUSING: FLAME RETARDANT THERMOPLASTIC. COLOR:BLACK. CONTACTS: PHOS BRONZE

FINISH SEE TABLE

108-25034
 APPLICATION SPEC
 114-25026

WEIGHT -

CUSTOMER DRAWING

Tyco Electronics Corporation
 Harrisburg, Pa 17105-3608

RCPT ASSY, AMPMODU MTE, SINGLE ROW, .100 CL, WITH GUIDE RIBS, FOR #26-#30 AWG WIRE SIZE, STRIP FORM

SIZE A2 CAGE CODE 00779 DRAWING NO C=103971 RESTRICTED TO -

SCALE 4:1 SHEET 1 OF 1 REV J1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103971-3](#)