

THIS DRAWING IS A CONTROLLED DOCUMENT

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES (TE). IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE PERSONNEL, WITHOUT AUTHORIZATION FROM TE (www.TE.com).

STANADARD MODULE


GROUNDING MODULE

CONNECTOR TYPE DMC-M

ARRANGEMENT 01-08

CONTACTS
P = Standard Male Contact
A = Without Male Contact

POLARIZATION
N, A, B, C, D


SEALING (Optional)
Omit - Standard (No Sealing)
E = Sealed 

CONNECTOR TYPE DMC-M








ARRANGEMENT 01-08

CONTACTS
P = Standard Male Contact
A = Without Male Contact

POLARIZATION
N, A, B, C, D

GROUNDING
G 

PLATING/FINISH (Optional)
Aluminium Alloy
Omit - Black Nickel
W - Olive Drab Cadmium



CHARACTERISTIQUES


TEMPERATURE D'UTILISATION : -55°C a +175°C



MATERIAUX : Thermoplastique et silicone fluore


TENSION DE TENUE : 1800 V eff. ; 50 Hz

Ø SUR GAINÉ CABLES ADMISSIBLES : 3.80 a 5.15 mm

UTILISATION CONTACTS : Contact DataBus (182-0034-03) ; Contact de Puissance (182-0001-08)

 Marquages realises sur la face opposee aux clés

DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC	±-
		1 PLC	±-0.05
		2 PLC	±-0.05
		3 PLC	±-0.02
		4 PLC	±-
ANGLES	±-°		
SURFACE TEXTURE			

DWN	LAKSHMI SUDHA R	MATERIAL	-	HEAT TREAT	-
CHK	RAKESH S	 TE Connectivity			
APVD	VINCENT P				
NAME	MODULE P & A				
SCALE	3:1	SIZE	A3	DRAWING NO	DMC-M_01-08_P+
		SHEET	1 OF 1	REV	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[ZPF00000000015173](#)