



| REVISIONS | | | | | |
|-----------|---------------------------|-------------|-----------|----|------|
| P | LTR | DESCRIPTION | DATE | DN | APVO |
| H1 | REVISED PER ECO-16-012733 | | 01SEP2016 | NK | MM |

- ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.
- PLATING: 0.00254-0.00508 [.000100-.000200] MATTE TIN LEAD, OVER 0.00127 [.000050] NICKEL.
- HOUSING: LCP, COLOR-BLACK. POSTS: COPPER ALLOY.
- PLATING: 0.00254-0.00508 [.000100-.000200] MATTE TIN OVER 0.00127 [.000050] NICKEL.
- OBsolete PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.



RECOMMENDED PC BOARD MOUNTING DIMENSIONS FOR .063 [.160] THICK PC BOARD AND .012 [.305] STENCIL THICK.

| PLATING | C | B | A | NO. OF POSITIONS | PART NUMBER |
|---------|----------------|---------------|----|------------------|-------------|
| 6 | 101.19 [3.984] | 99.06 [3.900] | 39 | 40 | 9-146278-0 |
| 6 | 98.65 [3.884] | 96.52 [3.800] | 38 | 39 | 7-146278-9 |
| 6 | 96.11 [3.784] | 93.98 [3.700] | 37 | 38 | 7-146278-8 |
| 6 | 93.57 [3.684] | 91.44 [3.600] | 36 | 37 | 7-146278-7 |
| 6 | 91.03 [3.584] | 88.90 [3.500] | 35 | 36 | 7-146278-6 |
| 6 | 88.49 [3.484] | 86.36 [3.400] | 34 | 35 | 7-146278-5 |
| 6 | 85.95 [3.384] | 83.82 [3.300] | 33 | 34 | 7-146278-4 |
| 6 | 83.41 [3.284] | 81.28 [3.200] | 32 | 33 | 7-146278-3 |
| 6 | 80.87 [3.184] | 78.74 [3.100] | 31 | 32 | 7-146278-2 |
| 6 | 78.33 [3.084] | 76.20 [3.000] | 30 | 31 | 7-146278-1 |
| 6 | 75.79 [2.984] | 73.66 [2.900] | 29 | 30 | 7-146278-0 |
| 6 | 73.25 [2.884] | 71.12 [2.800] | 28 | 29 | 7-146278-9 |
| 6 | 70.71 [2.784] | 68.58 [2.700] | 27 | 28 | 7-146278-8 |
| 6 | 68.17 [2.684] | 66.04 [2.600] | 26 | 27 | 7-146278-7 |
| 6 | 65.63 [2.584] | 63.50 [2.500] | 25 | 26 | 7-146278-6 |
| 6 | 63.09 [2.484] | 60.96 [2.400] | 24 | 25 | 7-146278-5 |
| 6 | 60.55 [2.384] | 58.42 [2.300] | 23 | 24 | 7-146278-4 |
| 6 | 58.01 [2.284] | 55.88 [2.200] | 22 | 23 | 7-146278-3 |
| 6 | 55.47 [2.184] | 53.34 [2.100] | 21 | 22 | 7-146278-2 |
| 6 | 52.93 [2.084] | 50.80 [2.000] | 20 | 21 | 7-146278-1 |
| 6 | 50.39 [1.984] | 48.26 [1.900] | 19 | 20 | 7-146278-0 |
| 6 | 47.85 [1.884] | 45.72 [1.800] | 18 | 19 | 6-146278-9 |
| 6 | 45.31 [1.784] | 43.18 [1.700] | 17 | 18 | 6-146278-8 |
| 6 | 42.77 [1.684] | 40.64 [1.600] | 16 | 17 | 6-146278-7 |
| 6 | 40.23 [1.584] | 38.10 [1.500] | 15 | 16 | 6-146278-6 |
| 6 | 37.69 [1.484] | 35.56 [1.400] | 14 | 15 | 6-146278-5 |
| 6 | 35.15 [1.384] | 33.02 [1.300] | 13 | 14 | 6-146278-4 |
| 6 | 32.61 [1.284] | 30.48 [1.200] | 12 | 13 | 6-146278-3 |
| 6 | 30.07 [1.184] | 27.94 [1.100] | 11 | 12 | 6-146278-2 |
| 6 | 27.53 [1.084] | 25.40 [1.000] | 10 | 11 | 6-146278-1 |
| 6 | 24.99 [.984] | 22.86 [.900] | 9 | 10 | 6-146278-0 |
| 6 | 22.45 [.884] | 20.32 [.800] | 8 | 9 | 5-146278-9 |
| 6 | 19.91 [.784] | 17.78 [.700] | 7 | 8 | 5-146278-8 |
| 6 | 17.37 [.684] | 15.24 [.600] | 6 | 7 | 5-146278-7 |
| 6 | 14.83 [.584] | 12.70 [.500] | 5 | 6 | 5-146278-6 |
| 6 | 12.29 [.484] | 10.16 [.400] | 4 | 5 | 5-146278-5 |
| 6 | 9.75 [.384] | 7.62 [.300] | 3 | 4 | 5-146278-4 |
| 6 | 7.21 [.284] | 5.08 [.200] | 2 | 3 | 5-146278-3 |
| 6 | 4.67 [.184] | 2.54 [.100] | 1 | 2 | 5-146278-2 |
| 6 | 2.13 [.084] | [-] | 0 | 1 | 5-146278-1 |

| PLATING | C | B | A | NO. OF POSITIONS | PART NUMBER |
|---------|----------------|---------------|----|------------------|-------------|
| 4 | 101.19 [3.984] | 99.06 [3.900] | 39 | 40 | 4-146278-0 |
| 4 | 98.65 [3.884] | 96.52 [3.800] | 38 | 39 | 3-146278-9 |
| 4 | 96.11 [3.784] | 93.98 [3.700] | 37 | 38 | 3-146278-8 |
| 4 | 93.57 [3.684] | 91.44 [3.600] | 36 | 37 | 3-146278-7 |
| 4 | 91.03 [3.584] | 88.90 [3.500] | 35 | 36 | 3-146278-6 |
| 4 | 88.49 [3.484] | 86.36 [3.400] | 34 | 35 | 3-146278-5 |
| 4 | 85.95 [3.384] | 83.82 [3.300] | 33 | 34 | 3-146278-4 |
| 4 | 83.41 [3.284] | 81.28 [3.200] | 32 | 33 | 3-146278-3 |
| 4 | 80.87 [3.184] | 78.74 [3.100] | 31 | 32 | 3-146278-2 |
| 4 | 78.33 [3.084] | 76.20 [3.000] | 30 | 31 | 3-146278-1 |
| 4 | 75.79 [2.984] | 73.66 [2.900] | 29 | 30 | 3-146278-0 |
| 4 | 73.25 [2.884] | 71.12 [2.800] | 28 | 29 | 2-146278-9 |
| 4 | 70.71 [2.784] | 68.58 [2.700] | 27 | 28 | 2-146278-8 |
| 4 | 68.17 [2.684] | 66.04 [2.600] | 26 | 27 | 2-146278-7 |
| 4 | 65.63 [2.584] | 63.50 [2.500] | 25 | 26 | 2-146278-6 |
| 4 | 63.09 [2.484] | 60.96 [2.400] | 24 | 25 | 2-146278-5 |
| 4 | 60.55 [2.384] | 58.42 [2.300] | 23 | 24 | 2-146278-4 |
| 4 | 58.01 [2.284] | 55.88 [2.200] | 22 | 23 | 2-146278-3 |
| 4 | 55.47 [2.184] | 53.34 [2.100] | 21 | 22 | 2-146278-2 |
| 4 | 52.93 [2.084] | 50.80 [2.000] | 20 | 21 | 2-146278-1 |
| 4 | 50.39 [1.984] | 48.26 [1.900] | 19 | 20 | 2-146278-0 |
| 4 | 47.85 [1.884] | 45.72 [1.800] | 18 | 19 | 1-146278-9 |
| 4 | 45.31 [1.784] | 43.18 [1.700] | 17 | 18 | 1-146278-8 |
| 4 | 42.77 [1.684] | 40.64 [1.600] | 16 | 17 | 1-146278-7 |
| 4 | 40.23 [1.584] | 38.10 [1.500] | 15 | 16 | 1-146278-6 |
| 4 | 37.69 [1.484] | 35.56 [1.400] | 14 | 15 | 1-146278-5 |
| 4 | 35.15 [1.384] | 33.02 [1.300] | 13 | 14 | 1-146278-4 |
| 4 | 32.61 [1.284] | 30.48 [1.200] | 12 | 13 | 1-146278-3 |
| 4 | 30.07 [1.184] | 27.94 [1.100] | 11 | 12 | 1-146278-2 |
| 4 | 27.53 [1.084] | 25.40 [1.000] | 10 | 11 | 1-146278-1 |
| 4 | 24.99 [.984] | 22.86 [.900] | 9 | 10 | 1-146278-0 |
| 4 | 22.45 [.884] | 20.32 [.800] | 8 | 9 | 1-146278-9 |
| 4 | 19.91 [.784] | 17.78 [.700] | 7 | 8 | 1-146278-8 |
| 4 | 17.37 [.684] | 15.24 [.600] | 6 | 7 | 1-146278-7 |
| 4 | 14.83 [.584] | 12.70 [.500] | 5 | 6 | 1-146278-6 |
| 4 | 12.29 [.484] | 10.16 [.400] | 4 | 5 | 1-146278-5 |
| 4 | 9.75 [.384] | 7.62 [.300] | 3 | 4 | 1-146278-4 |
| 4 | 7.21 [.284] | 5.08 [.200] | 2 | 3 | 1-146278-3 |
| 4 | 4.67 [.184] | 2.54 [.100] | 1 | 2 | 146278-2 |
| 4 | 2.13 [.084] | [-] | 0 | 1 | 146278-1 |

THIS DRAWING IS A CONTROLLED DOCUMENT.

| | | | | | | | |
|-------------------------|--|-----------|-----------|-------------------|--------------------|----------------------|------------|
| DIMENSIONS: mm [INCHES] | TOLERANCES UNLESS OTHERWISE SPECIFIED: | 0 PLC ± - | 1 PLC ± - | 2 PLC ± 0.51[.02] | 3 PLC ± 0.12[.005] | 4 PLC ± 0.012[.0005] | ANGLES ± - |
|-------------------------|--|-----------|-----------|-------------------|--------------------|----------------------|------------|

MATERIAL: 5 FINISH: SEE TABLE

APPROVED: G. DUBNICZKI 07 JUN 95

PRODUCT SPEC: HEADER ASSEMBLY, MOD II, BREAKAWAY, SINGLE ROW, HIGH TEMPERATURE, VERTICAL, W/.025 SQ. POSTS

SIZE: A1 CASE CODE: 00779 DRAWING NO: 146278

WEIGHT: -

CUSTOMER DRAWING: SCALE: 4:1 SHEET: 1 OF 1 REV: H1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-146278-2](#)