




D

C

B

A



RECOMMENDED HOLE LAYOUT

1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
4. HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
5. FINISH: 0.000381 [.000015] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN-LEAD ON SOLDER TAIL, 0.00127 [.000050] NICKEL ENTIRE POST.
6. FINISH: 0.000381 [.000015] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN ON SOLDER TAIL, 0.00127 [.000050] NICKEL ENTIRE POST.

D

C

B

A

SEE SHEET 2 FOR PART NUMBER TABLES

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

R

BROWN

02MAR2006

CHK

J

GESFORD

02MAR2006

APP

J

GESFORD

02MAR2006

TE Connectivity

DIMENSIONS:

mm [INCHES]

0. PLC

±

-

1. PLC

±

-

2. PLC

±

0.51 [.02]

3. PLC

±

0.12 [.005]

4. PLC

±

0.012 [.0005]

ANGLES

±

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

SEE TABLE

APPROVED

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

NAME

HEADER ASSEMBLY, MOD II, STACKING, DOUBLE ROW, .025 SQ.POST, UNSHROUDED

SIZE

A1

CAGE CODE

00779

DRAWING NO

146503

SCALE

4:1

SHEET

1

OF

2

REV

A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-146503-7](#)