

② USE 1.32 ± 0.02 [.0520 \pm .0010] DRILLED HOLE (#55 DRILL). FINISH TO BE
TIN OVER 0.02 [.001] MIN COPPER.

3 DIMENSION APPLIES AT BASE OF SHROUD.

4 THE NOTED DIMENSIONS APPLY AT THE MATING FACE OF THE HOUSING.

5 0.0038 [0.000150] TIN LEAD ON HOLD DOWN, ALL OVER 0.0013 [0.000050] NICKEL.

6. IF PLANNING TO USE MORE THAN ONE MATING PAIR OF CONNECTORS TO INTERCONNECT 2 BOARDS, PLEASE REFER TO THE SPACING PARAGRAPH IN APPLICATION SPEC, #114-7010

7. PACKAGED IN TUBES

⑧ DIMENSIONS NOTED APPLY FROM THE BASIC DIMENSION LINE (NOT THE CIRCUIT CAVITY CENTER LINE) TO THE SURFACE INDICATED.


9 0.00076[.000030] GOLD AT POINT OF MEASUREMENT, 0.00051[.000020] MIN AT THE
END POINTS OF AREA G, (LOCALIZED GOLD PLATE AREA), 0.0038[.000150] TIN
ON LOCALIZED TIN PLATED AREA, ALL OVER 0.0013[.000050] NICKEL.

USE 1.32±0.02(.0520±.0010) DRILLED HOLE (#55 DRILL) FINISH TO BE TIN OVER 0.02(.001) MIN COPPER.


11 0.0038 (.000150) TIN ON HOLDDOWN, ALL OVER 0.0013 (.000050) NICKEL

 ROHS 2002/95/EC COMPLIANT

△13 HOUSING: LCP, COLOR: BLACK
POST: PHOSPHOR BRONZE
VACCU COVER: ALUMINIUM
HOLD DOWN: COPPER ALLOY



CONTACTS NOT SHOWN




































PLATED THRU HOLE 
2 PLCS

⊕	∅0.15 [.006] (S)	M	N
	∅0.08 [.003] (S)		

Ø 1.65±0.02
[.065±.001]
PAD ON TOP SIDE
1.65[.065] MIN. ON UNDER
SIDE (2PLCS)

\varnothing	$\varnothing 0.23 \quad [.009] \textcircled{S}$	M	N
	$\varnothing 0.05 \quad [.002] \textcircled{S}$		

	65.33 [2.572]	66.59 [2.622]	64.05 [2.522]	49	100	 6-2267256-0
	58.98 [2.322]	60.24 [2.372]	57.70 [2.272]	44	90	 5-2267256-9
	52.63 [2.072]	53.89 [2.122]	51.35 [2.022]	39	80	 5-2267256-8
	46.28 [1.822]	47.54 [1.872]	45.00 [1.772]	34	70	 5-2267256-7
	39.93 [1.822]	41.19 [1.622]	38.65 [1.522]	29	60	 5-2267256-6
	33.58 [1.322]	34.84 [1.372]	32.30 [1.272]	24	50	 5-2267256-5
	27.23 [1.072]	28.49 [1.122]	25.95 [1.022]	19	40	 5-2267256-4
	20.88 [.822]	22.14 [.872]	19.60 [.772]	14	30	 5-2267256-3
	14.53 [.572]	15.79 [.622]	13.25 [.522]	9	20	 5-2267256-2
	8.18 [.322]	9.44 [.372]	6.90 [.272]	4	10	 5-2267256-1
	65.33 [2.572]	66.59 [2.622]	64.05 [2.522]	49	100	1-2267256-0
	58.98 [2.322]	60.24 [2.372]	57.70 [2.272]	44	90	2267256-9
	52.63 [2.072]	53.89 [2.122]	51.35 [2.022]	39	80	2267256-8
	46.28 [1.822]	47.54 [1.872]	45.00 [1.772]	34	70	2267256-7
	39.93 [1.822]	41.19 [1.622]	38.65 [1.522]	29	60	2267256-6
	33.58 [1.322]	34.84 [1.372]	32.30 [1.272]	24	50	2267256-5
	27.23 [1.072]	28.49 [1.122]	25.95 [1.022]	19	40	2267256-4
	20.88 [.822]	22.14 [.872]	19.60 [.772]	14	30	2267256-3
	14.53 [.572]	15.79 [.622]	13.25 [.522]	9	20	2267256-2
	8.18 [.322]	9.44 [.372]	6.90 [.272]	4	10	2267256-1
FINISH	D	C	B	A	NUMBER OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03APR2019 RAVI S CHK 03APR2019 J OLSON		 TE Connectivity	
DIMENSIONS: mm [INCH]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±0.13(.005) 3 PLC ±. 4 PLC ±. ANGLES ±. 		NAME HDR ASSY, THROUGH HOLE AMPMODU 50/50 GRID (9.90(.390) MATED HEIGHT)	
MATERIAL 		FINISH - SEE TABLE		SIZE CASE CODE DRAWING NO A1 100779 C=2267256	
		WEIGHT - CUSTOMER DRAWING		RESTRICTED TO SCALE 10:1 SHEET 1 of 1 REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-2267256-7](#)